



Save Money




Save Time





















Peace of Mind


The Fail-Safe FSN provides a 4" aperture, 6" grid width providing sleek lines of light with a clear bottom lens which seals the fixture preventing dust and water intrusion. Available in three fixed lengths, FSN can be grid recessed or hard ceiling recessed mounted. A selectable switch comes standard with three selectable lumen levels and three selectable color temperatures, providing FSN the flexibility to adapt to the changing needs of the space, setting, or environment. The FSN is an excellent choice for a wide range of applications including vandal-resistant, behavioral health, medical, and hosedown.




 Save Money
  Save Time
  Peace of Mind

Category	Feature	Benefit	Result
Construction	Clear bottom lens seals fixture	Prevents dust and water intrusion	  
	Optional polycarbonate lens available	Impact resistance	  
	Simple switch to adjust lumens and CCT on site as desired	Design flexibility; versatility	  
Performance	IP66 rated	Added protection from elements (dust, water)	  
	NSF rated	Certified for use in food processing facilities	  
	Five year warranty standard, ten year warranty available	Guaranteed performance	  

Ceiling Compatibility



Mounting Choices



Energy and Performance Data by Catalog Number

Catalog Number	CCT	Lumen Output Lumen Setting			Wattage Lumen Setting			Efficacy Lumen Setting		
		Low	Medium	High	Low	Medium	High	Low	Medium	High
2FSN6-SL1-CA08-L8SCT3	3000	1150	1685	1987	10.9	16.1	19.4	106	105	102
	3500	1181	1725	2044	10.8	16.1	19.4	109	107	105
	4000	1196	1751	2061	10.8	16.0	19.4	111	109	106
2FSN6-SL1-CA125-L8SCT3	3000	1148	1682	1983	10.9	16.1	19.4	105	104	102
	3500	1179	1722	2041	10.8	16.1	19.4	109	107	105
	4000	1194	1748	2058	10.8	16.0	19.4	111	109	106
2FSN6-SL1-CP125-L8SCT3	3000	1121	1642	1937	10.9	16.1	19.4	103	102	100
	3500	1151	1681	1993	10.8	16.1	19.4	107	104	103
	4000	1166	1707	2009	10.8	16.0	19.4	108	107	104
2FSN6-SL1-CP187-L8SCT3	3000	1107	1621	1912	10.9	16.1	19.4	102	101	99
	3500	1137	1660	1968	10.8	16.1	19.4	105	103	101
	4000	1152	1686	1984	10.8	16.0	19.4	107	105	102
2FSN6-SL1-CP250-L8SCT3	3000	1088	1594	1880	10.9	16.1	19.4	100	99	97
	3500	1117	1632	1934	10.8	16.1	19.4	103	101	100
	4000	1132	1657	1950	10.8	16.0	19.4	105	104	101
4FSN6-SL1-CA08-L8SCT3	3000	2164	3201	4028	18.3	27.6	36.1	118	116	112
	3500	2202	3257	4074	18.3	27.7	36.1	120	118	113
	4000	2222	3280	4121	18.2	27.5	35.9	122	119	115
4FSN6-SL1-CA125-L8SCT3	3000	2151	3182	4004	18.3	27.6	36.1	118	115	111
	3500	2188	3237	4050	18.3	27.7	36.1	120	117	112
	4000	2209	3261	4097	18.2	27.5	35.9	121	119	114
4FSN6-SL1-CP125-L8SCT3	3000	2101	3107	3910	18.3	27.6	36.1	115	113	108
	3500	2137	3161	3955	18.3	27.7	36.1	117	114	110
	4000	2157	3184	4000	18.2	27.5	35.9	119	116	111
4FSN6-SL1-CP187-L8SCT3	3000	2074	3068	3861	18.3	27.6	36.1	113	111	107
	3500	2110	3122	3905	18.3	27.7	36.1	115	113	108
	4000	2130	3144	3950	18.2	27.5	35.9	117	114	110
4FSN6-SL1-CP250-L8SCT3	3000	2039	3015	3795	18.3	27.6	36.1	111	109	105
	3500	2074	3068	3838	18.3	27.7	36.1	113	111	106
	4000	2094	3090	3883	18.2	27.5	35.9	115	112	108
8FSN6-SL1-CA08-L8SCT3	3000	4621	6767	7981	38.6	58.0	77.3	120	117	103
	3500	4743	6928	8213	38.6	58.0	77.3	123	120	106
	4000	4806	7034	8280	39.0	62.4	78.7	123	113	105
8FSN6-SL1-CA125-L8SCT3	3000	4594	6727	7934	38.6	58.0	77.3	119	116	103
	3500	4715	6887	8164	38.6	58.0	77.3	122	119	106
	4000	4777	6992	8230	39.0	62.4	78.7	123	112	105
8FSN6-SL1-CP125-L8SCT3	3000	4486	6568	7747	38.6	58.0	77.3	116	113	100
	3500	4604	6725	7972	38.6	58.0	77.3	119	116	103
	4000	4665	6828	8037	39.0	62.4	78.7	120	109	102
8FSN6-SL1-CP187-L8SCT3	3000	4429	6486	7650	38.6	58.0	77.3	115	112	99
	3500	4546	6640	7872	38.6	58.0	77.3	118	115	102
	4000	4606	6742	7936	39.0	62.4	78.7	118	108	101
8FSN6-SL1-CP250-L8SCT3	3000	4354	6375	7519	38.6	58.0	77.3	113	110	97
	3500	4468	6527	7737	38.6	58.0	77.3	116	113	100
	4000	4528	6627	7800	39.0	62.4	78.7	116	106	99