

CONFINEMENT	SURFACE									RECESSED		CORNER		WALL			
	FMS	FMSLP	FUS	FUSLP	FCT	FAS	HMS HMSCR	HDS HDSCR	HUR	FMR	FSR	FCC	FMC	FMB	FMW	FWS	
<b>Inner Lens</b>																	
90	UV Overlay, .005"						N/A	N/A	N/A								
80	Acrylic, Pattern 12, 0.125"						N/A	N/A	N/A								
89CV	Acrylic, Pattern 12, 0.187"						N/A	N/A	N/A								
89CB	Acrylic, Pattern 19, 0.187"						N/A	N/A	N/A								
89BB	Acrylic, Pattern 20, 0.140"						N/A	N/A	N/A								
89AH	Polycarbonate, Pattern 12, 0.125"						N/A	N/A	N/A								
81	Polycarbonate, Pattern 12, 0.156"						N/A	N/A	N/A								
82	Polycarbonate, Pattern 12, 0.187"						N/A	N/A	N/A								
93	Glass, Tempered Prismatic, 0.156"																
KSH25	Acrylic, Pattern 25 Directional, 0.115"						N/A	N/A	N/A								
<b>Outer / Environmental Lens</b>																	
84	Polycarbonate, Clear, 0.125"																
85	Polycarbonate, Clear, 0.187"																
86	Polycarbonate, Clear, 0.250"																
87	Polycarbonate, Clear, 0.375"																
88	Polycarbonate, Clear, 0.500"						N/A	N/A	N/A								
94	Glass, Tempered Clear, 0.187"																
96	Glass, Tempered, Clear, 0.250"																
97	Glass, Tempered Clear, 0.375"																
98	Glass, Tempered Clear, 0.500"						N/A	N/A	N/A								
99AR	Glass, Tempered Clear, 0.750"						N/A	N/A	N/A								N/A
89AM	Polycarbonate, Opal Smooth, 0.125"						N/A	N/A	N/A								

All lens options available for Surface, Recessed, Corner and Wall CONFINEMENT products  N/A Not Applicable

	CLEANROOM					HEALTHCARE		
	Linear Fluorescent					Medical		
	CPI	CFD	CFE	CF	CR	MOR	ORM	MPR
89AV	Acrylic, Pattern 12 RFI, 0.125"							
89BV	Acrylic, Clear, 0.125"							
IK12	Acrylic, Pattern 12, 0.110"							
89AP	Acrylic, Pattern 12, 0.125"							
89BM	Acrylic, Pattern 12, 0.140"							
89CV	Acrylic, Pattern 12, 0.187"							
89BG	Acrylic, Pattern 15, 0.187"							
89BC	Acrylic, Pattern 19 RFI, 0.125"							
89AG	Acrylic, Pattern 19, 0.156"							
89CB	Acrylic, Pattern 19, 0.187"							
89BB	Acrylic, Pattern 20, 0.140"							
KSH25	Acrylic, Pattern 25 Directional, 0.115"							
ID12	Acrytuf, Pattern 12, 0.110"							
89AR	Acrytuf, Pattern 12, 0.140"							
89AN	Acrytuf, Pattern 12, 0.187"							
93	Glass, Prismatic Tempered, 0.156"							
IP12	Polycarb, Pattern 12, 0.110"							
89AH	Polycarb, Pattern 12, 0.125"							
89BJ	Polycarb, Pattern 12, 0.187"							
90	UV Overlay, 0.005"							
89CP	UVA Lite, Pattern 12, 0.125"							
89AM	Polycarbonate, Opal Smooth, 0.125"							
89BW	Acrylic, Opal Smooth, 0.125"							
89AM	Polycarbonate, Opal Smooth, 0.125"							

