

HALO

IMPORTANT SAFETY INSTRUCTIONS INSTALLATION OF L-973 CANOPY ADAPTER 120 V.A.C.

NOTE: For use ONLY with Halo single & 2 circuit lampholders - 300W max A.C.

WARNING: Turn off main power supply before attempting to install this device. Danger of electric shock.


INSTALLATION

Step 1 Turn power off. Mount the adjustable mounting plate to the ceiling elec. box with (2) 8-32 screws as shown. Select the desired canopy mtg. position.

Step 2 Bring feed wire through center hole of mtg. plate. Connect these wires to wires from L973 adapter, black to black, white to white. If a green wire is available, connect it to the bare copper wire from the L-973 adapter. The bare copper wire may also be connected to one of the electrical box mtg. screws.

Step 3 Attach the canopy with (2) 8-32 flat head painted screws (furnished)

Step 4 Insert the desired 120 V.A.C. lampholder into canopy observing ground polarity line. Max wattage 300 W.



SAVE THESE INSTRUCTIONS