

DESCRIPTION

Adjustable Gimbal trim for 12V low voltage 4" H1499 family recessed housings. Gimbal tilts 30°. Die cast trim ring available in a variety of finishes. Three "cat's paw" springs secure trim in housing.


Catalog #		Type
Project		
Comments		Date
Prepared by		

DESIGN FEATURES

Cast aluminum gimbal and trim ring available in Matte White, Silver, Satin Nickel, Antique Copper or Tuscan Bronze finishes. Three pressure springs ensure positive retention in housing.

1495 is designed for use with the following small aperture housings;

- Low Voltage Housing
 - H1499T 50W 12V MR16
 - H1499RT 50W 12V MR16
 - H1499ICT 50W 12V MR16
 - H1499T75 75W 12V MR16




1495P
White Gimbal with White Trim




1495SL
Silver Gimbal with Silver Trim



1495SN
Satin Nickel Gimbal with Satin Nickel Trim



1495AC
Antique Copper Gimbal with Antique Copper Trim



1495TBZ
Tuscan Bronze Gimbal with Tuscan Bronze Trim Ring

1495
Adjustable Gimbal Trim

4" TRIMS

Trim

- 1495P**= White Gimbal and Trim
- 1495SL**= Silver Gimbal and Trim
- 1495SN**= Satin Nickel Gimbal and Trim
- 1495AC**= Antique Copper Gimbal and Trim
- 1495TBZ**= Tuscan Bronze Gimbal and Trim