

DESCRIPTION


Adjustable Eyeball trim for 4" H99 incandescent family recessed housings. The 998 eyeball is designed for use with PAR16 lamps. Eyeball has 30° tilt and can be rotated in housing 360° to align with wall surface. Eyeball and die cast trim ring are available in a variety of finishes. Three "cat's paw" springs secure trim in housing. Integral trim socket with screw base adapter to connect with housing socket.

SPECIFICATION FEATURES

The 998 eyeball and die cast aluminum trim ring available in Matte White, Polished Brass, Satin Nickel, Antique Copper or Tuscan Bronze finishes.

998 is designed for use with the following small aperture housings.

- Incandescent Housings
 - H99TAT - 40W R16, 60W PAR16
 - H99RTAT - 40W R16, 60W PAR16
 - H99ICAT - 40W R16



Trim



- 998P= White Adjustable Eyeball, White Trim Ring
- 998PB= Polished Brass Adjustable Eyeball, Polished Brass Trim Ring
- 998SN= Satin Nickel Adjustable Eyeball, Satin Nickel Trim Ring
- 998AC= Antique Copper Adjustable Eyeball, Antique Copper Trim Ring
- 998TBZ= Tuscan Bronze Adjustable Eyeball, Tuscan Bronze Trim Ring

Catalog #		Type
Project		
Comments		Date
Prepared by		



998P
White Trim with White Eyeball



998PB
Polished Brass Trim with Polished Brass Eyeball



998SN
Satin Nickel Trim with Satin Nickel Eyeball



998AC
Antique Copper Trim with Antique Copper Eyeball



998TBZ
Tuscan Bronze Trim with Tuscan Bronze Eyeball

998 Adjustable Eyeball Trim

4" TRIMS