

DESCRIPTION

Designed for sloped ceiling installations for ceilings from 2/12 to 6/12 pitch. The socket aiming mechanism allows the lamp to be aimed straight down regardless of ceiling pitch. Designed for use in insulated ceilings

Catalog #	Type
Project	
Comments	
Prepared by	Date

SPECIFICATION FEATURES

A...Baffle

One piece seamless baffle presents a clean finished appearance.

B...Trim Ring

White Polycarbonate trim ring.

C...Housing

Double wall housing construction. Door in outer housing allows junction box access from below ceiling.

D...Junction Box

Junction box is listed for through branch circuit wiring and has seven 1/2" knockouts with true pry-out slots.

E...GOT NAIL! Pass-N-Thru™ Bar Hangers

Bar Hanger Features include:

- Pre-installed nail easily installs in regular lumber, engineered lumber and laminated beams
- Safety and guidance system prevents snagging, ensures smooth straight nail penetration and allows bar hangers to be easily removed if necessary.
- Automatic levelling flange aligns the housing and lets you hold the housing in place with one hand while driving nails
- Housing can be positioned at any point within 24" joist span
- Score lines allow "toolless" shortening for 12" joists
- Bar hangers may be repositioned 90°
- Bar hangers do not need to be removed from frame for shortening

- Integral T-bar clips snaps onto T-bars - no additional clips required

F...Socket


Exclusive socket aiming mechanism swivels and rotates to properly align lamp. Slope indicator provides quick and consistent lamp settings (factory set for 3/12 slope).

G...Integral Thermal Protector

Integral thermal protector guards against improper lamping.

Labels


- UL Listed for Damp Location
 - UL listed for Feed Through
 - UL listed for Direct Contact with Insulation and combustible material
 - CSA Certified
- Meets following requirements:
- State of California Title 24



H47ICT

2 0 W 1 2 V M R 1 6
 7 5 W R 3 0
 7 5 W A 1 9
 9 0 W P A R 3 8
 1 0 0 W R 3 0

6" RECESSED
 INCANDESCENT
 DOWNLIGHT



ADV042510
 Supersedes ADV000337


TRIMS

ORDERING INFORMATION

SAMPLE NUMBER: H47ICT498P


Complete unit consists of housing and trim.

Housing



H47ICT=6" IC
Slope Ceiling Housing

Trims



BAFFLES

Coilix Baffle

90W PAR38
498P=Black
498W=White
OD: 7 7/8" (200mm)



Coilix Baffle with Reflector

75W A19
496P=Black
496W=White
OD: 7 7/8" (200mm)



ADJUSTABLES

Coilix Baffle Eyeball

75W R30, 65W BR30
417P=Black
417PB=Polished Brass
417W=White
OD: 8" (203mm)



Eyeball-30° Tilt

100W R30, 85W BR30
78P=Satin White
78B=Brass
78PB=Polished Brass
78PAT=White Air-Tite
OD: 8" (203mm)



Baffle Eyeball

20W 12V MR16
1417P=Black Baffle, White Eyeball, White Trim Ring
1417W=White Baffle, White Eyeball, White Trim Ring
OD: 8" (203mm)



Lensed Shower Light

60W A19
170PS=Glass Lens, White Trim Ring wet location
Listed
OD: 8" (203mm)

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at www.cooperlighting.com