

DESCRIPTION

594 Series LED Trims – 5-Inch Aperture Directional Eyeballs with Baffle – are integral elements in the Halo ML56 LED Downlighting System. ML56 LED System is a series of modular LED Light Modules for use with dedicated 5" or 6" ML56 LED trims. The ML56 LED trims in 5" and 6" aperture sizes are designed to fit Halo, All-Pro and others 5" or 6" recessed housings. The ML56 system is suitable for new construction, remodel or retrofit installation.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

594 Series LED trims are 5-inch aperture Eyeballs with baffles offered in White (Matte White), Satin Nickel, and Tuscan Bronze. The precision spun aluminum eyeball with baffle element delivers the functionality of a directional accent. The directional eyeball can be tilted from 0 to 30 degrees, and the rotational mechanism allows for rotation adjustment up to 360 degrees. The 594 eyeballs may be used in most standard height 5-inch aperture recessed housings; Halo, All-Pro, and more (refer to ML56 LED Light Module specifications for details).

- For use with ML56 Series LED light modules
- Eyeball with baffle and self- flange
- Torsion springs pull trim and light module tight to ceiling
- For use in standard and shallow housings
- Eyeball tilts from 0 to 30 degrees
- Rotation adjustment mechanism for rotation capability up to 360 degrees
- Damp location listed with ML56 LED light modules

Compatible with ML56 LED System of LED Downlight Light Modules

600 Series - 80CRI, 600lm

5" / 6" LED Retrofit Downlight Engine

ML5606827 - 2700K
ML5606830 - 3000K
ML5606835 - 3500K
ML5606840 - 4000K

600 Series - 90CRI, 600lm

5" / 6" LED Retrofit Downlight Engine

ML5606927 - 2700K
ML5606930 - 3000K
ML5606935 - 3500K
ML5606940 - 4000K

900 Series - 80CRI, 900lm

5" / 6" LED Retrofit Downlight Engine

ML5609827 - 2700K
ML5609830 - 3000K
ML5609835 - 3500K
ML5609840 - 4000K

900 Series - 90CRI, 900lm

5" / 6" LED Retrofit Downlight Engine

ML5609927 - 2700K
ML5609930 - 3000K
ML5609935 - 3500K
ML5609940 - 4000K

1200 Series - 80CRI, 1200lm


5" / 6" LED Retrofit Downlight Engine

ML5612827 - 2700K
ML5612830 - 3000K
ML5612835 - 3500K
ML5612840 - 4000K

1200 Series - 90CRI, 1200lm

5" / 6" LED Retrofit Downlight Engine

ML5612927 - 2700K
ML5612930 - 3000K
ML5612935 - 3500K
ML5612940 - 4000K



594WB



594SNB*



594TBZB*

594 Series LED Trim

5-Inch Eyeball with Baffle

For use with Halo ML56 LED System Light Modules

ORDERING INFORMATION

SAMPLE NUMBER: 594WB

Trim	Finish	Accessory
594= 5" Eyeball with Baffle	WB =White Eyeball with Baffle, White Flange SNB =Satin Nickel Eyeball with Baffle, Satin Nickel Flange* TBZB =Tuscan Bronze Eyeball with Baffle, Tuscan Bronze Flange*	TRM590WH =5" LED Oversize Trim Ring for use with 59" series trims, White 6.3" I.D., 7.5" O.D. Ring slips over LED trim. Inset design allows 5" trim to fit into oversize ring for an even trim surface

*SNB & TBZB models for use with 600 & 900 Series ONLY