



H221 - SHALLOW IC HOUSING

Source	Model	Description
H221	IC Housing with hanger bars, junction box and magnetic ballast	Integral 120V 60 Hz magnetic fluorescent ballast for one 13W Twin Tube 2-pin Compact Fluorescent lamp (F13TT, GX23 base). Junction box listed for through branch circuit wiring and has two 3/4" and five 1/2" knockouts. Bar hangers will span 24" joists. 3-1/2" height for use in shallow ceilings. May be installed in IC applications. May be installed in ceiling or wall. UL/cUL Damp location listed, Feed through Listed, Replacement Lamp: Available by others or as Halo #Z63
24P	Flush Diffuser Trim	
HOUSING	8-3/8"L x 4-5/8"D x 3-1/2"H (213mm x 117mm x 89mm)	
TRIM	5-1/2" x 9-1/4" (140mm x 235mm)	



H2925T, H2925TW, H2925PL - BRICK LIGHT / AISLE LIGHT

Source	Description
	With thermal protector, brown die cast trim, flat unbreakable lens and tamper proof screws. (Non-IC)
H2925T	Incandescent 20W T6 1/2 lamps (Halo Z7). (Damp location listed)
H2925TW	Incandescent 20W T6 1/2 lamps (Halo Z7). (Wet location listed)
H2925PL	7W 2-pin, G23 base compact fluorescent lamps or 9W lamp. (UL/cUL Wet location listed)
SD2925	Tamper proof screwdriver accessory
HOUSING	7-3/8"L x 3-1/2"D x 2-1/4"H (187mm x 89mm x 57mm)
TRIM	8-7/8"L x 3-1/2"H (225mm x 89mm)



H2926TW - BRICK LIGHT / AISLE LIGHT

Source	Description
	With thermal protector, brown die cast trim, glare reducing shade and tamper proof screws. (Non-IC)
H2926TW	Incandescent 20W T6 1/2 lamps (Halo Z7). (Wet location listed)
ACCESSORY	Tamper proof screwdriver accessory
HOUSING	7-3/8"L x 3-1/2"D x 2-1/4"H (187mm x 89mm x 57mm)
TRIM	8-7/8"L x 3-1/2"H (225mm x 89mm)



H2920ICT - STEP LIGHT

Source	Description
H2920ICT	Step Light with white louver trim. Wiring connections are made in fixture. 25W A19 lamp. (IP Rated)
HOUSING	8"L x 3-1/2"D x 4-1/2"H (203mm x 89mm x 114mm)
TRIM	9-3/8"L x 5-3/4"H (238mm x 146mm)
FINISH	White (P)



H2922ICT - STEP LIGHT

Source	Description
H2922ICT	Step Light with white louver trim. Fixture is prewired to junction box. UL/cUL listed junction box rated for feed through. 25W A19 lamp. IC rated for direct contact with insulation and combustible materials. (IP Rated)
HOUSING	11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)
TRIM	9-3/8"L x 5-3/4"H (238mm x 146mm)
FINISH	White (P)



H2922-120PL - STEP LIGHT

Source	Description
H2922-120PL	Step Light with white louver trim. Fixture is prewired to junction box. UL/cUL listed junction box rated for feed through. Integral 120V, 60 Hz magnetic ballast. (5W / 7W / 9W Twin Tube 2-pin CFL)
HOUSING	11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)
TRIM	9-3/8"L x 5-3/4"H (238mm x 146mm)
FINISH	White (P)

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.



H2900T - THRU-WALL LIGHT, NON-IC

Source	Description
H2900T	Provides lighting on each side of wall. 100W A19. (Albalite Glass Lens)
HOUSING	13-1/2"L x 4"D x 8-1/4"H (343mm x 102mm x 210mm)
TRIM	11-3/8"L x 7-3/4"H (289mm x 197mm)
FINISH	White (P)



H2932ICTW - LENSED WALL / STEP LIGHT

Source	Description
H2932ICTW	UL/cUL Listed for wall mounting in insulation. IC rated for direct contact with insulation and combustible material, UL/cUL listed for damp location; and feed through. (White trim with Albalite Glass Lens)
HOUSING	11-1/2"L (enclosure and J-Box) x 5-1/2"D x 3-1/2"H (292mm x 140mm x 89mm)
TRIM	5-3/4"L x 9-3/8"H (146mm x 238mm)
LAMP	25W, A19 max.
FINISH	White (P)



H2932T - CLOSET LIGHT / SHALLOW RECTANGLE, NON-IC

Source	Description
H2932T	White trim with albalite diffuser. Junction box rated for feed through branch applications. (For Non-Insulated Ceilings. UL/cUL Listed)
HOUSING	11-5/8"L x 3-1/2"D x 5-1/2"H (295mm x 89mm x 140mm)
TRIM	9-3/8"L x 5-3/4"H (238mm x 146mm)
LAMP	60W, A19 max.
FINISH	White (P)



H37T-401AL - HEAT LIGHT, NON-IC

Source	Description
H37T-401AL	For Non-Insulated Ceilings. IP Rated (Improper Lamp)
HOUSING	8"OD x 5-1/2"H (203mm x 140mm)
TRIM RING	Brushed Aluminum
LAMP	250W Infra-Red



477 - POWER-TRAC ADAPTER TRIM

Source	Description
477	Allows (120V) Trac Lampholders (150W max) to be used with recessed installations. (Use with H7T, H7ICT, H27T, H7RT, H7RICT, H27RT and H44T housings)
OD	7-1/4" (184mm)
FINISH	White with Black Baffle (477P), White with White Baffle (477W)



DICHROIC COLOR FILTERS

Source	Model
L114	UV Filter
L120	Red
L121	Amber
L122	Yellow
L123	Green
L124	Daylight
L125	Blue
L127	Cosmetic Color Filters
L130	Yellow

For low voltage MR16 units.



OPTICAL LENSES

Source	Model
L110	Diffuse Sand Blasted Lens
L111	Soft Focus Textured Lens
L113	Prismatic Lens
L115	Linear Spread Lens


For Low Voltage MR16 units

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.



DESIGNER FINISH TRIM RINGS

Source	Model	Description
TRM6P	White Metal	Metal 7 1/4" OD (184mm). (Compatible with 310°, 312°, 376, 378, 400, 404, 405, 406SC, 406RG, 409, 410, 416, 419, 420, 424, 425, 426°, 429°, 446, 448, 455CG, 455SC, 456P, 456W, 477, 478, 1412, 1416, 1475, 2412, 2416, 2475) *Supplied with TRM6P white metal trim rings (All others are supplied with white plastic trim rings)
TRM6C	Chrome	
TRM6SN	Satin Nickel	
TRM6TBZ	Tuscan Bronze	
TRM6MB	Black Metal	
TRM7MB	Black Plastic	



OVERSIZED TRIM RINGS

Source	Size	Description
OT400P	6" ID X 9-1/4" OD (152mm x 235mm)	Oversized white metal trim ring. (May be used behind any Halo H7/H750 trim family)
OT403P	6" ID X 8" OD (152mm x 203mm)	Oversized white plastic trim ring. (Compatible with 310, 312, 376, 378, 400, 404, 405, 406 (SC and RG only), 409, 410, 416, 419, 420, 424, 425, 426, 429, 446, 448, 477, 478, 1412, 1416, 1475, 2412, 2416, 2475)
OT999P	4" ID x 5-3/4" OD (102mm x 146mm)	Oversized white metal trim ring. (Compatible with 990, 992, 993, 994, 996, 998, 999, 1419, 1420, 1421, 1493 and 1498)
OT460P	7-1/2" ID x 11-1/4" OD (191mm x 286mm)	Oversized white metal trim ring compatible with 466, 468 and 480 trims
OT490WH	5-3/16" ID x 9-1/4" OD (132mm x 235mm)	White aluminum ring use with ML7x LED modules: 600 Series, 900 Series and 1200 Series
800PGR	7-1/2" ID x 8-5/8" OD (191mm x 219mm)	H800 oversized trim ring
OT500P	6" ID x 7 1/4" OD (152mm x 184mm)	Oversized white polymer trim ring for use with H5 series straight sided trims



DESIGNER TRIM RINGS

Source	Size	Finishes	Description
TRM400	3-3/8" ID X 5-1/8" OD (86mm x 130mm)	PC - Polished Chrome BK - Black WH - White SN - Satin Nickel TBZ - Tuscan Bronze	For H4 LED TL4 Series LED Trims. Die cast trim ring replaces standard ring included with each trim. (Thin profile provides subtle ceiling appearance) 0.12" OD x 0.18" ID (4mm x 5mm)
TRM490	5-3/16" ID x 7-1/4" OD (132mm x 184mm)		For H7 LED 49x Series LED Trims. Die cast trim ring replaces standard ring included with each trim. (Thin profile provides subtle ceiling appearance) 0.12" OD x 0.18" ID (4mm x 5mm)



TRANSFORMERS

Source	Description
H277	Steps 277V line voltage down to 120V fixture operating voltage. 300VA max. (For use with Non-IC housings)
H347	Same as above but steps 347V down to 120V, 75 VA max. (For use with Non-IC housings)
H347200	Same as above but steps 347V down to 120V, 200 VA max. (For use with Non-IC housings)



HANGING BARS

Source	Description
HB224	One piece hanger bar for 24" maximum joist spacing. (Set of two)
HB424	Two piece hanger bar for 24" maximum joist spacing. (Set of four pieces, order one HB424 per fixture)

Hanger bars are compatible with the following housing families: M700, H800, H801, H802, H803, and H880E.



SLOPE ADAPTERS

Description		Slope	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
White .050 spun aluminum. Available as shown in following table. Items in BOLD face are stocked		6" for H44	HSA680	HSA685	HSA610	HSA615	HSA620	HSA625	HSA630	HSA635	HSA640	
		8" for H46		HSA85	HSA810	HSA815	HSA820	HSA825	HSA830	HSA835	HSA840	HSA845

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.



AIR-TITE™ Gaskets

Description

GA-ATH5-6PK
H5ICAT Air-Tite™ 6-pack gaskets for installation at finished ceiling opening

GA-ATH7-6PK
H7ICAT Air-Tite™ 6-pack gaskets for installation at finished ceiling opening



TRIM GASKETS

Description

GA-ATTRIM-6PK
Accessory / spare trim gasket for use with H7 and EI/ET 700 family trims.



SOCKET EXTENDER

Description

H1999
For use with selected trims and housings. Extends lamp 1" (25mm)



MOUNTING CLIPS

Description

TB7
T-Bar attachment clips. Set of four. Order one set per fixture. Can also be used with HB424 and HB224 Hanger Bars

RK7
Hold down clips for non-remodel fixtures when hanger bars are not used. (Set of four)



R LAMP ACCESSORY

Description

H930
R/PAR lamp aiming accessory for H7T, H7TNB, H7RT, H7ICT, H7ICAT, H7RICT, H7RICAT, H7ICTNB, H7ICATNB housings with 310 and 426 trims. Allows lamp to be aimed up to 30° from vertical and rotated 358°. See housing-trim selection for lamp listings



SCREWDRIVER

Description

SD2925
Screwdriver for tamper resistant screws supplied with H2925 and H2926 brick lights



4 COIL SPRINGS

Description

RS7H
Set of 4 coil springs for use with 301, 310, 401 and 426 trims in the H7 recessed housing family



LAMPS

Description

COMPACT FLUORESCENT

Z62 22W 15mm PL-C, Gx32d-2 Double Twin Tube Compact Fluorescent (2700°K)

Z128 28W 15mm PL-C Gx32d-3 Double Twin Tube (DTT) 2-Pin Compact Fluorescent (2700°K)

Z63 13W Twin Tube Compact Fluorescent, 2-pin, Gx23 (2700°K)

Z64 13W Double Twin Tube Compact Fluorescent, 2-pin, Gx23-2 (2700°K)

Z113E 13W Double Twin Tube (DTT) 4-Pin Compact Fluorescent, G24q-1 (2700°K)

Z118 18W Double Twin Tube (DTT) 2-Pin Compact Fluorescent, G24d-2 (2700°K)

Z118E 18W Double Twin Tube (DTT) 4-Pin Compact Fluorescent G24q-2 (2700°K)

Z126E 26W Double Twin Tube (DTT) 4-Pin Compact Fluorescent, G24q-3 (2700°K)

Z126P30 26W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-3 (3000°K)

Z132P30 32W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-3 (3000°K)

Z142P30 42W Triple Twin Tube (TTT) 4-Pin PL Compact Fluorescent, GX24q-4 (3000°K)

Z118TE30 18W Triple Twin Tube (TTT) 4-Pin Compact Fluorescent, GX24q-2 (3000°K)

Z126TE30 26W Triple Twin Tube (TTT) 4-Pin Compact Fluorescent, GX24q-3 (3000°K)



LAMPS

Description

LOW VOLTAGE

Z21 12V Q50W MR16 NSP

Z26 12V Q50W MR16 NFL

Z31 12V Q50W MR16 FL

Z40 12V Q75W MR16 NSP

Z45 12V Q75W MR16 FL

Z121 50W MR16/Q/10°/TL (GE TURN-AND-LOCK BASE)

Z131 50W MR16/Q/20°/TL (GE TURN-AND-LOCK BASE)

Z124 50W MR16/Q/40°/TL (GE TURN-AND-LOCK BASE)



LAMPS

Description

INCANDESCENT

Z7 20W T 6 1/2" IF

Z9 40W R16 FL

Z10 100W BR25

Z28 120V GU10 base, line voltage MR16

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative or visit www.cooperlighting.com for available options, accessories and ordering information.