

E44 4" Trim Series

The E44 trims are offered in open, lens and lens wall wash in both round and square apertures. They are adjustable and feature 360° rotation, 35° tilt and when combined with various distribution lamps provide a broad range of optical distributions providing accent, task, wall washing / grazing and general area illumination. E26 medium base to GU10 adapter provided, useful in retrofitting H99 or compatible incandescent housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

FULL OVERLAP TRIMS



The E44 full overlap trims are used with both new construction and remodeler housings. The full overlap flange style trims match the ML4 trim series.

Directional Open
1440 Conical Reflector
1441 Conical Baffle
1444 Round Pinhole
1445 Round Pinhole w/Oculus
1484 Square Pinhole
1485 Square Pinhole w/Oculus

Lens Wall Wash
1442 Angle Cut Conical Reflector
1446 Round Pinhole
1486 Square Pinhole

Directional Lens
1443 Conical Reflector
1447 Round Pinhole
1449 Round All Acrylic-Glass
1487 Square Pinhole
1489 Square All Acrylic-Glass

DIRECTIONAL OPEN



1440
Conical Reflector,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1440MWWF

Trim	Finish
1440 = 4" conical reflector, open, 35° tilt	BN =Brushed Nickel GB =German Bronze H =Haze HWF =Haze, White Flange MWWF =Matte White, White Flange



1441
Conical Baffle,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1441MBWF

Trim	Finish
1441 = 4" conical baffle, open, 35° tilt	BBWF =Black Baffle, White Flange BN =Brushed Nickel GB =German Bronze WBWF =White Baffle, White Flange



1444
Round Pinhole,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1444MW

Trim	Finish
1444 = 4" round pinhole, open, 35° tilt	BN =Brushed Nickel GB =German Bronze MW =Matte White



1445
Round Pinhole with Oculus,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1445MWWB

Trim	Finish
1445 = 4" round pinhole w/oculus, open, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle

DIRECTIONAL OPEN



1484
Square Pinhole,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1484MW

Trim	Finish
1484 = 4" square pinhole, open, 35° tilt	BN =Brushed Nickel GB =German Bronze MW =Matte White



1485
Square Pinhole w/Oculus,
Open, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1485MWWB

Trim	Finish
1485 = 4" square pinhole w/oculus, open, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle

LENS WALL WASH



1442
Angle Cut Conical Reflector,
Lens Wall Wash

ORDERING INFORMATION

SAMPLE NUMBER: 1442MWWF

Trim	Finish
1442 = 4" angle cut conical reflector, lens wall wash	H =Haze HWF =Haze, White Flange MWWF =Matte White, White Flange



1446
Round Pinhole,
Lens Wall Wash

ORDERING INFORMATION

SAMPLE NUMBER: 1446MWWB

Trim	Finish
1446 = 4" round pinhole, lens wall wash	MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle



1486
Square Pinhole,
Lens Wall Wash

ORDERING INFORMATION

SAMPLE NUMBER: 1486MWWB

Trim	Finish
1486 = 4" square pinhole, lens wall wash	MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle

DIRECTIONAL LENS



1443
Conical Reflector,
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1443MWWF

Trim	Finish
1443 = 4" conical reflector, diffuse lens, 35° tilt	H =Haze HWF =Haze, White Flange MWWF =Matte White, White Flange



1447
Round Pinhole,
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1447MWWB

Trim	Finish
1447 = 4" round pinhole, diffuse lens, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle



1449
Round "All Acrylic-Glass",
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1449AAG

Trim	Finish
1449 = 4" round "all acrylic-glass", diffuse lens, 35° tilt	AAG =All Acrylic Glass



1487
Square Pinhole,
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1487MWWB

Trim	Finish
1487 = 4" square pinhole, diffuse lens, 35° tilt	BNBB =Brushed Nickel, Black Baffle GBBB =German Bronze, Black Baffle MWBB =Matte White, Black Baffle MWWB =Matte White, White Baffle



1489
Square "All Acrylic-Glass",
Diffuse Lens, 35° tilt

ORDERING INFORMATION

SAMPLE NUMBER: 1489AAG

Trim	Finish
1489 = 4" square "all acrylic-glass", diffuse lens, 35° tilt	AAG =All Acrylic Glass