


30

- Self-flanged socket supporting trim with torsion spring retention
- Accepts a wide range of lamps
- Makes installation AIR-TITE regardless of housing used

H7T	75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 100W A19
H7TNB	
H7RT	50W PAR30, 65W BR30, 75W R30, 75W PAR30L, 150W A21



Height: 5" [127mm]
Outside Diameter: 7-1/4" [184mm]

Super Trim™ AIR-TITE Reflector



30HAT

White Trim with Haze Reflector

30GAT

White Trim with Gold Reflector

30CAT

White Trim with Clear Specular Reflector


Halo AIR-TITE trims are designed to meet restricted airflow requirements. However local code may require a trim gasket regardless of trim design. Where required, use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATTRIM-6PK.

30SBAT

- Black Specular Reflector and Trim
- Self Flanged Socket Supporting Trim with Torsion spring retention
- Accepts a wide range of lamps
- Makes installation AIR-TITE regardless of housing used

H7T	50W PAR30, 75W PAR30, 100W R30, 85W BR30, 150W R40, 120W BR40, 100W A19, 150W PAR38, 150W A21
H7TNB	
H7RT	50W PAR30, 65W BR30, 75W R30, 75W PAR30L, 150W A21

Super Trim™ Self Flanged Reflector



Height: 5" [127mm]
Outside Diameter: 7-1/4" [184mm]



30SBAT

Black Specular Reflector


Halo AIR-TITE trims are designed to meet restricted airflow requirements. However local code may require a trim gasket regardless of trim design. Where required, use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATTRIM-6PK.

405

- Full reflector for use with A-lamps
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring
- Can lip friction clip retention

H7T	150W A21
H7RT	
H7TNB	

Specular Reflector



Height: 6" [152mm]
Outside Diameter: 7-1/4" [184mm]



405SC

White Trim with Clear Specular Reflector

405H

White Trim with Haze Reflector

405RG

White Trim with Gold Reflector



405CG


White Trim with Champagne Gold Reflector

4051

- Full reflector for use with A-lamps.
- Can lip friction clip retention
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring

H7T	150W A21
H7RT	
H7TNB	

Self Flanged White Reflector



Height: 6" [152mm]
Outside Diameter: 7-1/4" [184mm]



4051P


White Self Flanged Reflector

429

Dayform White Cone

- Sloped sides shield interior view of housing
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring

H7T	65W BR30, 75W R30
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L



Height: 3" [76mm]
Outside Diameter: 7-1/4" [184mm]




429P
White Trim and Splay Reflector

426

Reflector Cone

- Accepts a wide variety of lamps
- Coil spring retention
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring

H7T	65W BR30, 75W R30, 75W PAR30, 120W BR40, 150W R40, 150W PAR38
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 120W BR40, 150W R40



Height: 2-11/16" [68mm]
Outside Diameter: 7-1/4" [184mm]



426
White Trim Ring with
Clear Specular Reflector Cone

426MB
White Trim with Specular Black
Reflector Cone

426H
White Trim with Haze Reflector
Cone



426SN
Satin Nickel Trim with
Satin Nickel Reflector Cone

426AC
Antique Copper Trim with
Antique Copper Reflector Cone

426TBZ
Tuscan Bronze Trim with
Tuscan Bronze Reflector Cone



426RG
White Trim with Residential Gold
Reflector Cone

426CG
White Trim with Champagne Gold
Reflector Cone



H930
R/PAR lamp aiming accessory for 310 and 426 trims.
Allows 30° tilt and 358° rotation.


H7T	75W PAR30, 100W R30
H7TNB	
H7RT	50W PAR30, 100W R30

4261

Self Flange White Reflector Cone

- Accepts R and PAR lamps
- Coil Spring retention

H7T	65W BR30, 75W R30, 75W PAR30, 120W BR40, 150W R40, 150W PAR38
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 120W BR40, 150W R40



Height: 2-5/8" [67mm]
Outside Diameter: 7-1/4" [184mm]




4261P
White Self Flanged Reflector Cone

30

- Metal Baffle
- Self-flanged socket supporting trim with torsion spring construction
- Accepts a wide range of lamps
- Makes installation AIR-TITE regardless of housing used

H7T	100W R30, 150W PAR38, 75W PAR30,
H7TNB	75W PAR30L, 85W BR30, 100W A19
H7RT	50W PAR30, 50W PAR30L, 100W R30, 85W BR30, 100W A19, 150W PAR38



Height: 5" [127mm]
Outside Diameter: 7-1/4" [184mm]

Super Trim™ AIR-TITE Baffle



30WAT
White Trim with White Baffle and White Reflector

30WATH
White Trim with White Baffle and Clear Reflector

30PAT
White Trim with Black Baffle and Clear Reflector



30SNAT
Satin Nickel Trim with Satin Nickel Baffle and Reflector

30SCAT
Antique Copper Trim with Antique Copper Baffle and Reflector


30TBZAT
Tuscan Bronze Trim with Tuscan Bronze Baffle and Reflector

Halo AIR-TITE trims are designed to meet restricted airflow requirements. However local code may require a trim gasket regardless of trim design. Where required, use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATTRIM-6PK.

310

- Black or White Phenolic Coilex Baffle with separate metal trim ring
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring
- Coil Spring retention
- 310WG and 310PG models with separate wider metal trim ring hides ceiling irregularities and cut-out errors

H7T	65W BR30, 75W R30, 75W PAR30
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L



310W, P, SN, AC, TBZ
Height: 3" [76mm]
Outside Diameter: 7-1/4" [184mm]

310WG, PG
Height: 3" [76mm]
Outside Diameter: 8" [203mm]

Coilex® Baffle



310W
White Trim with White Coilex Baffle

310P
White Trim with Black Coilex Baffle

310SN
Satin Nickel Trim with Black Coilex Baffle



310AC
Antique Copper Trim with Black Coilex Baffle

310TBZ
Tuscan Bronze Trim with Black Coilex Baffle

310WG
Wide White Trim Ring with White Coilex Baffle



H930
R/PAR lamp aiming accessory for 310 and 426 trims. Allows 30° tilt and 358° rotation.

H7T	75W PAR30, 100W R30
H7TNB	
H7RT	50W PAR30, 100W R30




310PG
Wide White Trim Ring with Black Coilex Baffle

312

- Black or White Phenolic Coilex Baffle with separate metal trim ring
- 312 baffle features smaller lamp opening to conceal interior view of housing when used with PAR lamps
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring
- Coil Spring retention

H7T	65W BR30, 75W R30, 75W PAR30
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L



Height: 2-1/4" [57mm]
Outside Diameter: 7-1/4" [184mm]

Coilex® Baffle



312W
White Trim with White Baffle

312P
White Trim with Black Baffle


410

Coilex® Baffle

- Black or White Phenolic Coilex Baffle with separate trim ring
- For PAR38 and R40 lamps

H7T	150W PAR38, 120W BR40, 150W R40
H7RT	120W BR40, 150W R40

Height: 2-3/4" [70mm]
Outside Diameter: 7-1/4" [184mm]



410W
White Trim with White Baffle
(410WG - White Trim with White Baffle and 8" OD Trim Ring)

410P
White Trim with Black Baffle


353

Metal Baffle

- Metallic Finish Trim Rings and Baffles
- Coil Spring retention

H7T	65W BR30, 75W PAR30, 75W R30
H7RT	

Height: 3" [76mm]
Outside Diameter: 7-1/4" [184mm]



353SN
Satin Nickel Trim with
Satin Nickel Baffle

353AC
Antique Copper Trim with
Antique Copper Baffle


353TBZ
Tuscan Bronze Trim with
Tuscan Bronze Baffle

74

Eyeball - 30° Tilt

- Provides optimum position for PAR30 lamps
- Torsion Spring retention

H7T	75W PAR30
H7RT	
H7TNB	



Aperture: 3-7/8" [98mm]
Outside Diameter: 8" [203mm]




74P
White Trim and Eyeball

76

Adjustable Gimbal

- For use with PAR38 lamps
- Includes adapter for side prong lamp
- 50° tilt with side prong lamp
- 30° tilt with screw base lamp
- Torsion Spring retention

H7T	150W PAR38 Side Prong Lamp recommended
H7RT	
H7TNB	



Outside Diameter: 8" [203mm]




76P
White Trim with Gimbal Ring

77

Adjustable Eyeball - 30° Tilt

- For use with R20 and PAR20 lamps
- Torsion spring retention

H7T	50W R20 50W PAR20
H7RT	
H7TNB	



Aperture: 2-3/4" [70mm]
Outside Diameter: 8" [203mm]




77P
White Trim with White Eyeball

78

EyeBall - 30° Tilt

- Wide Choice of finishes for any decor
- 30° Tilt, 360° rotation
- Torsion spring retention

H7T	65W BR30, 75W R30, 75W PAR30, 75W PAR30L
H7RT	
H7TNB	



Height: 4-1/8" [105mm]
Aperture: 3-15/16" [100mm]
Outside Diameter: 8" [203mm]



78P
White Trim with White Eyeball

78PAT
White Trim with White Eyeball -
AIR-TITE trim

78SN
Satin Nickel Trim with
Satin Nickel Eyeball



78AC
Antique Copper Trim with
Antique Copper Eyeball

78TBZ
Tuscan Bronze Trim with
Tuscan Bronze Eyeball

78B
Satin Brass Trim with Satin Brass
Eyeball

Halo AIR-TITE trims are designed to meet restricted airflow requirements. However local code may require a trim gasket regardless of trim design. Where required, use accessory trim gasket GA-ATRIM. Order separately in a 6 pack: GA-ATRIM-6PK.




78PB
Polished Brass Trim with Polished
Brass Eyeball

90

Double Bubble Adjustable - 60° Tilt

- Provides up to 60° of tilt
- Torsion spring retention

H7T	250W PAR38
H7RT	



Outside Diameter: 8" [203mm]



90P
White Trim and Eyeball

376

Adjustable - 30° Tilt

- Regressed Gimbal with Baffle
- Torsion spring retention

H7T	75W PAR30
H7TNB	
H7RT	50W PAR30



Outside Diameter: 7-1/4" [184mm]




376P
White Trim Ring, Black Baffle

378

Adjustable with Splay - 25° Tilt

- Regressed Gimbal with Splay Trim
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring
- Friction clip on trim

H7T	75W PAR30
H7TNB	
H7RT	



Outside Diameter: 7-1/4" [184mm]



378P
White Trim with White Splay Trim


378
White Trim with Clear Specular Splay Trim

478

Adjustable with Splay - 25° Tilt

- Adjustable Gimbal with Splay Trim
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring
- Friction clip on trim

H7T	90W PAR38
H7TNB	
H7RT	150W PAR38



Outside Diameter: 7-1/4" [184mm]



478P
White Trim with White Splay

478
White Trim with Clear Specular Splay

417

Coilex® Baffle Eyeball - 30° Tilt

- 30° Tilt, 358° rotation

H7T	65W BR30, 75W R30
H7RT	
H7TNB	



Outside Diameter: 8" [203mm]



417W
White Trim and Eyeball with White Coilex Baffle

417P
White Trim and Eyeball with Black Coilex Baffle

417PB
Polished Brass Trim and Eyeball with Black Coilex Baffle

419

Regressed Eyeball with Splay - 25° Tilt

- 25° Tilt, 358° rotation
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring

H7T	75W PAR30
H7RT	
H7TNB	



Outside Diameter: 7-1/4" [184mm]



419P
White Trim and Eyeball with White Splay


419
White Trim and Eyeball with Clear Splay

420

Regressed Eyeball - 30° Tilt

- Regressed eyeball with baffle splay
- Accessories available: TRM6 designer trim rings, OT403 oversize trim ring

H7T	65W BR30, 75W PAR30L, 75W PAR30
H7TNB	
H7RT	65W BR30, 75W PAR30



Height: 3-15/16" [100mm]
Aperture: 4" [102mm]
Outside Diameter: 7-1/4" [184mm]



420W
White Trim with White Eyeball and White Baffle

420P
White Trim with White Eyeball and Black Baffle


420PB
Polished Brass Trim with Polished Brass Eyeball and Black Baffle

70

Albalite Lens

- White Trim, Frosted Glass Albalite Lens
- PS version is wet location listed for use in showers
- Non-conductive, non-corrosive polymer trim ring
- Torsion spring retention

H7T	60W A19
H7RT	



Outside Diameter: 8" [203mm]



70P
White Trim with Frosted Albalite Lens

70PS
White Trim with Frosted Albalite Lens, Wet Location




170

Albalite Lens with Reflector

- White Trim with Frosted Glass Lens
- PS version is wet location listed for use in showers
- Non-conductive, non-corrosive gasketed polymer trim ring
- Torsion spring retention

H7TNB	60W A19
-------	---------



Height: 4" [101mm]
Outside Diameter: 8" [203mm]



170P
White Trim with Frosted Albalite Lens

170PS
White Trim with Frosted Albalite Lens, Wet Location and AIR-TITE listed




71

Drop Opal Lens

- White Trim, Drop Opal glass lens
- PS version is wet location listed for use in showers
- Non-conductive, non-corrosive polymer trim ring
- Torsion spring retention

H7T	60W A19
H7RT	



Outside Diameter: 8" [203mm]



71P
White Trim with Drop Opal Lens

71PS
White Trim with Drop Opal Lens, Wet Location




171

Drop Opal Lens with Reflector

- White Trim with Drop Opal glass lens
- PS version is wet location listed for use in showers
- Non-conductive, non-corrosive gasketed polymer trim ring
- Torsion spring retention

H7TNB	60W A19
-------	---------



Height: 4" [102mm]
Outside Diameter: 8" [203mm]



171P
White Trim with Drop Opal Lens

171PS
White Trim with Drop Opal Lens, Wet Location and AIR-TITE listed




73

Fresnel Lens

- White Trim with glass Fresnel Lens
- PS version is wet location listed for use in showers
- Non-conductive, non-corrosive polymer trim ring
- Torsion spring retention

H7T	60W A19
H7RT	



Outside Diameter: 8" [203mm]



73P
White Trim with Fresnel Lens

73PS
White Trim with Fresnel Lens, Wet Location




173

Fresnel Lens with Reflector

- White Trim with glass Fresnel lens
- PS version is wet location listed for use in showers
- Non-conductive, non-corrosive gasketed polymer trim ring
- Torsion spring retention

H7TNB	60W A19
-------	---------



Height: 4" [102mm]
Outside Diameter: 8" [203mm]



173P
White Trim with Fresnel Lens

173PS
White Trim with Fresnel Lens, Wet Location and AIR-TITE listed




75

- All glass diffuser
- Provides some illumination on the ceiling plane
- Torsion spring retention

H7T	60W A19
H7RT	

Diffuser



Outside Diameter: 7-3/4" [197mm]



75
All Glass Diffuser

172

- Frosted Glass Dome
- Wet location listed for use in showers
- Non-conductive, non-corrosive gasketed polymer trim ring
- Torsion spring retention

H7T	75W PAR30, 100W A19
H7TNB	
H7RT	50W PAR30, 60W A19

Dome Lens with Reflector



172PS
White Trim with Frosted Glass Dome, Wet Location Listed


172SNS
Satin Nickel Trim with Frosted Glass Dome, Wet Location Listed

172ACS
Antique Copper Trim with Frosted Glass Dome, Wet Location Listed



172TBZ
Tuscan Bronze Trim with Frosted Glass Dome, Wet Location Listed

Height: 2-1/8" [54mm]
Outside Diameter: 7-3/4" [197mm]




416

- Regressed glass diffuser
- Baffle splay
- Coil Spring retention

H7T	60W A19
H7RT	

Regressed Diffuser



Aperture: 5-3/4" [146mm]
Outside Diameter: 7-1/4" [184mm]



416W
White Trim and Regressed Diffuser, White Baffle

416P
White Trim and Regressed Diffuser, Black Baffle

300

- Open trim for BR, R, and PAR Lamps
- Torsion spring retention

H7T	65W BR30, 75W PAR30, 75W PAR30L, 75W R30
H7TNB	

Open Trim with Socket Support



300P
White Trim


300SN
Satin Nickel Trim

300AC
Antique Copper Trim



300TBZ
Tuscan Bronze Trim


Aperture: 4" [102mm]
Outside Diameter: 7-1/4" [184mm]



301

- Open trim for BR, R, and PAR Lamps
- Coil spring retention

H7T	65W BR30, 75W R30, 75W PAR30
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L



Outside Diameter: 7-1/4" [184mm]


Open Trim



301P
White Trim

301SN
Satin Nickel Trim

301AC
Antique Copper Trim




301TBZ
Tuscan Bronze Trim

301PB
Polished Brass Trim

401

- Open trim for R Lamps
- Coil spring retention

H7T	120W BR40, 150W R40
H7RT	



Outside Diameter: 8" [203mm]

Open Trim



401P
White Trim


401AL
Satin Aluminum Trim

401PB
Polished Brass Trim

328

- Coil spring retention

H7T	65W BR30, 75W R30, 75W PAR30
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L



Aperture: 3-7/8" [98mm]
Outside Diameter: 7-3/4" [197mm]




328P
White Splay Trim

428

- Coil spring retention

H7T	120W BR40, 150W R40
H7RT	



Outside Diameter: 7-3/4" [197mm]




428P
White Splay Trim

79

- 1-7/8" open pinhole
- Torsion spring retention

H7T	50W R20
-----	---------



Outside Diameter: 8" [203mm]




79P
White Trim

303

Wall Wash

- Coil spring retention

H7T	60W A19
H7RT	



Outside Diameter: 8" [203mm]




303P
White Trim and Scoop

424

Wall Wash / Reflector Downlight

- Designed to spread light on cabinets or wall close to ceiling and provide downlighting on counters

H7T	100W A19
H7RT	



Outside Diameter: 7-1/4" [184mm]




424P
White Trim

425

Wall Wash with Coilex® Baffle and Scoop Reflector

- Designated to spread light close to ceiling
- Coil spring retention

H7T	60W A19
H7RT	



Outside Diameter: 7-1/4" [184mm]



425W
White Trim with White Baffle


425P
White Trim with Black Baffle

430

Wall Wash with Baffle and Full Reflector

- Designed to spread light close to the ceiling to eliminate the "cave effect"
- Torsion spring retention
- AIR-TITE construction

H7T	90W TB19, 100W A19, 100W BT15, 100W MB19
H7TNB	



Height: 5" [127mm]
Outside Diameter: 7-1/4" [184mm]



430W
White Trim with White Baffle

430P
White Trim with Black Baffle




1412

Low Voltage Adjustable Spot - 30° Tilt

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W 12V MR16
H7RT	



Aperture: 1-3/4" [44mm]
Outside Diameter: 7-1/4" [184mm]



1412W
White Trim with White Baffle and Lampholder


1412P
Black Trim with Black Baffle and Lampholder

1416

Low Voltage Specular Reflector - 30° Tilt

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W 12V MR16
H7RT	
H7TNB	



Outside Diameter: 7-1/4" [184mm]




1416C
White Trim with Clear Specular Reflector

1416

Low Voltage Baffle - 30° Tilt

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W 12V MR16
H7RT	
H7TNB	



Outside Diameter: 7-1/4" [184mm]



1416W
White Trim with White Baffle


1416BA
White Trim with Black Baffle

1417

Low Voltage Eyeball with Baffle - 30° Tilt

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W 12V MR16
H7RT	



Outside Diameter: 7-1/4" [184mm]



1417W
White Trim with White Eyeball and White Baffle


1417BA
White Trim with White Eyeball and Black Baffle

1450

Low Voltage Slot Aperture - 30° Tilt

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W 12V MR16
H7RT	



Outside Diameter: 7-1/4" [184mm]




1450P
White Slot Aperture Trim

1475

Low Voltage Adjustable Accent - 30° Tilt

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W PAR36 low voltage
H7RT	
H7TNB	



Outside Diameter: 7-1/4" [184mm]



1475W
White Trim with White Baffle


1475P
White Trim with Black Baffle

1479

Low Voltage Pinhole Trim

- Low Voltage Trim
- Includes 120V transformer for retrofit to H7T and H7RT housings
- Torsion spring retention

H7T	50W 12V MR16
H7RT	



Aperture: 1-7/8" [48mm]
Outside Diameter: 8" [203mm]



1479W
White Trim with White Baffle

1479P
White Trim with Black Baffle