

## DESCRIPTION


Retractable Elbow trim for 12V low voltage 4" H1499 family recessed housings. Elbow tilts 60° and rotates 360°. Die cast elbow and trim ring available in a variety of finishes. Three "cat's paw" springs secure trim in housing.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

- Precision die cast metal trim ring with matching finish retractable elbow.
- For directional accent lighting
- 60° Tilt, 360° rotation
- Friction clip "cat paw" retention
- Clear cover glass included with each trim, for use with non-cover glass MR16 lamps

Housings	Max Lamp Compatibility
H1499TAT H1499RTAT	50W 12V MR16
H1499ICAT H1499TCP	75W 12V MR16
H1499T75	



### Dimensions:

A: 1-3/4" [44mm]  
 H: 1-1/8" [29mm]  
 OD: 5" [129mm]

## ORDERING INFORMATION

SAMPLE NUMBER: 1496WH

Trim	Finish
1496= 4" Retractable Elbow, 60° tilt	WH=White SN=Satin Nickel TBZ=Tuscan Bronze

## HALO HOUSING COMPATIBILITY

Trim #	Style								
1496	Retractable	H995ICAT	H995RICAT						
		H457ICAT1E	H457RICAT1E	H457TATE010	H457RTATE010	H457TCPE010	EL4069xx		
		H99ICAT	E4ICATSB						
		H99TAT	H99RTAT	E4TATSB	E4RTATSB				
		H1499ICAT	H1499TAT	H1499TCP	H1499RTAT	H1499T75			

For use in select other's housings, refer to U.L. classification list at [www.cooperlighting.com](http://www.cooperlighting.com).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.



**1496P**  
White Elbow



**1496SN**  
Satin Nickel Elbow



**1496TBZ**  
Tuscan Bronze Elbow

## 1496

Retractable Elbow  
4" Trim



For use in Halo listed housings.



Select trims are classified for use in others housings. See [www.cooperlighting.com](http://www.cooperlighting.com).