

DESCRIPTION

Adjustable Coilex® baffle trim designed for use with IC or Non-IC AIR-TITE™ 3" Halo small aperture line and low voltage housings. Trim ring is available in multiple finishes to match interior decor. Baffle trim uses MR16 low voltage or GU10 line voltage lamps ideal for accent and task lighting. Trim offers 35° tilt, and 360° orientation within housing.

Catalog #		Type	
Project		Date	
Comments			
Prepared by			

SPECIFICATION FEATURES

Cast aluminum trim ring with machined Coilex® baffle available in Matte White, Black, Satin Nickel, or Tuscan Bronze finishes. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim.)

3003 is designed for use with the following Halo H3 small aperture housings:


- Line Voltage Housing (for 120V GU10 lamps).

H36ICAT	50W	IC Air-Tite Housing
H36TAT	50W	Non-IC Air-Tite Housing
H36RTAT	50W	Non-IC Air-Tite Remodel Housing
- Low Voltage Housing (for 12V MR16 lamps).


H36LVICAT	50W	IC Air-Tite Housing
H36LVTAT	50W	Non-IC Air-Tite Housing
H36LVRTAT	50W	Non-IC Air-Tite Remodel Housing
H36LVTAT277	50W	Non-IC Air-Tite Housing, 120/277V
H36LVRTAT277	50W	Non-IC Air-Tite Remodel Housing, 120/277V
- Line Voltage Housing (for 120V GU10 lamps).

H38ICAT	50W	IC Air-Tite Housing
---------	-----	---------------------
- Low Voltage Housing (for 12V MR16 lamps).

H38LVICAT	50W	IC Air-Tite Housing
-----------	-----	---------------------




Lamp Aperture: 2" [51mm]
 Baffle Diameter: 3" [75mm]
 Ceiling Opening: 3-3/4" [95mm]
 Outside Diameter: 4-1/4" [108mm]



3003WHWB
White with White Baffle



3003WHBB
White with Black Baffle



3003BKBB
Black with Black Baffle



3003SNB
Satin Nickel with Satin Nickel Baffle



3003TBZB
Tuscan Bronze with Tuscan Bronze Baffle

ORDERING INFORMATION

SAMPLE NUMBER: 3003WHBB

Order housing and trims separately.

Trim	Finish
3003= 3" Adjustable Baffle Trim	BKBB =Black with Black Baffle SNBB =Satin Nickel with Black Baffle TBZBB =Tuscan Bronze with Black Baffle WHBB =White with Black Baffle WHWB =White with White Baffle

3003

3" Adjustable Baffle Trim

3" TRIMS