

## DESCRIPTION

Art glass pendants offer the opportunity to add a truly unique touch to lighting needs in both commercial and residential spaces. They can add a pleasant free flowing accent in reception or hospitality areas or they can be used for general lighting with their inviting pools of muted illumination. Small dome 12V pendants use MR16 or T4 lamps. Four styles are available in small and large sizes.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

### A ... Electrical Quick Lock Adapter - Linea

Polycarbonate housing. Attaches electrically and mechanically anywhere along Linea Channel.

### B ... Canopy - Surface Mount

Aluminum canopy with integral 12V transformer. Attaches to standard junction box.

### C ... Shade

Hand crafted art glass. Art Glass Shades may vary in color, pattern and shape due to their handmade nature. Slight imperfections add to their charm. Art Glass Shades are made in the United States of America.

### D ... Finial


Machined brass finial.

### E ... Cord

Field adjustable 6' long 18AWG clear-jacketed cord.

### Labels

ETL Classified.



**LV2DMESML**  
**H2DMESML**

**Art Glass Low Voltage  
Pendant  
Small Dome  
50W MR16/T4**

Linea  
Surface

	<b>DME</b>		<b>4</b>		<b>SML</b>	
<b>Track</b> LV2= Linea Track H2=Low Voltage Surface Mount (includes electronic transformer)	<b>Style</b> DME=Dome	<b>Finial Finish</b> AH=Aluminum Haze BRZ=Bronze (H2 only)	<b>Lamp Type</b> (not included) 4=12V MR16, T4	<b>Adapter/Canopy Finish</b> Blank =Same as Finial BRZ=Bronze (H2 only) P=White MB=Black	<b>Shade Size</b> SML=Small	<b>Shade Colors</b> Blueberry= Blueberry Swirl Butterscotch=Butterscotch Twist Cherries=Cherries Jubilee Coconut=Tahitian Coconut Rocky=Rocky Road Spumoni=Spumoni