

Industrial LED Vaportite

Selection Guide

Metalux

Market focused portfolio with products designed for broad applications

Value - competitive prices with industry leading DLC listings

Performance - market leading performance with connected sensors options delivering value beyond lumens per watt



Metalux's sealed and gasketed products deliver maximum operation and reliability in complex environments where the elements require more than just a standard light fixture.

Click on products to learn more

Good

Better

Best

		APVT	VT2	VT3	VT4S	VT4
APPLICABILITY¹	Canopy	★★	★★	★★		
	Storage	★★★	★★★	★★		
	Parking Garage		★★	★★★		
	Warehouse	★	★★★	★★★	★	★
	Food Processing		★★	★★★	★★	★★
	Manufacturing		★★	★★	★★★	★★★
	Complex Environments		★	★	★★★	★★★
FEATURES / PERFORMANCE	Lumen Range	2,000 - 4,000	2,000 - 22,000	2,000 - 8,000	9,000 - 18,000	9,000 - 30,000
	Efficacy (Max)	132 lm/W	150 lm/W	154 lm/W	165 lm/W	146 lm/W
	Distribution ²	G	G, W	G, W, P	G	G
	Sizes	2', 4'	2', 4', 8'	2', 4'	2'	4'
	Housing	Polycarbonate	Fiberglass/Polyester	Fiberglass/Polyester	Fiberglass	Fiberglass
	Lensing	Polycarbonate	DR Acrylic or Polycarb	DR Acrylic or Polycarb	DR Acrylic or Polycarb	DR Acrylic or Polycarb
	Wet Location	Yes	Yes	Yes	Yes	Yes
	IP Rating	None	IP65	IP65, 66, 67	IP65, 66, 67, 69	IP65, 67
	NSF	None	Yes	Yes	Yes	Yes
	NEMA 4X	None	None	None	Yes	Yes
	Life (@60K hrs)	L70 at 54K	L91	L91	L91	L92
	Ambient Range	-20C to 30C	-40C to 35C	-40C to 50C	-40C to 40C	-40C to 40C
	Emergency	None	Yes	Yes	Yes	Yes
Vandal Resistant	None	Optional	Optional	Optional	Optional	
DLC	Standard	Premium	Premium	Premium	Premium	
INTEGRATED CONTROLS	Basic Occupancy		✓	✓	✓	✓
	Stand Alone Daylight / Occupancy		✓	✓	✓	✓
	WaveLinX					
	LumaWatt Pro ³					

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable
 2. G=General, W=Wide, P=Parking Garage.
 3. Location data for asset tracking.