

Good


Better

Best

Click on products to learn more



300K • 400K • 5000K



		FM CCT	WP	WPLD	LW	CWPLD	WNLED	WSNLED	BCLED
APPLICABILITY <sup>1</sup>	Education	★★	★★	★★	★★★	★★★	★★★	★★	★★
	Office	★	★	★★	★★	★★	★★	★★★	★
	Healthcare	★	★	★	★	★	★	★★	★★
	Retail	★★	★	★	★★	★★	★	★★★	★
	Industrial		★		★	★	★★		
	Residential	★★★	★★★	★★			★	★	
FEATURES / PERFORMANCE	Sizes	9", 11", 15", 19"	2' and 4', 5.1" wide	2', 4'	4', 6.8" wide	4'	2', 4'	2', 4'	2', 4'
	lm/W (Max)	85	114	110	122	115	118	108	120
	Lum (Max)	2,400	3,400	4,700	4,617	5,000	5,000	6,500	4,800
	Life (@60K)	L70/50K	L70/50K	L70/50K	L82	L70/50K	L88	L87	L82
	Lens	Frost / Acrylic	Prismatic Acrylic	Clear, Poly	White Ribbed Acrylic	Frost, Poly	Frost, Acrylic	Frost + Film, Acrylic	Frost, Smooth
	Emergency	No	No	No	Integrated	No	Integrated	Integrated	Integrated
	CRI	80+	80+	80/90	80+	80+	80+	80+	80+
	Row Mount	NA	N/A	No	Yes	Yes	Yes	Yes	Yes
	DLC	Energy Star	Standard	Standard	DLC, Title 24 Non-Res	Standard	Standard	Standard	None
INTEGRATED CONTROLS	Basic Occupancy								
	Stand Alone Daylight / Occupancy								
	LumaWatt Pro								

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable