











Type "G" Fixture																													
<p><b>(Exposed Grid)</b></p>  <p>G Grid Lay In (Standard)</p> <p><b>Integral Grid-Lock Feature (Standard)</b></p>	<p><b>A Recessed Luminaire with Narrow Flanges designed to rest on exposed 15/16" or 9/16" wide Inverted Grid Tees.</b></p> <ul style="list-style-type: none"> <li>• Fixture Example: 2GR8-432-UNV-EB81-U</li> </ul>																												
<p><b>(Concealed T)</b></p>  <p>G Concealed T</p>	<p><b>A Recessed Luminaire with Narrow Flanges designed to rest on 15/16" wide Concealed Inverted Grid Tees</b></p> <ul style="list-style-type: none"> <li>• Fixture Example 2EP3GAX-332S36I</li> <li>• Optional Aluminum TK Trim Kit Available                             <ul style="list-style-type: none"> <li>– Available TK Trim Finishes: Natural Anodized Aluminum (N) Standard and Baked White Enamel (W)</li> </ul> </li> </ul> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: center;">TK TRIM KIT</th> </tr> </thead> <tbody> <tr> <td>TK-14N-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>TK-22N-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>TK-24N-U</td> <td style="text-align: center;">2' x 4'</td> </tr> </tbody> </table>	TK TRIM KIT		TK-14N-U	1' x 4'	TK-22N-U	2' x 2'	TK-24N-U	2' x 4'																				
TK TRIM KIT																													
TK-14N-U	1' x 4'																												
TK-22N-U	2' x 2'																												
TK-24N-U	2' x 4'																												
<p><b>(Slot Grid)</b></p>  <p>G Slot Grid</p>	<p><b>A Recessed Luminaire designed to rest on 9/16" Slot T Grid</b></p> <ul style="list-style-type: none"> <li>• Fixture Example: 2GR8-432</li> <li>• T-Bar Safety Clips Required</li> </ul>																												
Type "F" Fixture																													
<p><b>(Flange Trim)</b></p>  <p>F Flange Trim</p>	<p>For factory installed flange, replace "G" in fixture trim description with "F". Factory installed flange available on GC8 and GC only, field installed kits are available for all other models and are listed below.</p> <p><b>A Recessed Luminaire with Horizontal Steel or Aluminum (A) Flanges which conceal the edges of the ceiling opening</b></p> <ul style="list-style-type: none"> <li>• Fixture example 2FC8-332</li> <li>• Adjustable Swing Gates for mounting</li> <li>• Optional Flange Kit available                             <ul style="list-style-type: none"> <li>– Field Convertible, Converts Grid Fixture (G) to Flange Fixture (F)</li> <li>– Standard Flange Trim Finish: Baked White Enamel (W)</li> </ul> </li> <li>• Typical fixture ceiling opening requirements: <b>Single</b> – (Width) One-quarter Inch (1/4") plus nominal width, (Length) 1/4" plus nominal length.</li> <li>• <b>Rows</b> - fixture quantity times fixture length plus 1/4".</li> <li>• Plaster Frames available, see options and accessories section</li> </ul> <p><b>FLANGE KITS (Field Installed)</b></p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="background-color: #0070C0; color: white;">Fixture</th> <th style="background-color: #0070C0; color: white;">Fixture Size</th> <th style="background-color: #0070C0; color: white;">Flange Kit</th> <th style="background-color: #0070C0; color: white;">Ceiling Opening Size</th> </tr> </thead> <tbody> <tr> <td>GR8/GC8/GR5</td> <td style="text-align: center;">1' x 4'</td> <td>FCS-14W-U (Steel)</td> <td style="text-align: center;">12-1/4" x 48-1/4"</td> </tr> <tr> <td>GC</td> <td style="text-align: center;">1' x 4'</td> <td>F2-14W-U (Steel)</td> <td style="text-align: center;">12-1/4" x 48-1/4"</td> </tr> <tr> <td>GC</td> <td style="text-align: center;">20" x 24"</td> <td>F2-2024W-U (Steel)</td> <td style="text-align: center;">20-1/4" x 24-1/4"</td> </tr> <tr> <td>GR8/GC8/GR5</td> <td style="text-align: center;">2' x 2'</td> <td>FCTKA-22W-U</td> <td style="text-align: center;">24-1/4" x 24-1/4"</td> </tr> <tr> <td>GC</td> <td style="text-align: center;">20" x 48"</td> <td>F2-28W-U (Steel)</td> <td style="text-align: center;">20-1/4" x 48-1/4"</td> </tr> <tr> <td>GR8/GC8/GR5</td> <td style="text-align: center;">2' x 4'</td> <td>FCTKA-24W-U</td> <td style="text-align: center;">24-1/4" x 48-1/4"</td> </tr> </tbody> </table>	Fixture	Fixture Size	Flange Kit	Ceiling Opening Size	GR8/GC8/GR5	1' x 4'	FCS-14W-U (Steel)	12-1/4" x 48-1/4"	GC	1' x 4'	F2-14W-U (Steel)	12-1/4" x 48-1/4"	GC	20" x 24"	F2-2024W-U (Steel)	20-1/4" x 24-1/4"	GR8/GC8/GR5	2' x 2'	FCTKA-22W-U	24-1/4" x 24-1/4"	GC	20" x 48"	F2-28W-U (Steel)	20-1/4" x 48-1/4"	GR8/GC8/GR5	2' x 4'	FCTKA-24W-U	24-1/4" x 48-1/4"
Fixture	Fixture Size	Flange Kit	Ceiling Opening Size																										
GR8/GC8/GR5	1' x 4'	FCS-14W-U (Steel)	12-1/4" x 48-1/4"																										
GC	1' x 4'	F2-14W-U (Steel)	12-1/4" x 48-1/4"																										
GC	20" x 24"	F2-2024W-U (Steel)	20-1/4" x 24-1/4"																										
GR8/GC8/GR5	2' x 2'	FCTKA-22W-U	24-1/4" x 24-1/4"																										
GC	20" x 48"	F2-28W-U (Steel)	20-1/4" x 48-1/4"																										
GR8/GC8/GR5	2' x 4'	FCTKA-24W-U	24-1/4" x 48-1/4"																										
Type "MZ" Fixture (GC Only)																													
<p><b>(Modular Trim / Aluminum)</b></p>  <p><b>MZ Modular Trim / Aluminum</b></p> <p><b>Concealed "T" Metal Pan and Concealed "Z" Spline Application</b></p>	<p><b>A Recessed Luminaire Trimmed to a Modular / Concealed Finished Dimension</b></p> <ul style="list-style-type: none"> <li>• Fixture example: 2MZC-332 (complete fixture / factory installed trim)</li> <li>• On complete ordered fixture, Modular MZ Trim matches door frame assembly unless otherwise specified</li> <li>• Adjustable Swing Gates for mounting</li> <li>• Optional Aluminum Modular (MZ) Trim Kit available                             <ul style="list-style-type: none"> <li>– Field Convertible, converts Grid Fixture (G) to Modular Fixture (MZ)</li> <li>– Available Aluminum Trim Finishes: Baked White Enamel (W) and Natural Anodized Aluminum (N)</li> </ul> </li> <li>• For Concealed "T" and Concealed "Z" the main ceiling carries must be on the sides of the Luminaire. The weight of the Luminaire exists on the Swing-Gates and must be supported by main carriers, not cross members. At each end of the luminaire, an Angle Spline must be used, Cross or Main T's cannot be used.</li> </ul> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: center;">MODULAR / MZ TRIM KIT / ALUMINUM</th> </tr> </thead> <tbody> <tr> <td>F2MZ/E-14W-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>F2MZ/E-22W-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>F2MZ/E-24W-U</td> <td style="text-align: center;">2' x 4'</td> </tr> <tr> <td>F2MZ/E-28W-U</td> <td style="text-align: center;">20" x 48"</td> </tr> </tbody> </table>	MODULAR / MZ TRIM KIT / ALUMINUM		F2MZ/E-14W-U	1' x 4'	F2MZ/E-22W-U	2' x 2'	F2MZ/E-24W-U	2' x 4'	F2MZ/E-28W-U	20" x 48"																		
MODULAR / MZ TRIM KIT / ALUMINUM																													
F2MZ/E-14W-U	1' x 4'																												
F2MZ/E-22W-U	2' x 2'																												
F2MZ/E-24W-U	2' x 4'																												
F2MZ/E-28W-U	20" x 48"																												

Type "G" Fixture																																																	
<p><b>(Exposed Grid)</b></p>  <p>G Grid Lay In (Standard)</p> <p>Integral Grid-Lock Feature (Standard)</p>	<p><b>A Recessed Luminaire with Narrow Flanges designed to rest on exposed 15/16" or 9/16" wide Inverted Grid Tees.</b></p> <ul style="list-style-type: none"> <li>• Fixture example: 2P2GX-332S36l</li> </ul>																																																
<p><b>(Concealed T)</b></p>  <p>T Concealed T</p>	<p><b>A Recessed Luminaire with Narrow Flanges designed to rest on 15/16" wide Concealed Inverted Grid Tees</b></p> <ul style="list-style-type: none"> <li>• Fixture Example 2EP3GX-332S36l</li> <li>• Optional TK Trim Kit available                             <ul style="list-style-type: none"> <li>– Available TK trim finishes: Natural Anodized Aluminum (N) standard and Baked White Enamel (W)</li> </ul> </li> </ul> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: center;">TK TRIM KIT</th> </tr> </thead> <tbody> <tr> <td>TK-14N-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>TK-22N-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>TK-24N-U</td> <td style="text-align: center;">2' x 4'</td> </tr> </tbody> </table>	TK TRIM KIT		TK-14N-U	1' x 4'	TK-22N-U	2' x 2'	TK-24N-U	2' x 4'																																								
TK TRIM KIT																																																	
TK-14N-U	1' x 4'																																																
TK-22N-U	2' x 2'																																																
TK-24N-U	2' x 4'																																																
<p><b>(Slot Grid)</b></p>  <p>G Slot Grid</p>	<p><b>A Recessed Luminaire designed to rest on 9/16" Slot-T Grid</b></p> <ul style="list-style-type: none"> <li>• Fixture example: 2EP3GAX-332S36l</li> <li>• T-Bar Safety Clips required</li> <li>• Face of luminaire/door assembly is recessed about 5/16" into ceiling</li> </ul>																																																
Type "F" Fixture																																																	
<p><b>(Flange)</b></p>  <p>F Aluminum Flange Trim with Supporting Swing Gates</p>	<p><b>A Recessed Luminaire with Horizontal Steel or Mitered Aluminum (M) Flanges which conceal the edges of the ceiling opening</b></p> <ul style="list-style-type: none"> <li>• Complete fixture / factory installed trim. Fixture example: 2EP3FX-332S36l</li> <li>• Adjustable Swing Gates for mounting</li> <li>• Field installed Flange Kit available                             <ul style="list-style-type: none"> <li>– Field Convertible, Converts Grid Fixture (G) to Flange Fixture (F)</li> <li>– Standard Flange Trim finish: Baked White Enamel (W)</li> </ul> </li> <li>• Typical fixture ceiling opening requirements: <b>Single</b> – (Width) One-quarter Inch (1/4") plus nominal width, (length) 1/4" plus nominal length.</li> <li>• <b>Rows</b> - fixture quantity times fixture length plus 1/4".</li> <li>• Plaster frames available, see options and accessories section</li> </ul> <p style="text-align: center;"><b>FLANGE KITS (Steel) (Field Installed)</b></p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Fixture</th> <th>Fixture Size</th> <th>Flange Kit</th> <th>Ceiling Opening Size</th> </tr> </thead> <tbody> <tr> <td>EP3, P4, P5</td> <td style="text-align: center;">1' x 2'</td> <td style="text-align: center;">F3/4-12W-U (steel)</td> <td style="text-align: center;">12-1/4" x 24-1/4"</td> </tr> <tr> <td>EP3, P4, P5</td> <td style="text-align: center;">1' x 4'</td> <td style="text-align: center;">F3/4M-14W-U</td> <td style="text-align: center;">12-1/4" x 48-1/4"</td> </tr> <tr> <td>P2</td> <td style="text-align: center;">1' x 4'</td> <td style="text-align: center;">F2M-14S-W-U</td> <td style="text-align: center;">12-1/4" x 48-1/4"</td> </tr> <tr> <td>EP3, P4, P5</td> <td style="text-align: center;">20" x 24"</td> <td style="text-align: center;">F3/4-2024W-U (steel)</td> <td style="text-align: center;">20-1/4" x 24-1/4"</td> </tr> <tr> <td>P2</td> <td style="text-align: center;">20" x 24"</td> <td style="text-align: center;">F2-2024W-U (steel)</td> <td style="text-align: center;">20-1/4" x 24-1/4"</td> </tr> <tr> <td>P4, P5</td> <td style="text-align: center;">2' x 2'</td> <td style="text-align: center;">F4/5M-22S-W-U</td> <td style="text-align: center;">24-1/4" x 24-1/4"</td> </tr> <tr> <td>P2, EP3</td> <td style="text-align: center;">2' x 2'</td> <td style="text-align: center;">F2/3M-22S-W-U</td> <td style="text-align: center;">24-1/4" x 24-1/4"</td> </tr> <tr> <td>EP3, P4, P5</td> <td style="text-align: center;">20" x 48"</td> <td style="text-align: center;">F3/4-28W-U (steel)</td> <td style="text-align: center;">20-1/4" x 48-1/4"</td> </tr> <tr> <td>P2</td> <td style="text-align: center;">20" x 48"</td> <td style="text-align: center;">F2-28W-U (steel)</td> <td style="text-align: center;">20-1/4" x 48-1/4"</td> </tr> <tr> <td>P4, P5</td> <td style="text-align: center;">2' x 4'</td> <td style="text-align: center;">F4/5M-24S-W-U</td> <td style="text-align: center;">24-1/4" x 48-1/4"</td> </tr> <tr> <td>P2, EP3</td> <td style="text-align: center;">2' x 4'</td> <td style="text-align: center;">F2/3M-24S-W-U</td> <td style="text-align: center;">24-1/4" x 48-1/4"</td> </tr> </tbody> </table>	Fixture	Fixture Size	Flange Kit	Ceiling Opening Size	EP3, P4, P5	1' x 2'	F3/4-12W-U (steel)	12-1/4" x 24-1/4"	EP3, P4, P5	1' x 4'	F3/4M-14W-U	12-1/4" x 48-1/4"	P2	1' x 4'	F2M-14S-W-U	12-1/4" x 48-1/4"	EP3, P4, P5	20" x 24"	F3/4-2024W-U (steel)	20-1/4" x 24-1/4"	P2	20" x 24"	F2-2024W-U (steel)	20-1/4" x 24-1/4"	P4, P5	2' x 2'	F4/5M-22S-W-U	24-1/4" x 24-1/4"	P2, EP3	2' x 2'	F2/3M-22S-W-U	24-1/4" x 24-1/4"	EP3, P4, P5	20" x 48"	F3/4-28W-U (steel)	20-1/4" x 48-1/4"	P2	20" x 48"	F2-28W-U (steel)	20-1/4" x 48-1/4"	P4, P5	2' x 4'	F4/5M-24S-W-U	24-1/4" x 48-1/4"	P2, EP3	2' x 4'	F2/3M-24S-W-U	24-1/4" x 48-1/4"
Fixture	Fixture Size	Flange Kit	Ceiling Opening Size																																														
EP3, P4, P5	1' x 2'	F3/4-12W-U (steel)	12-1/4" x 24-1/4"																																														
EP3, P4, P5	1' x 4'	F3/4M-14W-U	12-1/4" x 48-1/4"																																														
P2	1' x 4'	F2M-14S-W-U	12-1/4" x 48-1/4"																																														
EP3, P4, P5	20" x 24"	F3/4-2024W-U (steel)	20-1/4" x 24-1/4"																																														
P2	20" x 24"	F2-2024W-U (steel)	20-1/4" x 24-1/4"																																														
P4, P5	2' x 2'	F4/5M-22S-W-U	24-1/4" x 24-1/4"																																														
P2, EP3	2' x 2'	F2/3M-22S-W-U	24-1/4" x 24-1/4"																																														
EP3, P4, P5	20" x 48"	F3/4-28W-U (steel)	20-1/4" x 48-1/4"																																														
P2	20" x 48"	F2-28W-U (steel)	20-1/4" x 48-1/4"																																														
P4, P5	2' x 4'	F4/5M-24S-W-U	24-1/4" x 48-1/4"																																														
P2, EP3	2' x 4'	F2/3M-24S-W-U	24-1/4" x 48-1/4"																																														
Type "MZ" (Fixture) 2", 3", 4", 5" Parabolics																																																	
<p><b>(Modular Trim / Aluminum)</b></p>  <p>MZ Modular Trim with Supporting Swing Gates</p> <p><b>Concealed "T" Metal Pan and Concealed "Z" Spline Application</b></p>	<p><b>A Recessed Luminaire trimmed to a Modular / Concealed finished dimension</b></p> <ul style="list-style-type: none"> <li>• Complete fixture / factory installed trim. Fixture example: 2MZC-332S38l</li> <li>• On complete ordered fixture, Modular MZ Trim matches door frame assembly unless otherwise specified</li> <li>• Adjustable Swing Gates for mounting</li> <li>• Optional Aluminum Modular (MZ) Trim Kit available                             <ul style="list-style-type: none"> <li>– Field Convertible, Converts Grid Fixture (G) to Modular Fixture (MZ)</li> <li>– Available Aluminum Trim Finishes: Baked White Enamel (W) and Natural Anodized Aluminum (N)</li> </ul> </li> <li>• For Concealed "T" and Concealed "Z" the main ceiling carries must be on the sides of the Luminaire. The weight of the luminaire exists on the Swing-Gates and must be supported by main carriers, not cross members. At each end of the luminaire, an Angle Spline must be used, Cross or Main T's cannot be used.</li> </ul> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="3" style="text-align: center;">MODULAR / MZ TRIM KIT / ALUMINUM</th> </tr> <tr> <th>Fixture</th> <th>Flange Kit</th> <th>Fixture Size</th> </tr> </thead> <tbody> <tr> <td>EP3, P4, P5</td> <td style="text-align: center;">F3/4MZ-14W-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>P2</td> <td style="text-align: center;">F2MZ-14-W-U</td> <td style="text-align: center;">1' x 4'</td> </tr> <tr> <td>P4, P5</td> <td style="text-align: center;">F4/5MZ/E-22W-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>EP3, P2</td> <td style="text-align: center;">F2/3MZ/E-22W-U</td> <td style="text-align: center;">2' x 2'</td> </tr> <tr> <td>P4, P5</td> <td style="text-align: center;">F4/5MZ/E-24W-U</td> <td style="text-align: center;">2' x 4'</td> </tr> <tr> <td>EP3, P2</td> <td style="text-align: center;">F2/3MZ/E-24W-U</td> <td style="text-align: center;">2' x 4'</td> </tr> </tbody> </table>	MODULAR / MZ TRIM KIT / ALUMINUM			Fixture	Flange Kit	Fixture Size	EP3, P4, P5	F3/4MZ-14W-U	1' x 4'	P2	F2MZ-14-W-U	1' x 4'	P4, P5	F4/5MZ/E-22W-U	2' x 2'	EP3, P2	F2/3MZ/E-22W-U	2' x 2'	P4, P5	F4/5MZ/E-24W-U	2' x 4'	EP3, P2	F2/3MZ/E-24W-U	2' x 4'																								
MODULAR / MZ TRIM KIT / ALUMINUM																																																	
Fixture	Flange Kit	Fixture Size																																															
EP3, P4, P5	F3/4MZ-14W-U	1' x 4'																																															
P2	F2MZ-14-W-U	1' x 4'																																															
P4, P5	F4/5MZ/E-22W-U	2' x 2'																																															
EP3, P2	F2/3MZ/E-22W-U	2' x 2'																																															
P4, P5	F4/5MZ/E-24W-U	2' x 4'																																															
EP3, P2	F2/3MZ/E-24W-U	2' x 4'																																															

## DRYWALL FRAMING KIT (DF) SERIES



### FEATURES

- Individual modular frame unit
- Nominal 1-1/2" frame depth
- Side and end rails of extruded aluminum
- Offset toleranced corner fasteners
- Painted after fabrication
- Available in satin anodized or baked white enamel finish
- Individual row mount with center mullion support (DFR Series)
- Uninterrupted continuous row (DFC Series). Available for RCC fixtures only
- DF, DFC and DFR Series add 3/16" to nominal width of fixture used. Add 1/4" to nominal length of each fixture used for DF and DFR, add 1/4" to total length of all fixtures for DFC.

## DF SERIES


### Description

The **DF Drywall Frame Kit Series** features a modular framing unit that will trim out an opening in a drywall ceiling. This opening will resemble a modular grid ceiling when installed. The kits are field assembled and installed into the drywall ceiling independent of the luminaire. The Drywall Frame Kit enables the contractor or end user to frame out a modular opening and install a choice of any standard modular recessed luminaire. The ease of installation feature makes the Framing Kit a good choice for the commercial, residential and architectural market.

The **DF Series** is available in all popular modular sizes to fit any lay-in fixture to include: 1' x 2', 2' x 4', 2' x 2', 1' x 4', 1' x 8', 20" x 24", 20" x 48", 10" x 2' and 10" x 4'.

The **DFR Series** is a modular framing unit for row mounting luminaires with a center mullion support for trimming out an opening in drywall ceilings. The DFR Series is available in all popular modular sizes to fit any lay-in fixture to include: 1' x 2', 2' x 4', 2' x 2', 1' x 4', 1' x 8', 20" x 24", 20" x 48", 10" x 2' and 10" x 4'.

The **DFC Series** is a continuous row uninterrupted modular framing unit with no Cross T supports. It is used for trimming out an opening in drywall ceilings to install continuous row luminaires. The DFC Series is available in Twelve Inch (12") widths. For continuous row RCC luminaires only.




### ORDERING INFORMATION

SAMPLE NUMBER: DF-102-W


<b>Series</b> <b>DF</b> =Framing Kit <b>DFR</b> =Framing Kit Support/Center Mullion <b>DFC</b> =Framing Kit Continuous <sup>1</sup>	<b>Application (Leave Blank For DF Series)</b> <b>E</b> =End of Row <b>R</b> =Middle of Row	<b>Width</b> <b>10</b> =Ten Inch (10") (Not Available on DFC Series) <b>1</b> =One Foot (1') <b>20</b> =Twenty Inches (20") (Not Available on DFC Series) <b>2</b> =Two Feet (2') (Not Available on DFC Series) <b>4</b> =Four Feet (4') (Not Available on DFC Series)	<b>Length</b> <b>2</b> =Two Feet (2' Nominal) <b>4</b> =Four Feet (4' Nominal) <b>6</b> =Six Feet (6' Nominal) <b>8</b> =Eight Feet (8' Nominal)	<b>Finish</b> <b>N</b> =Satin Anodized Aluminum <b>W</b> =Baked White Enamel
--	---	---	--	--

### PRODUCT INFORMATION


Catalog Number	Nominal Luminaire Size (Inches)	Ceiling Opening Size (Inches) (Width x Length)
DF-12-W	1' x 2'	12-3/16" x 24-1/4"
DF-14-W	1' x 4'	12-3/16" x 48-1/4"
DF-18-W <sup>2</sup>	1' x 8'	12-3/16" x 96-1/4"
DF-22-W	2' x 2'	24-3/16" x 24-1/4"
DF-24-W	2' x 4'	24-3/16" x 48-1/4"
DF-2024-W	20" x 24"	20-3/16" x 24-1/4"
DF-2048-W	20" x 48"	20-3/16" x 48-1/4"
DF-102-W <sup>3</sup>	10" x 2'	10-3/16" x 24-1/4"
DF-104-W <sup>3</sup>	10" x 4'	10-3/16" x 48-1/4"
DFR-12-W	1' x 2'	12-3/16" + 1/4" added to <b>each</b> fixture length
DFR-14-W	1' x 4'	12-3/16" + 1/4" added to <b>each</b> fixture length
DFR-18-W <sup>2</sup>	1' x 8'	12-3/16" + 1/4" added to <b>each</b> fixture length
DFR-22-W	2' x 2'	24-3/16" + 1/4" added to <b>each</b> fixture length
DFR-24-W	2' x 4'	24-3/16" + 1/4" added to <b>each</b> fixture length
DFR-2024-W	20" x 24"	20-3/16" + 1/4" added to <b>each</b> fixture length
DFR-2048-W	20" x 48"	20-3/16" + 1/4" added to <b>each</b> fixture length
DFR-102-W <sup>3</sup>	10" x 2'	10-3/16" + 1/4" added to <b>each</b> fixture length
DFR-104-W <sup>3</sup>	10" x 4'	10-3/16" + 1/4" added to <b>each</b> fixture length
DFC-12-W	1' x 2'	12-3/16" + 1/4" added to <b>total</b> fixture length
DFC-14-W	1' x 4'	12-3/16" + 1/4" added to <b>total</b> fixture length
DFC-18-W <sup>1</sup>	1' x 8'	12-3/16" + 1/4" added to <b>total</b> fixture length



DF Series



DFR Series



DFC Series

NOTES: 1. For use with RCC fixtures only. 2. For use with RCG fixtures only. 3. For use with RWW fixtures only.