

## DESCRIPTION

The 147 series is a decorative pendant family with a square cylindrical form. This product has a tall square cylindrical shade with a variety of options. The integral LED light engine is available in 2700K, 3000K, 3500K, 4000K color temperatures that evenly illuminates the shades and bottom lens with 83+ CRI. The stem, canopy, and finial finishes are available in many painted options. Shaper's Fabrique collection is known for its high quality hand tucked fabrics. Shades come in 2 standard sizes, 11 standard fabrics, 3 vinyl materials, and 4 printed woods patterns as well as the option to add 1 of 2 translucent organza outer shade fabrics. This series also comes with the option for a 3 or 4 pendant cluster.

## SPECIFICATION FEATURES

### Materials

Aluminum housing, cold rolled steel cover and bracket extensions with LED boards attached. Matte white acrylic bottom diffuser with one finial, standard. Optional matte white acrylic top cover available (TC).

5" diameter canopy with self aligning swivel. Stem is 1/2" aluminum tubing with threaded rod. Air craft cable option is 3/64" cable. Slope adapter option available (SCA-XX - 18°- 45°, but slope dimension must be provided).

28" H x 10" L x 10" W

Standard Length=

40" OAH (Overall Height)

| Min     | Max     |
|---------|---------|
| 32" OAH | 96" OAH |

40" H x 10" L x 10" W

Standard Length=

54" OAH (Overall Height)

| Min     | Max     |
|---------|---------|
| 44" OAH | 96" OAH |

### Stem Options

|                   |        |
|-------------------|--------|
| Single Rigid Stem | -P1S   |
| Air Craft Cable   | -P1SAC |
| 3 Stem Cluster    | -3FCL  |
| 4 Stem Cluster    | -4FCL  |

Consult factory for non standard lengths under 18" and over 96".

### Painted Finishes

ALP (Aluminum Paint)  
 BM (Bronze Metallic)  
 DP (Dark Platinum)  
 GRM (Graphite Metallic)  
 MB (Matte Black)  
 MW (Matte White)  
 CC (Custom Color – Specify)  
 For Custom Color contact factory for quotation.

### Shades

Aluminum wire frame painted white. Material backed on to heavy translucent white styrene. All shades have "Hand-Tucked Rolled Edges" except for Vinyl. Shade in Shade offers 2 material selections, overlapping each other.

### Fabric Shade Selections

SIW - Silk White  
 SIY - Silk Ivory  
 SWH - Shantung White  
 SEG - Shantung Eggshell  
 SBG - Shantung Beige  
 LAT - Linen Alabaster  
 LCK - Linen Chopstick  
 NGS - Silk Glow  
 GBB - Glynn Brussels Beige  
 LOLA - Lola Sand  
 VLW - Verona Linen White

### Vinyl Coated Fabric

ABR - Alabaster Vinyl  
 NFX - Natural Flax  
 GHY - Golden Honey

### Printed Wood

PVDB - Varigated Bamboo  
 PMA - Maple  
 PCH - Cherry  
 PWA - Walnut

**Note:** For humid environments, such as showers or open

|             |  |      |
|-------------|--|------|
| Catalog #   |  | Type |
| Project     |  |      |
| Comments    |  | Date |
| Prepared by |  |      |

lobbies, Vinyl Coated Fabrics are recommended.

### LEDs

LEDs are offered in four color temperatures: 2700K, 3000K, 3500K, and 4000K CCTs at 80+ CRI. Rated LED Life: 50,000 hrs.

### Electrical

Standard driver is electronic universal voltage (120-277V, 50/60 Hz), greater than 0.9 power factor, less than 20% harmonic distortion, and ambient temperatures of 25°C (77°F).

### Control

Standard driver is 0-10V with 10% dimming.

### Compliance

Components are UL recognized and luminaires are cUL listed for 25° environments. Fixtures are rated for damp location listing. Made in North America. All LED components are RoHS compliant and drivers conform to appropriate FCC regulations. Sconce products meet ADA regulations.

### Certifications

All Fabrique Collection products are UL and cUL approved for interior damp locations. All LED components in the Fabrique Collection are RoHS compliant and drivers conform to appropriate FCC regulations.

### Life and Warranty

Standard five-year warranty on all parts.



## 147 SERIES

### Height: 28"

- Delivered Lumens (@3500K): 1959
- Wattage: 19W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

### Diameter: 40"

- Delivered Lumens (@3500K): 2790
- Wattage: 28W
- CRI: 83+
- CCT: 2700K, 3000K, 3500K, 4000K
- Rated Life of Lamp (hrs): 50,000
- Dimming: 0-10V

## ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Fixture Number: 147-28-P1S-L3/827-UNV-ALP-40

Shade Number: 147-28-SHD-SWH

| Series <sup>1</sup>                        | Shade Height         | Mounting Type  | Lamp   | LED Voltage   | Finish   | Options <sup>2</sup>   | Overall Height (OAH)  |
|--|----------------------|--|--|---------------|--|--|---|
| 147 = Square Cylinder Pendant <sup>1</sup> | 28 = 28"<br>40 = 40" | P1S = Single Stem<br>P1SAC = Single Stem with Aircraft Cable<br>3FCL = 3 Stem Cluster<br>4FCL = 4 Stem Cluster | 28"<br>L3/827<br>L3/830<br>L3/835<br>L3/840<br><br>40"<br>L4/827<br>L4/830<br>L4/835<br>L4/840 | UNV (120-277) | MW = Matte White<br>MB = Matte Black<br>BM = Bronze Metallic<br>DP = Dark Platinum<br>ALP = Aluminum Paint<br>GRM = Graphite Metallic<br>CC = Custom Color specify | SCA = Sloped ceiling adapter 18°-45°<br>TC = Matte White Acrylic Top Cover | 40 = 40" OAH (28" shade height)<br>54 = 54" OAH (40" shade height)<br>XX = Custom length must be specified (147-28 = 32" - 96"<br>147-40 = 44" - 96")<br>See "Dimensions" section for Overall Height per fixture length per cluster type. |

Notes: <sup>1</sup> Fabric shade not included. Please specify fabric shade from selections provided to complete fixture order. <sup>2</sup> Sloped ceiling adapter can accommodate up to 18-45 degree slope. Slope dimension must be provided. <sup>3</sup> Shade in Shade option for Fabric selections only.


ORDERING INFORMATION (SELECT FIXTURE AND FABRIC KIT TO COMPLETE SPECIFICATION)

Shade Number: 147-28-SHD-SWH

| Series                           | Size                 | SHD         | Finish  |   |  | Options  |
|----------------------------------|----------------------|-------------|---|---|--|--|
| 147 = Rectangular Cylinder Shade | 28 = 28"<br>40 = 40" | SHD = Shade | <b>Fabric:</b><br>SIW = Silk White<br>SIY = Silk Ivory<br>SWH = Shantung White<br>SEG = Shantung Eggshell<br>SBG = Shantung Beige<br>LAT = Linen Alabaster<br>LCK = Linen Chopstick | NGS = Silk Glow<br>GBB = Glynn Brussels Beige<br>LOLA = Lola Sand | <b>Printed Wood:</b><br>PVDB = Varigated Bamboo<br>PMA = Maple<br>PCH = Cherry<br>PWA = Walnut<br><b>Vinyl Coated Fabric:</b><br>ABR = Alabaster Vinyl<br>NFX = Natural Flax<br>GHY = Golden Honey | <b>Organza Outer Shade</b><br>TSQISIS-EDT = Top Square-in Shade, Earth Dust<br>TSQISIS-WMT = Top Square-in Shade, White Mist |

OPTIONS


MOUNTING TYPES - SINGLE PENDANT




147-P-TC  
(TOP COVER)




147-P-SCA  
(SLOPED CEILING ADAPTOR)



147-28-P1S  
(SINGLE STEM)




147-40-P1S  
(SINGLE STEM)




147-P  
(PLAN VIEW)


MOUNTING - SINGLE PENDANT - SHADE IN SHADE



147-28-P1S-TSQISIS  
(TOP SQUARE SHADE-IN-SHADE)






147-40-P1S-TSQISIS  
(TOP SQUARE SHADE-IN-SHADE)



147-P-TSQISIS  
(PLAN VIEW)

**DIMENSIONS - 3 CLUSTER PENDANT**



**DIMENSIONS - 4 CLUSTER PENDANT**

