

LXF/LXT Lexington LED AF24

Decorative post top luminaire


Streetworks

Discrete LED solution. Energy conscious illumination.

The Lexington AF24 LED outdoor luminaire displays the old-fashioned charm of traditional lantern-type post top lighting, enhancing any setting with distinctive styling. As a decorative luminaire, the Lexington LED tastefully complements the architectural and environmental design of parks and roadways. It's patented AccuLED Optics™ technology delivers uniform and efficient illumination to pedestrian and roadway applications.

Key features:

- Up to 120 lumens per watt
- Five optical distributions (T2U, T3, SL3, T4W and 5WQ), that are precisely designed to shape the distribution, maximizing efficiency and fixture spacing
- Choice of 9 lumen packages ranging from 2,000 - 9,000 delivered lumens
- 4000K CCT standard with minimum 70 CRI, optional 3000K 70 CRI and 2700K CCT at 80 CRI



Quick facts:

- Replaces up to 400W equivalent HID
- 0-10V dimming driver standard
- 3G vibration rated
- Surge protection device standard
- IP66 rated optics
- Universal voltage (120-277V 50/60 Hz)
- Operates at -40°C to +40°C (-40°F to 104°F), limited 50°C high ambient option available
- Five-year warranty

Learn more about our outdoor lighting solutions at eaton.com/lighting

Additional lens options



Clear lens



Textured lens



Frosted lens



Refractive lens

EATON

Powering Business Worldwide

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. SA516002EN
August 17, 2018 11:32 AM

Eaton is a registered trademark.
All other trademarks are property of their respective owners.
Product availability, specifications, and compliances are subject to change without notice.