

Project		Catalog #		Type	
Prepared by		Notes		Date	



# Sure-Lites

## APWR Series

Remote Heads LED Emergency Heads  
Wet Location Listed

### Typical Applications

Office • Education • Healthcare • Hospitality  
• Retail • Industrial • Manufacturing

### Interactive Menu

- Order Information page 2
- Photometric Data page 2
- Control Solutions page 2
- Connected Systems page 2
- Product Warranty

### Product Certification




### Product Features



### Top Product Features

- 3.6V, .78W DC long lasting LED heads
- Lamp heads adjust 80° from vertical with 358° rotation
- Universal mounting plate
- Flame-resistant and impact-resistant
- Injection-molded thermoplastic material

### Dimensional Details



additional product diagrams


## APWR2BK

SAMPLE ORDER NUMBER: **APWR2BK**

### Order Information

Series	Remote Heads	Housing Color	Catalog Numbers
APWR	1=one LED head 2=two LED heads	_=White <b>BK</b> =Black	<b>APWR1, APWR2, APWR1BK, APWR2BK</b>

### APWR Spacing



## Product Specifications

### Electrical

- 3.6V DC Input Voltage

### Lampholder/Mounting Plate Construction

- Flame resistant and impact resistant, injection molded thermoplastic
- Lamp heads adjust 80° from vertical with 358° rotation
- Universal mounting plate
- Available in white or black

### Code Compliance

- UL 924 Listed
- Wet Location Listed (APWR)
- - (-30 C) to 50 C; (-22 F) to 122 F
- California Energy Code compliant

### Head/Lamp Data

- Long Life LED Emergency Heads
- Fully adjustable
- High impact thermoplastic
- Matches housing finish
- 3.6V, .78W DC Long Lasting LED Heads

### Warranty

- Five-year warranty