





CAUTION! RISK OF FIRE.







NOTICE: DO NOT EXCEED MAXIMUM RATED WATTAGE INDICATED FOR CORRESPONDING HOUSING, TRIM AND LAMP COMBINATIONS.




HALO E26 Series trims are UL Classified for use in housings manufactured by others.




Please refer to table below for manufacturer, housing catalog number, maximum rated wattage for lamp type, compatible trim and finish.



HALO E26 SERIES TRIMS CLASSIFIED -- 5-INCH IC HOUSING COMPATIBILITY

TRIM CATALOG NO.												
TRIM DESCRIPTION	5102WB White Metal Tapered Baffle / WHITE SELF-FLANGE		5102BB Black Metal Tapered Baffle, WHITE SELF-FLANGE		51075C Specular Tapered Reflector, WHITE SELF-FLANGE			5109WB White Plastic Tapered COILEX Baffle, WHITE SELF-FLANGE Ring			5109BB Black Plastic Tapered COILEX Baffle, WHITE SELF-FLANGE Ring	5109BKBB Black Plastic Tapered COILEX Baffle, BLACK SELF-FLANGE Ring
	LAMP TYPE MAXIMUM RATED WATTAGE			LAMP TYPE MAXIMUM RATED WATTAGE			LAMP TYPE MAXIMUM RATED WATTAGE			LAMP TYPE MAXIMUM RATED WATTAGE		
	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30
JUNO IC20*, IC20R	60	60	50	60	60	50	39	39	50	N/A	60	50

TRIM CATALOG NO.																																													
TRIM DESCRIPTION	5120WH FULL CONE REFLECTOR White Reflector, White Oversize Self-Flange			5120SN FULL CONE REFLECTOR Satin Nickel Reflector, Satin Nickel Oversize Self-Flange			5120TBZ FULL CONE REFLECTOR Tuscan Bronze Reflector, Tuscan Bronze			5125WB FULL CONE BAFFLE White Baffle, White Oversize Self-Flange			5125BB FULL CONE BAFFLE Black Baffle, White Oversize Self-Flange			5125BKBB FULL CONE BAFFLE Black Baffle, Black Oversize Self-Flange			5121WH SHALLOW FULL CONE REFLECTOR White Reflector, White Oversize Self-Flange			5126WB SHALLOW FULL CONE BAFFLE White Baffle, White Oversize Self-Flange			5126BB SHALLOW FULL CONE BAFFLE Black Baffle, White Oversize Self-Flange			5145WH OPEN WET LOCATION, White, Shallow, Deep Self-Flange			5145SN OPEN WET LOCATION, Satin Nickel, Shallow, Deep Self-Flange			5145TBZ OPEN WET LOCATION, Tuscan Bronze, Shallow, Deep Self-Flange			5146WH OPEN WET LOCATION, White, Standard Self-Flange			5146SN OPEN WET LOCATION, Satin Nickel, Standard Self-Flange			5146TBZ OPEN WET LOCATION, Tuscan Bronze, Standard Self-Flange		
	LAMP TYPE MAXIMUM RATED WATTAGE				LAMP TYPE MAXIMUM RATED WATTAGE				LAMP TYPE MAXIMUM RATED WATTAGE			LAMP TYPE MAXIMUM RATED WATTAGE				LAMP TYPE MAXIMUM RATED WATTAGE			LAMP TYPE MAXIMUM RATED WATTAGE																										
	A19	PAR30S	PAR30L	BR30	A19	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30	A19	PAR30S	PAR30L	BR30	PAR30S	PAR30L	PAR30S	PAR30L	PAR30S	PAR30L																								
ELITE BSIC-AT	29	50	60	N/A	29	50	60	N/A	50	75	50	29	50	75	50	60	75	50	60	50	60																								
NORA NHIC-501QAT	29	50	60	N/A	29	50	60	N/A	50	75	50	29	50	75	50	60	75	50	60	50	60																								

TRIM CATALOG NO.																																		
TRIM DESCRIPTION	5130WH White Eyeball / White Oversize Self-Flange 30-degree short / 20-degree long tilt		5165WH White Gimbal & Trim Ring 35-degree tilt				5165BK Black Gimbal & Trim Ring 35-degree tilt				5165SN Satin Nickel Gimbal & Trim Ring 35-degree tilt				5165TBZ Tuscan Bronze Gimbal & Trim Ring 35-degree tilt				5222WH Regressed Gimbal, White Baffle & Narrow Trim Ring 45-degree tilt				5222BB Regressed Gimbal, Black Baffle & Narrow Trim Ring 45-degree tilt				5222SC Regressed Gimbal, Specular Reflector & Narrow Trim Ring 45-degree tilt				5222H Regressed Gimbal, Haze Reflector & Narrow Trim Ring 45-degree tilt			
	LAMP TYPE MAXIMUM RATED WATTAGE		LAMP TYPE MAXIMUM RATED WATTAGE				LAMP TYPE MAXIMUM RATED WATTAGE				LAMP TYPE MAXIMUM RATED WATTAGE																							
	PAR30S		PAR30S				PAR30L				PAR30S				PAR30L																			
ELITE BSIC-AT	75		39				39				39				60																			
NORA NHIC-501QAT	75		50				50				39				60																			
JUNO IC20*, IC20R	N/A		39				39				N/A				N/A																			

TRIM CATALOG NO.								
TRIM DESCRIPTION	5150WH Flat Frost Lens with Reflector, White Plastic Self-Flange		5150SN Flat Frost Lens with Reflector, Satin Nickel Plastic Self-Flange		5150TBZ Flat Frost Lens with Reflector, Tuscan Bronze Plastic Self-Flange		5162WH Drop Lens, Reflector, White Plastic Trim [Impact resistant & non-conductive]	
	LAMP TYPE MAXIMUM RATED WATTAGE				LAMP TYPE MAXIMUM RATED WATTAGE			
	A19				A19			
ELITE BSIC-AT	N/A				29			
NORA NHIC-501QAT	29				29			

TRIM CATALOG NO.																		
TRIM DESCRIPTION	5176WH Open, Wide Flange, w/bracket, White			5176SN Open, Wide Flange, w/bracket Satin Nickel			5176TBZ Open, Wide Flange, w/bracket Tuscan Bronze			5186WH Open, Wide Flange, w/bracket, White			5186SN Open, Wide Flange, w/bracket Satin Nickel			5186TBZ Open, Wide Flange, w/bracket Tuscan Bronze		
	LAMP TYPE MAXIMUM RATED WATTAGE						LAMP TYPE MAXIMUM RATED WATTAGE											
	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30	PAR30S	PAR30L	BR30			
ELITE BSIC-AT	60	60	40	60	60	50	60	60	50	60	60	50	60	60	50			
NORA NHIC-501QAT	60	60	50	60	60	50	60	60	50	60	60	50	60	60	50			

