


Market focused portfolio with products designed for broad applications

Value - competitive prices with a high level of features and customization

Performance - market leading performance with connected sensors options delivering value beyond lumens per watt



Whether lighting schools, offices, or hospitals on a budget, Corelite's commercial recessed products offer a complete family of innovative, affordable, and energy saving LED solutions for your next project.

Good Better Best

Click on products to learn more



		Class RX/ZX	Class D3X	Class R2X	InDepth	Bridge	Divide	Class R3/Z3
APPLICABILITY	Education	★★★	★★	★★★	★★★	★★	★★	★
	Office	★★★	★★★	★★★	★★★	★★★	★★★	★★★
	Healthcare	★	★★	★★★	★★	★	★★★	★★
	Retail	★★	★★	★★	★★	★★	★	★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4, Metric	1x4, 2x2, 2x4	1x4, 2x2, 2x4, Metric	1x4, 2x2, 2x4	1x4, 2x2, 2x4, Metric
	lm/W (Max)	145	139	134	127	118	137	141
	Lumens (Max)	7600	7800	8000	9000	7300	7500	7200
	Life (@60K)	L94	L93	L87	L84	L80	L87	L87
	Lens	Round (R), Flat (Z) Frost - Smooth	Frost - Smooth, Perf Inlays	Round (R), Frost - Smooth	1", 2" Cube Regress 1", 2", 3" Cube Drop 2" Curve Regress & Drop	Acrylic (Wavestream), Perf Inlays	Acrylic (Wavestream), Specular, Diffuse	Round (R), Flat (Z) Frost - Ribbed, Perf Inlays
	Emergency	Integrated	Integrated	Integrated	Integrated, Indicator is Remote	Integrated	Integrated	Integrated
	CRI	80+ / 90	80+ / 90	80+ / 90	80+	80+ / 90	80+ / 90	80+ / 90
	Sensor Location	Integrated	Integrated	Tile Mount	Tile Mount	Integrated	Integrated	Tile Mount
	DLC	Standard	Standard	Standard	Premium	Standard	Premium	Premium
	Air Return	Yes	None	Yes	Planned	Yes, concealed	None	Yes
VividTune™	Tunable White	Tunable White	No	No	No	No	No	
INTEGRATED CONTROLS	Stand Alone Daylight / Occupancy	✓	✓	✓		✓	✓	✓
	WaveLinx	✓	✓			✓	✓	
	WaveLinx, No Sensor	✓	✓		✓			
	Enlighted	✓	✓	✓		✓	✓	✓
	DLVP	✓	✓		✓	✓		

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable