

Good

Better

Best

Click on products to learn more



		Panels									
		CGT	FP	FPS	FPX	AP GR	GR	RTC	FR	Cruze Retrofit	Cruze ST
APPLICABILITY ¹	Education	★★★	★★★	★★★	★★★	★★★	★★★	★★★	★★	★★★	★★★
	Office	★★	★★	★★★	★★★	★★	★★	★★★	★★★	★★	★★★
	Healthcare	★	★	★	★★	★★	★★	★★	★★	★	★★
	Retail	★★	★★★	★★★	★★★	★★	★★	★★	★★	★	★★★
FEATURES / PERFORMANCE	Sizes	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4	2x2, 2x4	1x4, 2x2, 2x4	1x4, 2x2, 2x4
	lm/W (Max)	115	136	120	130	140	140	126	130 STD/150 HP	138	157
	Lum (Max)	5,300	7,000	6,500	6,400	6,400	18,000	7,000	3200 STD/8000 HP	5,000	17,000
	Life (@60K)	L84	L86	L87	L87	L90	L89	L75	L88	L85	L90
	Lens	Frost, Smooth	Frost, Smooth	Frost, Smooth	Frost, Smooth	Clear, Prismatic	Frost, Prismatic	Frost, Ribbed	Frost, Smooth	Frost, Ribbed	Round or Square, Frost - Ribbed or Smooth, Perf Inlays
	Emergency	Remote	Remote	Remote	Integrated	No	Integrated	Integrated	Integrated	Integrated	Integrated
	CRI	80+	80 / 90	80+	80+	80+	80+	80+	80+	80+	80+ / 90
	Sensor Location	Tile Mount	Tile Mount	Tile Mount	Integrated	Tile Mount	Integrated	Integrated	Integrated	Integrated	Integrated
	DLC	Standard	Premium	Standard	Premium	Premium	Premium	Premium	Premium	Premium	Premium
	Door	No	No	No	No	Yes	Yes	No	Yes	None	Yes
	Lumen / CCT Select	No	No	Yes	No	No	No	No	No	No	No
VividTune™	No	No	No	No	No	Tunable White	No	No	No	Tunable White	
INTEGRATED CONTROLS	Stand Alone Daylight / Occupancy				✓		✓	✓	✓	✓	✓
	WaveLinx Lite				✓		✓		✓	✓	✓
	WaveLinx				✓		✓	✓	✓	✓	✓
	DLVP				✓		✓		✓		✓

Notes: 1. ★★★ = high applicability, ★★ = medium applicability, ★ = low applicability, blank = non-applicable