


CGT Contractor Go-to Series FLAT PANEL

- Affordable backlit LED panel that fits in shallow plenums with room to spare
- Robust die-formed steel housing is post-painted for maximum durability
- Acrylic micro optics provide uniform illumination from corner to corner
- Extruded aluminum bezel with mitered corners tightly sealed to housing for durability
- Ideal for office spaces, schools, healthcare and retail merchandising areas



Dedicated CCT & Lumens

Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14CGT4040C	1x4 CGT Backlit LED Panel	2-T8 32W, 3-T8 32W	4000K	120/277V	4,000	39.4/38.8	080083879540	PGNH8KOZ
22CGT3535C	2'x2' CGT Backlit LED Pane	3-T8	3500K	120/277V	3,449	32	080083880003	P6WE1HNZ
22CGT3540C	2'x2' CGT Backlit LED Pane	3-T8	4000K	120/277V	3,582	32	080083880027	P0YGNM7S
24CGT4535C	2'x4' CGT Backlit LED Panel	2-T8, 3-T8	3500K	120/277V	4,268	38	080083880089	P28JP113
24CGT4540C	2'x4' CGT Backlit LED Panel	2-T8, 3-T8	4000K	120/277V	4,432	38	080083880102	PLTEVMIJ
24CGT4550C	2'x4' CGT Backlit LED Panel	2-T8, 3-T8	5000K	120/277V	4,432	38	080083880126	P8BJJLKN
24CGT5540C	2'x4' CGT Backlit LED Panel	3-T8, 4-T8	4000K	120/277V	5,337	47	080083880188	P5F04P82

CGT LED Panel Series and Accessories

Catalog Number	Description	UPC
CGTSURF14	1x4 CGT SURFACE MOUNT KIT	080083083145
CGTSURF22	2x2 CGT SURFACE MOUNT KIT	080083083121
CGTSURF24	2X4 CGT SURFACE MOUNT KIT	080083083107

CGTS NUV FLAT PANEL

- Backlit LED panel with selectable switches located on the side of the junction box, for quick and easy adjustment
- Ideal for office spaces, schools, healthcare facilities and retail merchandising areas
- Acrylic micro-optics provide uniform illumination from corner to corner
- Three colour temperature and three lumen package choices



Selectable CCT & Lumens

Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
14CGTS-NUV	1'x4' Recessed Panel	2-T8 32W, 3-T8 32W	3500K-5000K	120-347V	3,500-4,500	30,35,40	080083247806	PLA9H842922L
22CGTS-NUV	2'x2' Recessed Panel	2-T8 32W, 3-T8 32W	3500K-5000K	120-347V	3,500-4,500	30,35,40	080083247837	PLDJXEJJPJEQR
24CGTS-NUV	2'x4' Recessed Panel	3-T8 32W, 3-T5 28W	3500K-5000K	120-347V	4,000-6,000	35,40,50	080083247851	PLJQJQPJ7TDJ
CGTSNUV-SURF14	1'x4' Surface Mount Kit	Accessory	N/A	Accessory	N/A	N/A	080083248308	N/A
CGTSNUV-SURF22	2'x2' Surface Mount Kit	Accessory	N/A	Accessory	N/A	N/A	080083248322	N/A
CGTSNUV-SURF24	2'x4' Surface Mount Kit	Accessory	N/A	Accessory	N/A	N/A	080083248346	N/A

FPanel Series

FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- Fixed and selectable configurations available
- Selectable switch to set colour temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal solution for office spaces, schools, healthcare facilities and retail merchandising areas



Dedicated CCT & Lumens

Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14FP4240C	1x4 LED Flat Panel	2-T8 32W, 3-T8 32W	4000K	120/277V	4,451	39	080083833481	PBGLLF3K
22FP3240C	2'x2' Recessed Panel	3-T8	4000K	120/277V	3,560	30	080083833542	PUOIG6S2
22FP4235C	2'x2' Recessed Panel	2-U6T8	3500K	120/277V	4,641	39	080083833580	P8HIK308
22FP4240C	2'x2' Recessed Panel	3-U6T8	4000K	120/277V	4,567	39	080083833603	PELH4PNQ
24FP4740C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120/277V	4,858	40	080083833665	PGY6ID6B
24FP6440C	2'x4' Recessed Panel	3-T8, 4-T8	4000K	120/277V	6,611	59	080083833726	N/A

FPanel LED Series and Accessories

Catalog Number	Description	UPC
FPSUS24	Suspension Kit for Panels (CGT, FP, FPX)	080083258895
FPSURF14	1x4 Flat panel Surface mounting kit	080083802708
FPSURF22	2x2 Flat panel Surface mounting kit	080083802722
FPSURF24	2x4 Flat panel Surface mounting kit	080083802746

Achieva Recessed Selectable

TROFFER

- Design friendly with (3) selectable colour temperatures and (3) selectable lumen packages
- Ultra slim 1.5" design for shallow plenum applications
- One piece stamped housing delivers improved modern aesthetic look
- Up to 146 LPW for increased energy savings and reduced watts per square foot



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14ARS-L3C3-NUV	1x4 Troffer	2-T8 32W	3500K;4000K;5000K	120-347V	2800-4600	20/25/34	080083287529	Pending approval
22ARS-L3C3-NUV	2x2 Troffer	3-U6T	3500K;4000K;5000K	120-347V	2800-4300	20/27/33	080083287543	Pending approval
24ARS-L3C3-NUV	2x4 Troffer	2-T8 32W, 2-T5 54W	3500K;4000K;5000K	120-347V	6300-8200	25/33/47	080083287567	Pending approval

METALUX TROFFERS

Cruze ST Recessed Series TROFFER

- Architectural center basket lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; Ribbed, frosted acrylic lens
- High-performance LED system with advanced light distribution
- Ideal choice for commercial, institutional and healthcare facilities



Dedicated CCT & Lumens

Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
14CZ2-39-UNV-L835-CD1-U	1'x4', Troffer	2-T8 32W	3500K	120/277V	3,545	27.3	080083151103	PJ5LDRBX
14CZ2-39-UNV-L840-CD1-U	1'x4', Troffer	2-T8 32W	4000K	120/277V	3,545	27.3	080083147335	PCSA3DGA
22CZ2-39-UNV-L835-CD1-U	2'x2', Troffer	3-T8, 2-T5HO	3500K	120/277V	3,943	31	080083881284	P0AXJUK1
22CZ2-39-UNV-L840-CD1-U	2'x2', Troffer	3-T8, 2-T5HO	4000K	120/277V	3,943	31	080083881307	PU7UA6BJ
22CZ2-44-UNV-L835-CD1-U	2'x2', Troffer	3-U6T8	3500K	120/277V	4,424	33	080083881321	PXAMKHHN
22CZ2-44-UNV-L840-CD1-U	2'x2', Troffer	3-U6T8	4000K	120/277V	4,424	33	080083881345	PKWC1G2R
24CZ2-50-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 2-T5	3500K	120/277V	5,015	39.6	080083881628	P0K3FN8Z
24CZ2-50-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 2-T5	4000K	120/277V	5,015	39.6	080083881642	PI0YCHQ9

Note: DLC Premium items are noted in bold.

GRLED Series TROFFER

- Built and designed for general purpose lighting applications
- Shallow, low-profile housing, makes it compatible with highly restrictive plenums
- Traditional prismatic A12 lens and door assembly; Insulated ceiling (IC) rated
- Easy to install; Fits most T-grid systems; Below the ceiling maintenance
- Great choice for commercial offices, schools, hospitals, retail and more applications



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
24GR-LD5-48-F1-UNV-L835-CD1-U	2'x4' A Lens Troffer	2-T8 32W	3500K	120/277V	4,800	43	080083817160	PUSH29NN
24GR-LD5-48-F1-UNV-L840-CD1-U	2'x4' A Lens Troffer	2-T8 32W	4000K	120/277V	4,800	43	080083817153	PMDVK98H
24GR-LD5-64-F1-UNV-L835-CD1-U	2'x4' A Lens Troffer	2-T8 32W	3500K	120/277V	6,400	48	080083798889	P9KHQJP1

Note: DLC Premium items are noted in bold.

Troffer options and Accessories

Catalog Number	Description	UPC
DF-14W-U	1'x4' Dry Wall Frame Kit	662401232949
DF-22W-U	2'x2' Dry Wall Frame Kit	662401232963
DF-24W-U	2'x4' Dry Wall Frame Kit	662401232970