

METALUX STRIPLIGHTS

SLSTP Series STRIPLIGHT

- LED strip light with decorative end caps and toolless lens removal
- Suitable for either single or continuous row application
- Surface, suspended or wall mounted capable
- Impact resistant polycarbonate lens reduces maintenance
- Ideal for warehouse, retail, office or retrofit applications



Selectable CCT & Lumens

Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4SLSTPSLC-347	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	347V	2,400-6,000	18/30/46	080083249466	S-GLY0MQ
4SLSTPSLC-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120/277V	2,400-6,000	18/30/46	080083174416	S-5PSVX8
8SLSTPSLC-347	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	347V	4,300-11,200	33/63/85	080083249480	S-6CXKOJ
8SLSTPSLC-UNV	8' Single Lens	4-T8 32W, 2-T12 75W	3500K-5000K	120/277V	4,300-11,200	33/63/85	080083174423	S-DH9QR0

Dedicated CCT & Lumens

Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID/ Energy Star
4SLSTP4040DD-120V	4' Single Lens	2-T8 32W, 1-T5HO 54W	4000K	120V	4,000	40	080083705801	2268835 *
4SLSTP4040DD-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4,927	41	080083705825	PXZQGN9C
8SLSTP8040DD-UNV	8' Single Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	9,304	79	080083814787	P0K8WFD1

Note: Energy Star items are noted with an Asterisk (*).

Sensor Kits


Catalog Number	Description	PIR Sensor	UPC
SLSTP MS00 KIT	SLSTP Field Installable Sensor KIT	100% / 50% / OFF	080083254200
SLSTP MS25 KIT	SLSTP Field Installable Sensor KIT	100% / 50% / Low (~30%)	080083254224



METALUX STRIPLIGHTS | WRAPS

SSF Series STRIPLIGHT

- Heavy-Duty steel welded wireguard
- Protects 4' striplights from damage and abuse
- Painted after fabrication, white standard
- Fits most 4' Cooper Lighting strip lights



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC
WG/SSF-4FT-B	4' White Wire Guard	Accessory	Accessory	Accessory	Accessory	Accessory	662400106647

ST Series STRIPLIGHT

- Full-length LED striplight ideal for replacing lamp fluorescent strips
- Superior performance with lumens up to 9,200 and 115 lumens per watt
- 3 field-selectable CCT options available: 3500K, 4000K, 5000K; 80 CRI
- Continuous row mount aligner included to add-on length as needed
- Low voltage 0-10V dimming to 10%



Dimming and Selectable CCT

Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4ST2L40SC3	4' Dual Lens	2-T8 32W, 1-T5HO 54W	3500K-5000K	120/277V	4,760	40	080083241583	S-TSP41D

Dedicated CCT & Lumens

Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	Energy Star ID
4ST1L2040R	4' Single Lens	1-T8 32W	4000K	120/277V	2,298	20	080083838189	2382010
8ST2L8040R	8' Dual Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	8,867	78	080083838202	2382033

Achieva™ Surface WRAP

- Ideal for replacing up to four lamp fluorescent and low-bay linear fluorescents
- 3 colour Field-Selectable in 35/40/5000K, Field-Selectable lumens: 2,250 - 12,500
- Designed for single or continuous row mount
- Suitable for ceiling, wall, or suspension mounting



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4AWWS-L3C3-NUV	4' Wide Modern Wrap, Dimming	2-T8 32W	3500K-5000K	120-347V	4,500-6,500	32/40/50	Pending	Pending

NWS Series

WRAP

- Ideal for replacing two or three lamp fluorescents up to 96W
- 3 field-selectable CCT: 3500K, 4000K, 5000K
- Field-selectable lumens: 2,000 - 5,272
- Surface (wall or ceiling) mount via junction box or direct to surface, UNV 0-10V dimming to 10%



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4NW35C3R	4ft Linear LED Wrap	2-T8 32W	3000K-4000K	120V	3500	35	080083257447	2398236
4NWS3C3-NUV	4ft Linear LED Wrap	2-T8 32W, 2-T12	3500K-5000K	120-347V	4000-5400	28/34/42	080083257546	S-YJTA0N

WP Series

WRAP

- Compact LED wrap light delivers value and energy savings
- Perfect retrofit solution for replacing single or 2-lamp fluorescent wraparounds
- Low-profile, highly versatile design; Post-painted die-formed channel
- Prismatic lens ensures even, glare-free light distribution



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC
4WP3040R	4' Linear Utility	2-T8 32W	4000K	120V	3,400	31	080083847167

WN Series

WRAP

- 100% clear acrylic prismatic lens provide excellent illumination
- Lift-and-shift lens offers easy re-lamping
- Ends formed with housing for strength and row alignment
- Commercial or residential electronic ballast
- Rotorlock lampholders enable easy lamp engagement



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC
WN-232A-UNV-EB81-U	4' Surface Commercial Wraparound	2-T8 32W	Lamp Dependant	120/277V	Lamp Dependant	Lamp Dependant	080083518845