

METALUX COMMERCIAL



METALUX


Commercial LED Lighting

Metalux Commercial offers a broad range of panels, troffers, striplights, wraps and flushmount solutions that feature the latest LED and driver technology for optimal performance.

- **Controllability.** Selectable options for flexibility.
- **Performance.** Delivers value and energy savings.
- **Durability.** Long service life and reduced maintenance.
- **Low Glare.** Increase comfort levels with less glare.



Scan to browse Metalux Commercial videos



METALUX FLAT PANEL

CGT Contractor Go-To Series FLAT PANEL


- Affordable LED panel that fits in shallow plenums with room to spare; Thin 2 1/8 inch height
- Robust die-formed steel housing is post-painted for maximum durability
- Acrylic micro optics provide uniform illumination from corner to corner
- Extruded aluminum bezel with mitered corners tightly sealed to housing for durability
- Ideal for office spaces, schools, healthcare and retail merchandising areas



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22CGT3535C	2'x2' Recessed Panel	3-T8	3500K	120/277V	3,449	32	080083880003	P6WE1HNZ
22CGT3540C	2'x2' Recessed Panel	3-T8	4000K	120/277V	3,582	32	080083880027	P0YGNM7S
24CGT4535C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120/277V	4,268	38	080083880089	P28JP113
24CGT4540C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120/277V	4,432	38	080083880102	PLTEVMIJ
24CGT4550C	2'x4' Recessed Panel	2-T8, 3-T8	5000K	120/277V	4,432	38	080083880126	P8BJJLKN
24CGT5535C	2'x4' Recessed Panel	3-T8, 4-T8	3500K	120/277V	5,139	47	080083880164	PGQBATOL
24CGT5540C	2'x4' Recessed Panel	3-T8, 4-T8	4000K	120/277V	5,337	47	080083880188	P5F04P82

FP / FPS Series FLAT PANEL

- Ultra-thin LED flat panel; Less than 2-inches height for shallow plenums
- Fixed and selectable configurations available
- Selectable switch to set color temperature, lumens and watts desired for task
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Ideal solution for office spaces, schools, healthcare facilities and retail merchandising areas



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22FP3235C	2'x2' Recessed Panel	3-T8	3500K	120/277V	3307	29	080083833528	PQC9IUIC
22FP3240C	2'x2' Recessed Panel	3-T8	4000K	120/277V	3,560	30	080083833542	PUOIG6S2
22FP4235C	2'x2' Recessed Panel	2-U6T8	3500K	120/277V	4,641	39	080083833580	P8HIK308
22FP4240C	2'x2' Recessed Panel	3-U6T8	4000K	120/277V	4,567	39	080083833603	PELH4PNQ
24FP4735C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120/277V	4,990	40	080083833641	PRZ2RGDY
24FP4740C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120/277V	4,858	40	080083833665	PGY6ID6B
24FP6440C	2'x4' Recessed Panel	3-T8, 4-T8	4000K	120/277V	6,611	59	080083833726	PUQIRODO

Selectable CCT & Selectable Lumens

22FPSL2SCT3	2'x2' Recessed Panel	3-T8	3000K-4000K	120/277V	1,700-3,500	15	080083889402	PIBWK9P9, PB32RP9H, PJQG8V0T
24FPSL2SCT3	2'x4' Recessed Panel	2-T8, 3-T8	3000K-4000K	120/277V	3,100-6,300	27	080083889365	PK4M6K93, PZFCJCMXS, PU0HKZ87

RBG Series

FLAT PANEL

- Architectural elegant 6-inch grid, 4-inch aperture fixture
- Recessed, surface or suspension mounting
- 3 field-selectable CCT: 3000K, 3500K, 4000K; 80 CRI
- Lumen selectable: 500, 750 or 1,000 lumens per foot



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	UPC	DLC Product ID
4RBG6-SL1-L8SCT3	4' Length	2-F32T8, 1-F54T5HO, 2-F28T5	3000K-4000K	120/277V	500/750/1,000*	36	080083866465	PUREBLSF, PSMWARPL, PW27GGE8

*Lumens per ft.

Cruze ST Recessed Series

TROFFER

- Architectural center basket lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; Ribbed, frosted acrylic lens
- High-performance LED system with advanced light distribution
- Ideal choice for commercial, institutional and healthcare facilities



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22CZ2-32-UNV-L835-CD1-U	2'x2', Troffer	2-T5, 2-T8	3500K	120/277V	3,280	26	080083881185	PL057CFW (120V) , P15VC648 (277V)
22CZ2-32-UNV-L840-CD1-U	2'x2', Troffer	2-T5, 2-T8	4000K	120/277V	3,280	26	080083881208	PO30DW27 (120V) , P8GWVDUZ (277V)
22CZ2-34HE-UNV-L835-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	3500K	120/277V	3386	26	080083881222	P6ZEZIGY
22CZ2-34HE-UNV-L840-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	4000K	120/277V	3386	26	080083881260	PMRQB66T
22CZ2-39-UNV-L835-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	3500K	120/277V	3,943	34	080083881284	P0AXJUK1
22CZ2-39-UNV-L840-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	4000K	120/277V	3,943	34	080083881307	PU7UA6BJ
24CZ2-40-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 3-T8	3500K	120/277V	4,196	36	080083881505	PUDYNNME
24CZ2-40-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 3-T8	4000K	120/277V	4,196	36	080083881529	PWWGAYMY
24CZ2-50-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 2-T5	3500K	120/277V	5,015	48	080083881628	POK3FN8Z
24CZ2-50-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 2-T5	4000K	120/277V	5,015	48	080083881642	PI0YCHQ9

Note: DLC Premium items are noted in bold.

CooperKit Retrofit Kit Series

TROFFER

- 2'x2' and 2'x4' LED center basket retrofit kit is the ideal solution to upgrading existing recessed fluorescent lighting
- Engineered for quick installation in existing luminaire
- Simple and tool-less installation for labor savings
- Reduced maintenance costs due to the extended lifetime of LEDs



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22CBRK-31-UNV-L840-CD1-U	2'x2' Center Basket Retrofit Kit	2-T5, 2-T8	4000K	120/277V	3168	21	080083195909	P6PT30P6
24CBRK-42-UNV-L840-CD1-U	2'x4' Center Basket Retrofit Kit	2-T8, 3-T8	4000K	120/277V	4200	28	080083196203	P1DQUGFJ

Note: DLC Premium items are noted in bold.

Perceive Recessed Architectural Series

TROFFER

- 3D optical pattern adds dimension and visual interest on a smooth flat surface
- Low-glare solution for increased comfort level
- Extruded aluminum bezel for enhanced durability and clean finished look
- Bottom surface can be wiped down for easy cleaning and maintenance
- Ideal solution for office spaces, schools, and healthcare facilities



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22PT-35-PB1-L835-U	2'x2' Troffer	3-T8, 4-T8, 2-T5HO	3500K	120-277V	3500	29	080083253906	DLC Pending
22PT-35-PB1-L840-U	2'x2' Troffer	3-T8, 4-T8, 2-T5HO	4000K	120-277V	3500	29	080083253913	DLC Pending
24PT-45-PB1-L835-U	2'x4' Troffer	2-T8, 3-T8	3500K	120-277V	4500	37	080083253920	DLC Pending
24PT-45-PB1-L840-U	2'x4' Troffer	2-T8, 3-T8	4000K	120-277V	4500	37	080083253937	DLC Pending

SkyRidge Series

TROFFER

- Recessed LED specification series with glare-reducing performance
- Affordable, aesthetically pleasing alternative to fluorescent fixtures
- Advanced optical control with optimal illumination
- Over 60% energy savings when compared to fluorescent troffers
- Ideal choice for commercial interiors



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
22SR-LD2-29-C-UNV-L835-CD1-U	2'x2', Recessed Troffer	2-T5, 2-T8	3500K	120/277V	3,095	23	080083752584	PL2K2CYL (120V) , PURGNZ9E(277V)
22SR-LD2-29-C-UNV-L840-CD1-U	2'x2', Recessed Troffer	2-T5, 2-T8	4000K	120/277V	3,157	23	080083752577	PSRAE17C
24SR-LD2-48-C-UNV-L835-CD1-U	2'x4', Recessed Troffer	2-T8, 2-T5	3500K	120/277V	4,805	38	080083752492	P6V4CWNY
24SR-LD2-48-C-UNV-L840-CD1-U	2'x4', Recessed Troffer	2-T8, 2-T5	4000K	120/277V	4,901	38	080083752485	PDLK7ZMQ

Note: DLC Premium items are noted in bold.

SLSTP Series

STRIPLIGHT

- LED strip light with decorative end caps and toolless lens removal
- Suitable for either single or continuous row application
- Surface, suspended or wall mounted capable
- Impact resistant polycarbonate lens reduces maintenance
- Ideal for warehouse, retail, office or retrofit applications



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4SLSTP4040DD-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4927	41	080083705825	PXZQGNP9C, PPA1YS12
8SLSTP8040DD-UNV	8' Single Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	9304	79	080083814787	POK8WFD1, PARMCVA1