

SNLED Series STRIPLIGHT

- Round lens linear LED striplights available in two sizes
- Offers excellent fixture efficiency and control versatility
- Full body strip can be paired with Sure-Lites EBP emergency options
- 0-10V dimming to 10%
- Ideal solution for commercial office, warehouses, retail, and schools



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4SNLED-LD5-41SL-LW-UNV-L840-CD1-U	4' Round Lens	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4214	35	080083817078	PJWRG9KV
8TSNLED-LD5-74SL-LW-UNV-L840-CD1-U	8' Round Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	7625	61	080083852703	PY759J1D

ST Series STRIPLIGHT

- Full-width LED striplight; Ideal for replacing single or 2-lamp fluorescent striplights
- Superior performance with lumens up to 9200 and 115 lumens per watt
- Unique single or dual lens tube design
- 0-10V Dimming to 10%
- Continuous row mount aligner included to add-on length as needed



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
2ST2L2040	2' Dual Lens, Dimming	2-T8 17W	4000K	120/277V	2,300	20	080083150960	PL5HYNT07031
4ST2L4040	4' Dual Lens, Dimming	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4,600	40	080083150984	PLL0TV2Y2320
8ST2L8040	8' Dual Lens, Dimming	4-T8 32W, 2-T12 75W	4000K	120/277V	9,200	80	080083151004	PL7YD22S7XBJ

WNLED Series WRAP

- Utility commercial LED linear wrap
- Single or continuous row applications
- Frosted lens offers best-in-class uniform illumination
- Ideal for commercial applications including schools, institutions and retail spaces
- Provides long service life, eliminating re-lamping issues and minimizing maintenance common with traditional fluorescent



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4WNLED-LD4-40SL-F-UNV-L840-CD1-U	4' Linear Wrap	2-T12, 2-T8 32W	4000K	120/277V	4,006	30	080083756889	PK3W95DW

WP Series WRAP

- Compact LED wrap light delivers value and energy savings
- Perfect retrofit solution for replacing single or 2-lamp fluorescent wraparounds
- Low-profile, highly versatile design; Post-painted die-formed channel
- Prismatic lens ensures even, glare-free light distribution
- Ideal for commercial applications from schools and dorms to warehouses and retail areas



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4WP3040C	4' Linear Utility	2-T8 32W	4000K	120/277V	3,588	31	080083858361	PC1Y20YN

WPLD Series WRAP

- Streamlined, low-profile design
- Smooth LED lens provides soft, uniform, glare-free light output
- Providing up to 60% energy savings over fluorescent light sources
- Suitable for ceiling, wall or suspension mounting
- Mounting slots allow for installation directly into the junction box with 100° of rotational freedom



Catalog Number	Description	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	DLC Product ID
4WPLD4035C	4' Low Profile	2-T8 32W	3500K	120/277V	4,557	39	080083750603	PZ4NNCFK
4WPLD4040C	4' Low Profile	2-T8 32W	4000K	120/277V	4,576	39	080083749676	PYGI6R4N

FM Dimming Series FLUSHMOUNT

- Versatile ceiling- or wall-mount series for a broad range of applications
- 3-field selectable CCT: 3000K, 4000K and 5000K
- Full frost, opal white LED lens provides optimal light output with no pixelation
- Even, uniform light distribution; Easy lens installation
- Perfect for utility or laundry rooms, closets, dormitories and more



Catalog Number	Description	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	ENERGY STAR ID
FM11WRCCR	11" Flushmount, Round	22 W T9 Circline	3000K-5000K	120V	1,100	14	080083840151	2324855
FM15WRCCR	15" Flushmount, Round	100W INC or 32W T9 Circline	3000K-5000K	120V	1,800	22	080083845378	2324853