

SLD Downlight SURFACE MOUNT

- Ultra-low profile 4 and 6-inch surface mount LED downlight
- 5 field-selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K; 90 CRI
- Ceiling or wall mounting in standard and fire-rated compatible junction boxes
- SLD6 retrofits in 5-inch and 6-inch insulated ceiling (IC) and non-IC rated recessed housings
- Supply wire adapter with LED quick wiring connector included



Catalog Number	Description	Finish	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	ENERGY STAR ID
SLDSL4069S1EMWR	4" Surface Downlight	White	65W INC	2700K-5000K	120V	600	9	080083153107	2366149
SLDSL6069S1EMWR	6" Surface Downlight	White	65W INC	2700K-5000K	120V	600	9	080083153121	2366163
SLD6129S1EMWR	6" Surface Downlight	White	75W INC	2700K-5000K	120V	1200	15	080083153145	2373952
SLD6129SE010MWR	6" Surface Downlight	White	75W INC	2700K-5000K	120-277V	1200	15	080083153169	2373954
SLDACCKIT	4" and 6" SLD Accessory Kit	N/A	N/A	N/A	N/A	N/A	N/A	080083159819	2373954

HLC Closet Light Downlight SURFACE MOUNT

- Low-profile 6 and 9-inch surface mount LED downlights
- Below the ceiling installation, no clips or plates needed
- Installs in most 3-1/2-inch and 4-inch square, octagon or round junction and pancake boxes
- Supply wire adapter with LED quick wiring connector included; Sold as bulk packs only
- Meets NFPA requirements for use in closets



Catalog Number	Description	Finish	Replaces Up To	CCT	Voltage	Lumens	Watts	UPC	ENERGY STAR ID
HLC6099301EWH-6BP	6" Closet Light (6-Pack)	White	65W INC	3000K	120V	925	16	080083896448	2338422
HLC6099301EWH-12BP	6" Closet Light (12-Pack)	White	65W INC	3000K	120V	900	16	080083884728	2338422
HLC6099401EWH-6BP	6" Closet Light (6-Pack)	White	65W INC	5000K	120V	900	16	080083896462	2338423
HLC9129301EWH	9" Closet Light	White	100W INC	3000K	120V	1285	18	080083884667	N/A
HLC9129401EWH	9" Closet Light	White	100W INC	4000K	120V	1200	18	080083884681	N/A
HLCMS9129301EWH	9" Closet Light, Motion Sensor	White	100W INC	3000K	120V	1200	18	080083127993	N/A
HLCMS9129401EWH	9" Closet Light, Motion Sensor	White	100W INC	4000K	120V	1200	18	080083130214	N/A

BLD Downlight SURFACE MOUNT

- 4 and 6-inch low-profile surface mount LED downlight with wide distribution
- 5 field-selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K; 90 CRI
- Installs in most 3-1/2-inch and 4-inch square, octagon or round junction and pancake boxes
- Retrofits in 4, 5 and 6-inch insulated ceiling (IC) and non-IC rated recessed housings
- Supply wire adapter with LED quick wiring connector included



Catalog Number	Description	Finish	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	ENERGY STAR ID
BLD4089SWHR	4" Surface Downlight	White	65W INC	2700K-5000K	120V	802	10	080083826766	2362340
BLD6089SWHR	6" Surface Downlight	White	65W INC	2700K-5000K	120V	812	10	080083826803	2319364

SMD Downlight SURFACE MOUNT

- Low-profile 4, 6 and 12-inch surface mount LED downlight with wide distribution
- 5 field-selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K; 90 CRI
- Ceiling/Wall mounting in many 3½- and 4-inch square, octagon or round junction boxes
- Retrofits 4-inch and 6-inch insulated ceiling (IC) and non-IC rated recessed housings
- Supply wire adapter with LED quick wiring connector included
- Dimmable to 5% (120V dimmers); 90 CRI



Catalog Number	Description	Finish	Replaces Up To	Selectable CCT	Voltage	Lumens	Watts	UPC	ENERGY STAR ID
SMD4R69SWH	4" Surface Mount	White	60W INC	2700K-5000K	120V	738	9	080083020904	2365919
SMD4S69SWH	4" Surface Mount	White	60W INC	2700K-5000K	120V	757	9	080083020928	2365921
SMD6R69SWH	6" Surface Mount	White	60W INC	2700K-5000K	120V	777	9	080083020942	2365923
SMD6S69SWH	6" Surface Mount	White	60W INC	2700K-5000K	120V	774	9	080083020966	2366348
SMD12R209SWHE	12" Surface Mount	White	150W INC	2700K-5000K	120V	2,232	27	080083138005	N/A