






# OVERSTOCK INVENTORY BLOWOUT

Take advantage of the overstock Inventory Blowout pricing. Flat Panels, recessed downlighting, strips, wraps, exit and emergency lighting are available at extraordinary low prices to save you money!

Hurry, place your order TODAY!

SAVE up to 75%\*

on HALO, HALO Outdoor, Metalux, Sure-Lites and Greengate

| HALO   | HALO OUTDOOR  | METALUX  | SURE-LITES  |
|--|---|--|---|
| <p>Recessed downlighting.<br/>LED Outdoor</p>  | <p>Floodlights</p>  | <p>Flat Panels,<br/>Troffers, Strips</p>  | <p>Exit Signage</p>                           |
|  |   |  | GREENGATE   |
|  |   |  | <p>Wall Switches,<br/>Occupancy Sensors</p>  |

See SKU list attached to this flyer

Contact your Cooper Lighting Sales agent for terms, conditions and promotional details. While supplies last.

\*Savings is based on national average pricing. Final savings will be calculated at the time of purchase.


















Visit our website to learn more:  
[www.cooperlighting.com/overstock](http://www.cooperlighting.com/overstock)

| Brand                              | Family                        | Catalog No.   | Description  | Spec Link | UPC          | Per Case | Per Pallet |
|------------------------------------|-------------------------------|---|--|-----------|--------------|----------|------------|
| Ambient Flat-Panels Metalux        | LED Panel                     | <b>22FP3840C-UNC</b>  | 2x2 LED Flat Panel, 3800 lumens, 4000K, UNC  |           | -            | 4        | 32         |
|                                    |                               | <b>24FP3140C</b>  | 2x4 LED Flat Panel, 3100 lumens, 4000K, 80 CRI, 0-10V Dimming  |           | 080083858903 | -        | -          |
|                                    |                               | <b>24FP4750C</b>  | 2x4 LED Flat Panel, 4700 lumens, 5000K, 80 CRI, 0-10V Dimming  |           | 080083833689 | 1        | 22         |
|                                    |                               | <b>24FP6450C</b>  | 2x4 LED Flat Panel, 6400 lumens, 5000K, 80 CRI, 0-10V Dimming  |           | 080083833740 | 1        | 22         |
|                                    | LED Panel Accessory           | <b>FPXSURF24</b>  | 2x4 FPX Series Surface Mount Kit   |           | 080083867400 | 10       | 180        |
| Ambient Highbay and Lowbay Metalux | LED High Bay                  | <b>AMZ-OHB-24SE-W-480V-L850-CD-MW48DS16/2G06D08-FSP-211-U</b> | High Bay, Lensed, Wide Distribution, 80CRI / 5000K, 0-10V Dimming Driver, 480V   |           | -            | -        | -          |
|                                    |                               | <b>HBRLD2440R</b>   | HBR, 24000 Lumens, 120-277V, 4000K, Clear Lens   |           | 080083910755 | 1        | 24         |
|                                    |                               | <b>LCHB1240R</b>  | Lensed Comm. HiBay 12K Lum UNV Dim 40K   |           | 080083859320 | 1        | 72         |
|                                    |                               | <b>OHB-48HE-MCL-UNV-L740-CD-MS-MW27DS16/2G11M02-U</b>         | High Bay, HE, Clear Lens, Medium dist, 70CRI /4000K, 0-10V Dim, Motion Sensor, MWS   |           | -            | 1        | 28         |
|                                    |                               | <b>OHB-60HE-MCL-UNV-L740-CD-MS-MW27DS16/2G11M02-U</b>         | High Bay, HE, Clear Lens, Medium dist, 70CRI /4000K, 0-10V Dim, Motion Sensor, MWS   |           | 080083285020 | 1        | 28         |
|                                    | LED Vapor Tite                | <b>COO-4VT2-LD4-4-DR-UNV-L840-CD1-WL-U</b>                    | 4' Vaportite, LED 4.0, 4000 Lumens, Internal Prismatic Lens/15% DR High Impact Additive, 120-277V, 4000K, LED, 1 Dimming Driver, Wet Location Label, Unit pack |           | -            | 1        | 35         |
| Ambient Recessed Linear Metalux    | Center Basket 2'x2' Retrofit  | <b>22CZRK-LD4-24-UNV-L835-CD1-U</b>                           | 2x2 Cruze Retrofit LED, 2400 Lumens, UNV, 3500K, 0-10V 1%-100%   |           | 080083771318 | 1        | 72         |
|                                    | Center Basket Shallow 2'x4'   | <b>24RTC4835</b>  | 2x4 RTC LED Troffer, 4800 lumens, 3500K, 80 CRI (min), 0-10V Dimming   |           | 080083802623 | 1        | 13         |
|                                    |                               | <b>24RTC4840</b>  | 2x4 RTC LED Troffer, 4800 lumens, 4000K, 80 CRI (min), 0-10V Dimming   |           | 080083802630 | 1        | 13         |
|                                    | Troffers 2'x4'                | <b>24GPT7540CF</b>  | 2 X 4 LED Troffer, 54W, 7700 Lumens  |           | 080083147922 | 1        | 20         |
| Ambient Striplights All-Pro        | 8' Linear LED                 | <b>8SLSTP11040DD-UNV</b>                                      | 8' Linear LED Striplight, 11000 lumen, 4000K, UNV, 0-10V Dim to 10%  |           | 080083807680 | 2        | 70         |
|                                    |                               | <b>8SLSTP8040DD-UNV</b>                                       | 8' Linear LED Striplight, 8000 lumen, 4000K, UNV, 0-10V Dim to 10%   |           | 080083814787 | 2        | 110        |
|                                    |                               | <b>8SLSTP8050DD-UNV</b>                                       | 8' Linear LED Striplight, 8000 lumen, 5000K, UNV, 0-10V Dim to 10%   |           | 080083158966 | 2        | 80         |
| Ambient Strips Metalux             | 8' Linear LED                 | <b>8ST2L8040</b>  | 8' Dual Lens Dimming, 9200L 4K CCT   |           | 080083151004 | 1        | 90         |
| Ambient Wraparounds Metalux        | 4' Ceiling Mount              | <b>4NW50C3R</b>   | 4 FT Wrap, 5200 Lumens, 4000K, LED Dimmable, White   |           | 080083257461 | 4        | 144        |
| Controls                           | Occupancy and Vacancy Sensors | <b>OLW-DT-MV-N-W</b>  | Dual Tech PIR and Ultrasonic Wall Switch occupancy sensor with neutral   |           | 080083288212 | 1        | 1          |
|                                    |                               | <b>OLW-DT-MV-W</b>  | Dual Tech PIR and Ultrasonic Wall Switch occupancy sensor  |           | 080083288205 | 1        | 1          |
|                                    |                               | <b>OSC10-RMW</b>  | Occupancy Sensor, White, 1000 Sq Ft  |           | -            | -        | -          |

| Brand                                     | Family                        | Catalog No.                  | Description   | Spec Link                            | UPC          | Per Case     | Per Pallet |
|---|-------------------------------|------------------------------|---|--------------------------------------|--------------|--------------|------------|
| Controls                                  | Occupancy and Vacancy Sensors | <b>OSC15-RIW</b>             | Occupancy Sensor, White, 1500 Sq Ft   |                                      | -            | -            | -          |
|   |                               | <b>OSC20-RMW</b>             | Occupancy Sensor, White, 2000 Sq Ft   |                                      | -            | -            | -          |
|   |                               | <b>OSC-DT-1000</b>           | 1000sq ft coverage Dual tech ceiling sensor   |                                      | 080083259236 | 10           | 840        |
|   |                               | <b>OSC-DT-2000</b>           | 2000sq ft coverage Dual tech ceiling sensor   |                                      | 080083259250 | 10           | 840        |
|   |                               | <b>OSC-P-1500</b>            | 1500sq ft coverage PIR ceiling sensor   |                                      | 080083259212 | 10           | 840        |
|   |                               | Remote Control               | <b>ISHH-01</b>  | Integrated Sensor Programming Remote |              | 080083736287 | 250        |
| Exit and Emergency All-Pro                | Exit and Emergency Commercial | <b>APX6R</b>                 | AC Only, White Housing, LED Exit, Red Letters   |                                      | 080083566518 | 6            | 270        |
| Fail-Safe GUV                             | Accessory                     | <b>GUV4-LAMP-U</b>           | 4FT, T8 36W TUV Lamp  |                                      | 080083158805 | 6            | 1122       |
|   | Ceiling 2'x2'                 | <b>22GAC-4GUV9W-UNV-R1-W</b> | Germicidal Air Ceiling Mount4 SourcesGermicidal UV Emitter ,9W ,120-277V ,Single Rapid Start Driver ,White Finish |                                      | 080083182657 | 1            | 8          |
| Halo Commercial                           | Surface Mount LED             | <b>HLC9129301EWH</b>         | 9" LED Surface, 1200 lumens, 90 CRI, 3000k, 120V 60Hz, LE & TE Phase Cut 10% Dimming, M White                     |                                      | 080083884667 | 4            | 256        |
| Outdoor - Halo Floodlights                | Multi-Use Floodlighting       | <b>TGS2S402MSRB</b>          | Lumark Outdoor Floodlight, 2500 Lumens, 4000K, Double Head, Motion Sensor, Square, Residential, Bronze            |                                      | 080083913558 | 2            | 280        |
|   |                               | <b>TGS2S402MSRW</b>          | Lumark Outdoor Floodlight, 2500 Lumens, 4000K, Double Head, Motion Sensor, Square, Residential, White             |                                      | 080083913572 | 2            | 280        |
|   |                               | <b>TGS3S401DSRB</b>          | Lumark Outdoor Floodlight, 3,000 Lumens, 4000K, Single Head, Dusk to Dawn, Square, Residential, Bronze            |                                      | 080083913268 | 2            | 320        |
|   |                               | <b>TGS3S403FRRB</b>          | Lumark Outdoor Floodlight, 3000 Lumens, 4000K, Triple Head, Flood, Round, Residential, Bronze                     |                                      | 080083913596 | 2            | 210        |
|   |                               | <b>TGS3S403MRRB</b>          | Triple, 3K Lumen Selectable, 4K, MTN, RESI, RD,BR   |                                      | 080083256105 | 4            | 168        |
|   |                               | <b>TGS3S403MRRW</b>          | Triple, 3K Lumen Selectable, 4K, MTN, RESI, RD,WH   |                                      | 080083256129 | 4            | 168        |
|   |                               | <b>TGS5S401MSCB</b>          | Single, 5800 Lumen Selectable,4K, Mtn, Sq, Resi,Br  |                                      | 080083260041 | 4            | 216        |
| Outdoor Security & Worklights Floodlights | Dusk to Dawn                  | <b>WP5550LBZ</b>             | LED Wall Pack Floodlight, 5600 lumens - Bronze  |                                      | 080083835850 | 2            | 36         |
|   | Flood                         | <b>FT18VCW</b>               | Flood, Twin head floodlight, 3 selectable CCT, White  |                                      | 080083837151 | 2            | 240        |
|   |                               | <b>FT28VCB</b>               | LED Twin head floodlight, 3 selectable CCT, Bronze  |                                      | 080083837175 | 2            | 240        |
|   |                               | <b>FT28VCIBCE</b>            | LED Twin head floodlight with PC, 3 selectable CCT, Bronze  |                                      | 080083867165 | -            | -          |
|   | Motion Solar                  | <b>MSLED600</b>              | 180° Single LED Solar Wedge   |                                      | 080083787104 | -            | -          |
|   |                               | <b>SLMT1000W</b>             | 180° Solar LED Twin 1000 Lumens 5000K, White  |                                      | 080083859801 | -            | -          |

| Brand  | Family                               | Catalog No.   | Description  | Spec Link    | UPC          | Per Case | Per Pallet |
|--|--------------------------------------|---|--|--------------|--------------|----------|------------|
| Outdoor Security & Worklights Portable Worklight | Twin Stand                           | WLT5040LST  | 5100 Lumen Twin Head LED Portable Worklight with Stand   |              | 080083708086 | 2        | 32         |
| Recessed Halo Downlighting                       | Canless EZ-Trim                      | CEZ3125GU10WBICAT   | 3" Canless EZ-Trim, GU10 Lamp Base   |              | 080083175512 | 4        | 216        |
|  |                                      | CEZ4125E26WBICAT  | 4" Canless EZ-Trim, E26 Lamp Base  |              | 080083175550 | 4        | 168        |
|  |                                      | CEZ4125GU10WBICAT   | 4" Canless EZ-Trim, GU10 Lamp Base   |              | 080083175536 | 4        | 168        |
|  |                                      | CEZ6125E26WBICAT  | 6" Canless EZ-Trim, E26 Lamp Base  |              | 080083176212 | 4        | 96         |
|  |                                      | CEZ6125GU24WBICAT   | 6" Canless EZ-Trim, GU24 Lamp Base   |              | 080083175574 | 4        | 96         |
|  |                                      | CEZ6126E26WBICAT  | 6" Canless EZ-Trim, Shallow, E26 Lamp Base   |              | 080083176236 | 4        | 112        |
|  |                                      | CEZ6126GU24WBICAT   | 6" Canless EZ-Trim, Shallow, GU24 Lamp Base  |              | 080083175598 | 4        | 96         |
|  | E Series - Housings New Construction | E44MR16ICAT   | 4" Ultra Shallow Housing, ICAT, 10W MR16, UNV  |              | 080083818327 | 6        | 192        |
|  | E Series - Trims                     | RE-6109WB   | 6" White Plastic Tapered Coilex® Baffle, White Self-Flange Ring  |              | 080083757725 | 6        | 480        |
|  | H Series - Housings New Construction | H272ICAT  | 6" Housing 26W IC Air-Tite Compact Fluorescent, Electronic Ballast, 120V                                     |              | 622697900700 | 4        | 80         |
|  | H Series Contractor Packs            | H245RICATLA46930  | LA Contractor Pack - (1) H245RICAT 4" Housing ultra-shallow and (1) LA4 LED Module                           |              | 080083847105 | 1        | -          |
|  |                                      | H245RICATLT46930  | LT Contractor Pack - (1) H245RICAT 4" Housings ultra-shallow and (1) LT46 LED Modules                        |              | 080083847082 | 1        | -          |
|  | LED Flushmount                       | FM119S1EWHR   | 11" LED Low Profile Round Flushmount, 5-Color Field Selectable CCT: 2700-5000 CCT                            |              | 080083257706 | 4        | 108        |
|  |                                      | FM159S1EWHR   | 15" LED Low Profile Round Flushmount, 5-Color Field Selectable CCT: 2700-5000 CCT                            |              | 080083257720 | 4        | 72         |
|  | Module Retrofit LT Series Trims      | LT3059FS351EWHDMR   | 3" LED Direct Mount, 500 Lumens, 90 CRI, 3000K/4000K/5000K Select, 120V, Matte White Flange                  |              | 080083159628 | 4        | 588        |
|  |                                      | LT4069FS351EWHDMR   | 4" LED Direct Mount, 600 Lumens, 90 CRI 3000K/4000K/5000K Select, 120V, Matte White Flange                   |              | 080083159642 | 4        | 336        |
|  |                                      | LT6089FS231EWHDMR   | 6" LED Direct Mount, 800 Lumens, 90 CRI 2700K/3000K/3500K Select, 120V, Matte White Flange                   |              | 080083159963 | 4        | 288        |
|  |                                      | LT6089FS351EWHDMR   | 6" LED Direct Mount, 800 Lumens, 90 CRI 3000K/4000K/5000K Select, 120V, Matte White Flange                   |              | 080083159666 | 4        | 288        |
|  |                                      | LTSS4069FS351EWHWR  | 4" Retrofit Smooth Splay -Trim LED Module, 600 Lumens, 120V, 90CRI, 3000K/4000K/5000K Selectable CCT,White   |              | 080083162543 | 4        | 576        |
|  |                                      | LTSS56069FS231EWHWR   | 5/6" Retrofit Smooth Splay -Trim LED Module, 600 Lumens, 120V, 90CRI, 2700K/3000K/3500K Selectable CCT,White |              | 080083162581 | 4        | 300        |
| LTSS560WH9930R-CA                                |                                      | 5/6" Retrofit Smooth Splay -Trim LED Module, 900 Lumens, 90CRI, 3000k,White, CA |  | 080083154029 | 6            | 288      |            |
| Module Retrofit RSQ Series Trims                 | RSQ5089FS1EMWWB                      | 5" Square lens downlight, 800lm (nom), 90 CRI, Field Select, 120V, MWWB         |  | 080083824595 | 6            | 360      |            |

| Brand                      | Family                       | Catalog No.              | Description   | Spec Link  | UPC  | Per Case | Per Pallet |
|----------------------------|------------------------------|--------------------------|---|--|--|----------|------------|
| Recessed Halo Downlighting | Trims-Module Adj Gimbals     | <b>RA5606930WHR</b>      | 5/6" Retrofit Adjustable Gimbal LED Module, 90CRI, 120V, 3000K, Very Wide Flood, White                        |    | 080083693160   | 6        | 240        |
|                            | Trims-Module Adj Gimbals DM  | <b>HLA305FL9271EMWR</b>  | 3" HLA Adjustable Round Gimbal, 500 Lumens, 90CRI, 120V, Selectable CCT, 40 degree beam spread, MW Flange     |    | 080083882663   | 6        | 672        |
|                            |                              | <b>HLA3S05FL9301EMWR</b> | 3" HLA Adjustable Downlight, Square, 500 Lumens, 40D, 3000K, 120V, Matte White                                |    | 080083882724   | 6        | 672        |
|                            | Trims-Module DM              | <b>HLA305FL9301EMWR</b>  | 3" Round LED Directional Downlight w/Remote Driver/Junction Box, 500 Lumens, 40 deg Flood, 90 CRI, 3000K      |    | -  | -        | -          |
|                            | Trims-Module Retrofit LED DM | <b>LCR4129FSE010MW</b>   | 4" Round, 1200 Lumens, 90 CRI, 2700 - 5000K Selectable CCT, UNV (120-277), 0-10V, 100% to 5% Dimming, M White |    | 08008389002  | 6        | 360        |
|                            | Trims-Modules Surface        | <b>BLD6089SWHR</b>       | 6" Backlit LED Downlight (BLD), 90CRI, SeleCCTable CCT  |    | 080083826803   | 4        | 320        |
|                            |                              | <b>SMD4R6930WHDM</b>     | 4" Round Surface Mount Downlight, 600 Lumen, 90CRI, 3000K, Spring Clips                                       |    | 080083766390   | 6        | 300        |
|                            |                              | <b>SMD4S6930WHDM</b>     | 4" Square Surface Mount Downlight, 600 Lumen, 90CRI, 3000K, Spring Clips                                      |    | 080083766451   | 6        | 300        |
|                            |                              | <b>SMD6R12927WH</b>      | 6" Round Surface Mount Downlight, 1200 Lumen, 90CRI, 2700K  |    | 080083825400   | 6        | 360        |
|                            |                              | <b>SMD6S129SWH</b>       | 6" Square Surface Mount Downlight, 1200 Lumen, 90CRI, CCT Selectable, White                                   |    | 080083021307   | 4        | 320        |
|                            |                              | <b>SMD6S6930WHDM</b>     | 6" Square Surface Mount Downlight, 600 Lumen, 90CRI, 3000K, Spring Clips                                      |    | 080083767151   | 6        | 240        |
|                            |                              | Trims-Modules Surface DM | <b>HLB4069FSMWR-6PK-C</b>   | 4" LED Lens Downlight with Remote Driver/Junction Box, 600 Lumens, 6PK               |  | -        | -          |
|                            | <b>HLB4-5CCT-4PK</b>         |                          | 4-Pack 4" White Round Recessed LED 792 Lumens 2700-5000K Selectable   |  | 080083863761   | 2        | 160        |
|                            | <b>HLB6-5CCT-4PK</b>         |                          | 4-Pack 6" White Round Recessed LED 792 Lumens 2700-5000K Selectable   |  | 080083863822   | 2        | 144        |
|                            | <b>HLBPH4069FS1EMWR-12BP</b> |                          | 4" LED Smooth Lens Downlight, Remote Driver, Junction Box, Matte White Flange, 12 PK                          |  | 080083259717   | 1        | 54         |