

NOW OR NEVER

because it is not forever!

Take advantage
of the lighting

**SUPER
DEAL**
of the year!



HALO

Recessed Downlights



METALUX

Flat Panels, Strips, Wraps and High Bays



LUMARK

Wall Packs and Canopy



SURE-LITES

Exit & Emergency Lighting



See SKU list and sales agent for details.





























Distributor Order Guidelines:

- Offer is for qualified distributors. Qualification subject to credit approval. Standard terms apply.
- The order must meet the minimum \$3,000 freight allowance to be prepaid. Shipments to your branch or job site are allowed.
- There are no quantity limits. No minimum order requirements. No promo code is required.
- Only products listed in the Now or Never Promotion SKU list qualify www.cooperlighting.com/overstock.
- Only available while supplies last. Super deal pricing cannot be applied to previously purchased products. Super deal product SKUs are not eligible for returns.
- All rights reserved. Cooper Lighting Solutions reserves the right to change or cancel the promotional offer at any time without notice.

Brand	Family	Catalog No.	Description	Spec Link	LM	W	UPC	Per Case	Per Pallet
Ambient Flat-Panels Metalux	LED Panel 1'x4'	14CGT4040C	1x4 CGT LED Flat Panel, Acrylic micro optics, Back-lit, 4000 lumens, 4000K, 80 CRI, 0-10V Dimming		4351	39	080083879540	-	-
	LED Panel 2'x2'	22CGT3535C	2x2 CGT LED Flat Panel, Acrylic micro optics, Back-lit, 3500 lumens, 3500K, 80 CRI, 0-10V Dimming		3582	32	080083880003	1	72
		22FP3240C	2x2 LED Flat Panel, 3200 lumens, 4000K, 80 CRI, 0-10V Dimming		3560	30	080083833542	1	44
		22FP3840C-UNC	2x2 LED Flat Panel, 3800 lumens, 4000K, UNC		3654	39	-	4	32
		22FP4250C	2x2 LED Flat Panel, 4200 lumens, 5000K, 80 CRI, 0-10V Dimming		4704	39	080083833627	1	44
	LED Panel 2'x4'	24FP4750C	2x4 LED Flat Panel, 4700 lumens, 5000K, 80 CRI, 0-10V Dimming		5005	40	080083833689	1	22
		24FP5830C9	2x4 LED Flat Panel, 5800 lumens, 3000K, 90 CRI, 0-10V Dimming		5282	58	080083833849	1	22
	LED Panel Accessory	FPXSURF24	2x4 FPX Series Surface Mount Kit		-	-	080083867400	10	180
Ambient Flush Mount All-Pro	FM LED	FM15WSSCCR	15" LED Flush Mount, Square, Selectable Color Temp (2700-5000K), 1700 Lumen Fixture White		1800	21	080083840137	4	32
Ambient Highbay and Lowbay All-Pro	Vapor Tite 4'	4APVTL-D-54L840	4' Vaportite, LED, 5400 lumen, UNV, 4000K, Wet Location		6209	50	080083802166	4	80
Ambient Highbay and Lowbay Metalux	High Bay LED	LCHB1240R	Lensed Comm. HiBay 12K Lum UNV Dim 40K		12000	4000	080083859320	1	72
		OHB-24HE-MCL-UNV-L840-CD-U	High Bay, HE, Clear Lens, Medium Distribution, 80CRI / 4000K, 0-10V Dimming Driver		24000	130	080083266111	1	18
		OHB-24HE-MCL-UNV-L850-CD-U	High Bay, HE, Clear Lens, Medium Distribution, 80CRI / 5000K, 0-10V Dimming Driver		24000	130	080083266104	1	18
		OHB-24HE-MFL-UNV-L850-CD-U	High Bay, HE, Frosted Lens, Medium Distribution, 80CRI / 5000K, 0-10V Dimming Driver		24000	132	080083151448	1	18
		OHB-24SE-W-UNV-L840-CD-ZW-SWPD3-MW27TS10/2G06M02-PALC	High Bay, Clear Lens, Wide, 80CRI / 4000K, 0-10V Dimming, Int Wavelinx Sensor, MWS, Jobpack, in carton		24000	148	-	1	36
		OHB-36SE-MCL-UNV-L850-MS/12307770-MW27DS16/2G11A36-U	High Bay, Clear Lens, Medium dist, 80CRI /5000K, 0-10V Dimming, Motion Sensor, MWS		36000	181	-	1	9
		OHB-36SE-MFL-UNV-L840-CD-ZW-SWPD3-U	High Bay, Frosted Lens, Medium dist, 80CRI /4000K, 0-10V Dim, Integrated Wavelinx Motion Sensor		36000	181	080083251346	1	18
		OHB-48HE-MCL-UNV-L740-CD-MS-MW27DS16/2G11M02-U	High Bay, HE, Clear Lens, Medium dist, 70CRI /4000K, 0-10V Dim, Motion Sensor, MWS		48000	-	-	1	28
		VHB-1824-N-UNV-L840-CD-U	Value High Bay, Narrow distribution, Lumen Select 18000, 24000, 4000K, 0-10V Dimming		-	-	080083194834	1	78
Ambient Recessed Linear Metalux	Center Basket 2'x2' Retrofit	22CZRK-LD4-24-UNV-L835-CD1-U	2x2 Cruze Retrofit LED, 2400 Lumens, UNV, 3500K, 0-10V 1%-100%		2631	23	080083771318	1	72
	Center Basket 2'x4' Retrofit	24CBRK-42-UNV-L840-CD1-U	2'x4' Center Basket Retrofit Kit		4200	28	080083196203	1	24
	Center Basket Shallow 2'x4'	24RTC4835	2x4 RTC LED Troffer, 4800 lumens, 3500K, 80 CRI (min), 0-10V Dimming		4773	38	080083802623	1	13
		24RTC4840	2x4 RTC LED Troffer, 4800 lumens, 4000K, 80 CRI (min), 0-10V Dimming		4775	38	080083802630	1	13

Brand	Family	Catalog No.	Description	Spec Link	LM	W	UPC	Per Case	Per Pallet	
Ambient Striplights All-Pro	2' Linear LED	2SLSTP2040DD-120V	2' Linear LED Striplight, 2000 lumen, 4000K, 120V Triac Dimmable		2510	23	080083705788	2	144	
		2SLSTP2040DD-UNV	2' Linear LED Striplight, 2000 lumen, 4000K, UNV Triac Dimmable		2510	23	080083807826	2	84	
		2SLSTP2050DD-UNV	2' Linear LED Striplight, 2000 lumen, 5000K, UNV Triac Dimmable		2573	22	080083158928	1	168	
	4' Linear LED	4SLSTP2040DD-UNV	4' Linear LED Striplight, 2000 lumen, 4000K, UNV, 0-10V Dimmable		2410	21	080083705818	2	80	
		4SLSTP2050DD-UNV	4' Linear LED Striplight, 2000 lumen, 5000K, UNV, 0-10V Dimmable		2451	21	080083158935	2	80	
		4SLSTP4040DD-120V	4' Linear LED Striplight, 4000 lumen, 4000K, 120V Triac Dimmable		4474	40	080083705801	2	80	
		4SLSTP5550DD-UNV	4' Linear LED Striplight, 5500 lumen, 5000K, UNV, 0-10V Dimmable		57	49	080083158959	2	80	
	8' Linear LED	8SLSTP11040DD-UNV	8' Linear LED Striplight, 11000 lumen, 4000K, UNV, 0-10V Dim to 10%		10464	83	080083807680	2	70	
		8SLSTP11050DD-UNV	8' Linear LED Striplight, 11000 lumen, 5000K, UNV, 0-10V Dim to 10%		10197	83	080083158973	2	80	
		8SLSTP8035DD-UNV	8' Linear LED Striplight, 8000 lumen, 3500K, UNV, 0-10V Dim to 10%		8064	71	080083804368	2	80	
		8SLSTP8040DD-UNV	8' Linear LED Striplight, 8000 lumen, 4000K, UNV, 0-10V Dim to 10%	MarketPro	8176	71	080083814787	2	70	
		8SLSTP8050DD-UNV	8' Linear LED Striplight, 8000 lumen, 5000K, UNV, 0-10V Dim to 10%		8324	70	080083158966	2	80	
	Ambient Strips Metalux	2' Linear LED	2ST2L2040R	2'LED Striplight, Dual Lens, UNV NO-DIM, 4000K, 120/277V, 2298 lumen		2298	19	080083838172	6	180
		4' Linear LED	4SNLED-LD5-41SL-LW-UNV-L840-CD1-U	4' Linear LED Striplight, 4100 lumen, 4000K, 0-10V Dimmable driver, Full Frost Lens Wide	MarketPro	4204	35	080083817078	1	99
			4ST2L4040	4' Dual Lens Dimming, 4600L 4K CCT	MarketPro	4600	40	080083150984	1	234
8' Linear LED		8ST2L8035R	8' LED Strip, Dual Lens, 8200 Lumen, 3500K, UNV NON-DIM		8200	80	080083890743	6	150	
		8ST2L8040	8' Dual Lens Dimming, 9200L 4K CCT	MarketPro	9200	80	080083151004	1	150	
		8ST2L8050R	8' Dual Lens, White		9412	81	080083890644	6	150	
		8TSNLED-LD5-110HL-LW-UNV-L840-CD1-U	8' Striplight, LED, 11000 lumens, 4000K, 85 CRI, 0-10 volt Dimming Driver, Full Frost Lens Wide		10101	86	-	1	63	
		CITY-8TSLES-2SBDIM-U	8' Socket-fit Light Engine Striplight, 2 Rows, UNV, 0-10V Dimming		8502	70	-	1	50	
Strips Accessory		2SLSTPLNS	2' Replacement Lens for SLSTP Lensed LED		-	-	080083733026	60	720	
		8SLSTPLNS	8' Replacement Lens for SLSTP Lensed LED		-	-	080083814909	50	450	
	SLSTPROW842	Row Aligner 8' - 4' for SLSTP Series		-	-	080083815661	100	3600		

Brand	Family	Catalog No.	Description	Spec Link	LM	W	UPC	Per Case	Per Pallet
Ambient Strips Metalux	Strips Accessory	SLSTPROW88	Row Aligner 8' - 8' for SLSTP Series		-	-	080083815647	50	1800
Ambient Wraparounds Metalux	2' Ceiling Mount	2WP1540C	2' Wrap, 1500 lumens, 4000K, UNV Non-Dimming		1788	16	080083858385	-	-
		2WPLD2035C	2' Wrap, Low Profile, 2400 lumens, 3500K, UNV 0-10V Dimming Driver		2476	22	080083750610	2	120
	4' Ceiling Mount	4WP3040R	4' Wrap, 3432 lumens, 4000K, 120V, Non-Dimming		3432	31	080083847167	6	72
Exit and Emergency All-Pro	Square Heads Combo	AP2SQLED	Wall Mounting Square Head Emergency Lighting; LED, White	MarketPro	80	2	080083824922	12	288
Exit and Emergency Sure-Lites	Emergency NEMA 4X	SELDW60WHSD	LED Emergency, NEMA 4X, wet location, 58' coverage, Self Diagnostic, White		600	5	080083619177	2	120
	Exit and Emergency Commercial Combo LPX	LPX6	LED, White Housing, Universal Face, Red and Green Letters, AC Only		-	-	080083532742	6	144
Outdoor - Lumark Outdoor Parking Garage and Canopy	Canopy Slim Low Profile LED	RPGC25-MS/DIM-L20	LED Canopy Luminaire, UNV, 60W, Motion Sensor for Dimming Operation, 9' - 20' Mounting Height		-	-	080083911820	1	72
Outdoor - Lumark Outdoor Parking Garage Canopy	Canopy Slim Low Profile LED	RPGC25S	Round Parking Garage and Canopy, 31W/49W/63W Selectable, Round Polycarbonate Drop Lens, Quick-Mount Bracket System, 120V-277V, 4000K, White		-	-	080083911769	1	72
Outdoor - Lumark Wall Mount	Wall Pack LED	WPMLED07B	Medium LED Wall Pack, 3500 lumens, 4000k, 80 CRI, Bronze	MarketPro	3500	30	080083175901	2	32
		WPMLED10B	Medium LED Wall Pack, 4800 lumens, 4000k, 80 CRI, Bronze	MarketPro	4800	40	080083175925	2	32
		WPMLED15B	Medium LED Wall Pack, 7100 lumens, 4000k, 80 CRI, Bronze	MarketPro	7100	60	080083175949	2	32
		WPMLED25	Wal-Pak, Stock sku, Medium LED Wall Pack, 80W, 10,200lm (250W equiv.)		10227	80	080083885725	4	32
		WPMLED25B	Medium LED Wall Pack, 12000 lumens, 4000k, 80 CRI, Bronze	MarketPro	12000	100	080083175987	2	32
Outdoor Security & Worklights Floodlights	Motion Solar	MSLED600	180° Single LED Solar Wedge		680	-	080083787104	-	-
Recessed Halo Downlighting	3" Canless EZ-Trim	CEZ3125GU10WBICAT	3" Canless EZ-Trim, GU10 Lamp Base		-	-	080083175512	4	216
		CEZ4125E26WBICAT	4" Canless EZ-Trim, E26 Lamp Base	MarketPro	-	-	080083175550	4	144
		CEZ4125GU10WBICAT	4" Canless EZ-Trim, GU10 Lamp Base	MarketPro	-	-	080083175536	4	168
	4" E44 Series - Housings New Construction	E44MR16ICAT	4" Ultra Shallow Housing, ICAT, 10W MR16, UNV		-	10	080083818327	6	192
	4" Module Retrofit LT Series Trims	LT4069FS351EWHDMR	4" LED Direct Mount, 600 Lumens, 90 CRI 3000K/4000K/5000K Select, 120V, Matte White Flange	MarketPro	600	-	080083159642	4	336
	4" Trims-Module Adj Gimbals DM	HLA406FL9FS1EMWR	4" HLA Adjustable Round Gimbal, White Baffle, 90CRI, 120V, Selectable CCT, 40 degree beam spread	MarketPro	660	11	080083863600	6	504
	4" Trims-Module Retrofit LED DM	LCR4129FSE010MW	4" Round, 1200 Lumens, 90 CRI, 2700 - 5000K Selectable CCT, UNV (120-277), 0-10V, 100% to 5% Dimming, M White	MarketPro	1200	-	08008389002	6	360

Brand	Family	Catalog No.	Description	Spec Link	LM	W	UPC	Per Case	Per Pallet
Recessed Halo Downlighting	5" Module Retrofit LT Series Trims	LTSS560WH9930R-CA	5/6" Retrofit Smooth Splay -Trim LED Module, 900 Lumens, 90CRI, 3000k,White, CA		900	-	080083154029	6	288
	5"-6" Module Retrofit LT Series Trims	LT560WH6930R	5/6" Retrofit Baffle-Trim LED Module, 120V, 90CRI, 3000K, Matte White	 	683	10	080083746187	4	240
	5"-6" Module Retrofit RL Series Trims	RL56069B4AWHVA-CA	RL56 LED module, 600 lumens, 90 CRI, select CCT 2700K - 5000K, BT, Amazon Alexa Voice, T24 Compliant	 	600	13	080083905980	4	240
	6" Canless EZ-Trim	CEZ6125E26WBICAT	6" Canless EZ-Trim, E26 Lamp Base	 	-	-	080083176212	4	96
		CEZ6125GU24WBICAT	6" Canless EZ-Trim, GU24 Lamp Base	 	-	-	080083175574	4	80
		CEZ6126E26WBICAT	6" Canless EZ-Trim, Shallow, E26 Lamp Base	 	-	-	080083176236	4	112
		CEZ6126GU24WBICAT	6" Canless EZ-Trim, Shallow, GU24 Lamp Base	 	-	-	080083175598	4	96
	6" H Series - Housings New Construction	H750FR2ICAT	6" Fire safe new construction LED housing for LED integrated trims or modules		-	-	080083134021	4	80
	6" H Series - Trims Coilex Baffle	310W	6" Trim Coilex Baffle White Trim with White Baffle	 	-	-	080083515882	6	360
	6" Module Retrofit LT Series Trims	LT6089FS231EWHDMR	6" LED Direct Mount, 800 Lumens, 90 CRI 2700K/3000K/3500K Select, 120V, Matte White Flange	 	800	-	080083159963	4	288
		LT6089FS351EWHDMR	6" LED Direct Mount, 800 Lumens, 90 CRI 3000K/4000K/5000K Select, 120V, Matte White Flange	 	800	-	080083159666	4	288
	6" RL QuickLink Direct Mount	RLQL6069SE010DM-8PK	6" LED RL-DM QuickLink 8-pack with Remote Driver, J-Box, Low Voltage Cable, 120-277V, 0-10V 5% Dimming, 2700-5000 CCT	 	600	7	080083182305	1	32
	6" Trims-Modules Surface DM	HLBPH6099FS1EMWR	6" LED Smooth Lens Downlight, 900 Lumens, Round Soft Lens, Remote Driver, Junction Box, 120v	 	900	-	080083190027	4	600
	7" Trims-Modules Surface	CLD7089SWHR	7" CLD, 800 lumens, 3 SeleCCTable	 	810	11	080083856763	-	-
8" Trims-LED Direct Mount	LCR8809FSE010MW	8" All Purpose Round LED Module, 8000 Lumens, 90 CRI, FS, 120-277v, 50/60Hz, 0-10V Analog 100% to 5% Dimming	 	8000	96	080083890125	4	128	

NOW OR NEVER

because it is not forever!

Lighting Product Lines

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Product Lines

Fifth Light Technology
Greengate
iLight (International Only)
iLumin
Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power
HALO Home
iLumin Plus
LumaWatt Pro
WaveLinx
Trellix



Cooper Lighting Solutions
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.cooperlighting.com

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2022 Cooper Lighting Solutions
All Rights Reserved
Printed in USA
Publication No. CA525770

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.