



## RL Recessed LED Trim

- 3", 4", 5"/6" Recessed LED Trim
- Baffle and LED Trim with regressed lens
- 5 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K
- D2W- Dim-To-Warm Technology included: use your dimmer to warm color temperature from 3000K-1500K
- Selectable Lumen options available: 4" 600/900 Lumens, 6" 900/1200
- Compatible with most recessed housings



[LEARN MORE](#)



## RL Canless Downlight

- 4", 6" canless downlights
- Baffle and LED Trim with regressed lens
- 5 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K
- D2W- Dim-To-Warm Technology included: use your dimmer to warm color temperature from 3000K-1500K
- Selectable Lumen options available: 4" 600/900 Lumens, 6" 900/1200



[LEARN MORE](#)



## Night Light

- 4", 6" Canless downlights
- Baffle and LED Trim with regressed lens
- 5 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K
- D2W- Dim-To-Warm Technology included: use your dimmer to warm color temperature from 3000K-1500K



[LEARN MORE](#)



## ML56 Series

- Downlight system of LED modules and trims
- 5" and 6" Designer trims
- 5 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K
- D2W- Dim-To-Warm Technology included: use your dimmer to warm color temperature from 3000K-1500K
- Selectable Lumen from 400 - 1500 lumens
- Use with 5" or 6" new construction or remodel housings or retrofit with screwbase adapter
- 25°, 40°, 55° and 75° field installable TIR optics available



[LEARN MORE](#)



## LCR Series

- 2", 4", 6", 8" Canless downlights
- 6 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K, 6500K
- Wall Wash option in 4" and 6"
- Emergency Battery pack option for 4", 6" and 8"
- Residential and Commercial applications



[LEARN MORE](#)



## HLB Smart Wi-Fi Slim Canless Downlight WiZ Pro

- 4", 6" Canless downlights
- Smart Wi-Fi lighting provides white tuning and 16 million colors
- Easy to use app to control lighting, set schedules, and rhythms
- Compatible with all Connected by WiZ and WiZ Pro products



[LEARN MORE](#)



## HLS Series

- 4", 6", 9", 9" w/motion sensor
- 5 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K
- D2W- Dim-To-Warm Technology included: use your dimmer to warm color temperature from 3000K-1500K
- Selectable Lumen options available: 4" 600/900 Lumens, 6" 900/1200
- Compatible with most recessed housings



[LEARN MORE](#)



## FM Series

- 8", 11", 15" Flushmount
- 3 Color Field selectable CCT: 3000K, 4000K, 5000K - 8" fixture
- 5 Color Field selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K - 11" & 15" fixture
- Retrofit ready to fit 5" and 6" incandescent housings



[LEARN MORE](#)



## HLBE Series

- 4", 6" Canless downlights
- Polymer trim with smooth lens
- Fixed 3000K soft white color temperature
- Ultra-slim 1/2" thin design and installs in 2x2 plenum space
- Sold in contractor friendly bulk packs of 12 and 24 units




[LEARN MORE](#)




## RL Smart Wi-Fi Recessed LED Trims WiZ Pro

- 4", 6" Recessed LED Trim
- Baffle and LED Trim with regressed lens
- Smart Wi-Fi lighting provides white tuning and 16 million colors
- Easy to use app to control lighting, set schedules, and rhythms
- Compatible with all Connected by WiZ and WiZ Pro products
- Easily installs in most housings with flexible mounting hardware and standard medium E26 socket adapter



[LEARN MORE](#)



## Black Designer Trims

- Black trims added to the following HALO product families:
  - SMD Series
  - HLB Series
  - HLA Series
  - RL Series
  - LCR Series
- The addition of black designer trims was a result of Cooper Lighting Solutions Insights



[LEARN MORE](#)  
Insights



## ML4 Series

- 4" Canless or retrofit, Downlight, wall wash, accent/task distributions
- 5 Color Selectable CCT: 2700K, 3000K, 3500K, 4000K, 5000K
- D2W Field Selectable: 3000K-1800K, 2700K-1800K
- Field-interchangeable round and square 2-inch pinhole aperture trims
- Die-formed steel trims, Magnetic attachment, Painted, plated finishes
- Distributions: spot, narrow flood, flood and very wide flood



[LEARN MORE](#)