

Description

The HALO Home Smart Plug-In Lamp Dimmer enables convenient control for standard floor and table lamps from the Smart Plug-in Dimmer or the HALO Home mobile app. Combine with more HALO Home light fixtures and accessories to create groups and scenes throughout the home.

Catalog #		Type
Project		
Comments		Date
Prepared by		

Specification Features

Features

- Manual ON/OFF and brightness control with the side panel push button
- Using the HALO Home app and the Lamp Dimmer lighting device has the following capabilities:
 - On/Off
 - Dimming
 - Groups
 - Scheduling
 - Scenes

Driver

- Grounded 3-wire power connection for safety
- Power: 120VAC, 60Hz
- For use with 110/120V compatible sockets

Compatible Products

- 2.5A; 300W Incandescent or 150W Dimmable CFL/LED
- Maximum load for the Bluetooth-controlled outlet: 2.5A, 300W Incandescent or 150W Dimmable CFL/LED.

Factory Reset

- Hold the ON button for more than 15 seconds
- Constant flashing of blue status indicator light indicates successful reset.


Compliance

- cULus certified
- EMI/RFI emissions per FCC 47CFR Part 15 consumer limits
- Operating Temperature Range: -30 C to +45C

Warranty

Five year limited warranty, consult website for details.
eaton.com/lighting/legal

Dimensions



Ordering Information

SAMPLE NUMBER: HWP1BLE40AWH

Device	Driver	Finish
HWP1 = Wall Adapter Plug	BLE40A=Bluetooth wireless mesh 4.0 control	WH=White



**HALO Home
HWP1**

**Smart Plug-In Lamp
Dimmer**

