

Axcent LED wall mount luminaire

Features and benefits

Lumark



Sleek architectural design with superior performance.

The Axcent LED wall mount luminaire provides a flush-mounted, architectural design with high performing, energy-efficient illumination resulting in up to 95% energy and maintenance savings. The die-cast aluminum construction along with stainless steel hardware, gasketed housing, and sealed optical compartment make the Axcent impervious to contaminants. The Axcent replaces 70W up to 450W metal halide equivalents making it ideal for pathway illumination, building entrances, vehicle ramps, schools, tunnels, stairways, loading docks and floodlighting applications.

Key features:

- Save up to 95% in energy and maintenance costs over traditional metal halide solutions
- Hook-N-Lock mounting eliminates the need to open the factory-sealed and vacuum tested luminaire. Allows for installation without requiring any additional caulking or silicone to seal the luminaire
- Superior optical design in both full cutoff and refractive lens versions provide superior illumination and efficacies of up to 144 lm/W
- Further maximize energy savings and meet code requirements by utilizing the integrated controlled and connected solutions

Design features



Easy Installation

Contractor-friendly installation with wedge mounting plate and fixture wire hook.




Controls

Integrated photocontrol, motion sensor, or connected controls solutions available.



Emergency Egress

Optional integrated emergency egress for up to 90-minutes of emergency operation.



Quick facts:

- 120 - 277V (Standard); 347V, 480V
- Standard 0 - 10V dimming
- Lumen packages ranging from 1,800 - 17,000 lumens
- 4000K / 70 CRI (Standard); 5000K / 70 CRI, 3000K / 80 CRI
- Wall mount, inverted mount, floodlight, and pole mount options
- IP66 rated, UL/cUL wet location listed

Learn more about our outdoor lighting solutions at www.eaton.com/lighting



Powering Business Worldwide

Axcent LED wall mount luminaire

Features and benefits

Lumark

Stock ordering information

Model	Input Watts	Lumens	Efficacy	HID Equivalent	UPC
Axcent Small					
AXCS1A	14W	1,806	134	70W	080083887965
AXCS1ARL	14W	1,915	142	70W	080083887972
AXCS2A	21W	2,561	124	100W	080083887989
AXCS2ARL	21W	2,716	131	100W	080083887996
AXCS3A	27W	3,537	132	150W	080083888009
AXCS3ARL	27W	3,704	139	150W	080083888016
AXCS4A	44W	5,520	126	250W	080083888023
AXCS4ARL	44W	5,858	139	250W	080083888030
AXCS5A	52W	6,300	121	320W	080083888047
AXCS5ARL	52W	6,699	131	320W	080083888054
Axcent Large					
AXCL6A	56W	7,594	136	320W	080083811564
AXCL6ARL	56W	7,809	139	320W	080083811649
AXCL8A	72W	9,696	135	400W	080083811588
AXCL8ARL	72W	9,970	139	400W	080083811663
AXCL10A	102W	13,283	133	400W	080083811601
AXCL10ARL	102W	13,641	131	400W	080083811687
AXCL12A	123W	16,823	140	450W	080083811625
AXCL12ARL	123W	17,346	144	450W	080083811700

Mounting configurations

Axcent Small



Slipfitter Mount



Trunnion Mount



Knuckle Mount

Axcent Large



Slipfitter Mount



Trunnion Mount



Pole Mount



Powering Business Worldwide

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. SA514018EN
May 9, 2019 9:40 AM

Eaton is a registered trademark.
All other trademarks are property of their respective owners.
Product availability, specifications, and compliances are subject to change without notice.