

METALUX AMBIENT COMMERCIAL



Troffer
p. 33-36



Strip
p. 36



Wrap
p. 37



Flushmount
p. 37



Cruze ST Recessed LED Luminaire

Metalux

- Architectural center basket lens troffer with aesthetic appeal
- Latch-less design provides clean architectural look; Ribbed, frosted acrylic lens
- High-performance LED system with advanced light distribution
- Refined finish; Unmatched value
- Ideal choice for commercial, institutional and healthcare facilities



Rapid Response



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
22CZ2-32-UNV-L835-CD1-U	2'x2', Troffer	2-T5, 2-T8	3500K	120/277V	3,280	26	48	080083881185	PL057CFW (120V) , P15VC648 (277V)
22CZ2-32-UNV-L840-CD1-U	2'x2', Troffer	2-T5, 2-T8	4000K	120/277V	3,280	26	56	080083881208	P030DW27 (120V) , P8GWVUDUZ (277V)
22CZ2-34HE-UNV-L835-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	3500K	120/277V	3386	26	28	080083881222	P6ZEZIGY
22CZ2-34HE-UNV-L840-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	4000K	120/277V	3386	26	48	080083881260	PMRQB66T
22CZ2-39-UNV-L835-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	3500K	120/277V	3,943	34	48	080083881284	P0AXJUK1
22CZ2-39-UNV-L840-CD1-U	2'x2', Troffer	3-T8, 4-T8, 2-T5HO	4000K	120/277V	3,943	34	48	080083881307	PU7UA6BJ
24CZ2-40-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 3-T8	3500K	120/277V	4,196	36	26	080083881505	PUDYNNME
24CZ2-40-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 3-T8	4000K	120/277V	4,196	36	28	080083881529	PWWGAYMY
24CZ2-50-UNV-L835-CD1-U	2'x4', Troffer	2-T8, 2-T5	3500K	120/277V	5,015	48	26	080083881628	POK3FN8Z
24CZ2-50-UNV-L840-CD1-U	2'x4', Troffer	2-T8, 2-T5	4000K	120/277V	5,015	48	26	080083881642	PI0YCHQ9

Note: DLC Premium items are noted in bold.

Features	Benefits
Latchless-design with no visible hinges	Improved aesthetic to delight specifiers
Standard matte white paint from corner to corner	Improved aesthetic to delight specifiers
Large J Box with standard access plate and trade size knockouts	Easier wiring access to delight contractors
Hemmed side flanges	Easier handling during installation to delight contractors
Linear disconnect included	Easier installation to delight contractors
Multiple sizes available (2'x2', 2'x4' in standard 3.25" depth & 1'x4' shallow 2.25" depth)	Enables fixture matching in spaces
Grid lock feature included in the endplate with available "earthquake clip" accessory	Helps meet building codes

Cruze LED Recessed Retrofit Kit

Metalux

- Upgrade 2' x 4' fluorescent luminaires to a high-performing LED system
- Engineered for simple and quick installation (less than 5 minutes); Labor savings
- Tool-less installation
- Uses the fluorescent luminaire's housing resulting in lower disposal costs
- Architectural style aesthetics for multiple applications



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
24CZRK-LD4-40-UNV-L840-CD1-U	2'x4' Center Basket Retrofit Kit	2-T8, 3-T8	4000K	120/277V	4,423	37	36	080083804610	P6J3B352

Note: Fixture housing not included; DLC Premium items are noted in bold.

Troffer

Encounter LED Series

Metalux

- Leverages patented WaveStream™ Technology with AccuAim™ optics
- Contemporary styling; Advanced optical control
- Optimal light uniformity, resulting in soft, natural light for superior visual comfort
- Over 60% energy savings when compared to fluorescent troffers
- Ideal choice for commercial interiors



Rapid Response



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
22EN-LD2-34-UNV-L835-CD1-U	2'x4', Recessed Troffer	3-T8, 4-T8, 2-T5HO	3500K	120/277V	3,471	29	40	080083752324	PUJBJAKE
22EN-LD2-34-UNV-L840-CD1-U	2'x4', Recessed Troffer	3-T8, 4-T8, 2-T5HO	4000K	120/277V	3,540	29	36	080083752317	PSRD33BV , PXJ7Q3QF
24EN-LD2-45-UNV-L835-CD1-U	2'x2', Recessed Troffer	2-T8, 3-T8	3500K	120/277V	4,656	38	18	080083752225	PYDG9S8N , PNGQ7GTA
24EN-LD2-45-UNV-L840-CD1-U	2'x2', Recessed Troffer	2-T8, 3-T8	4000K	120/277V	4,748	38	20	080083752218	PF2T7Y87 , PUGD2UQG

Note: DLC Premium items are noted in bold.

Troffer

SkyRidge LED Series

Metalux

- Leverages patented WaveStream™ Technology with AccuAim™ optics
- Affordable, aesthetically pleasing alternative to fluorescent fixtures
- Advanced optical control with optimal illumination
- Over 60% energy savings when compared to fluorescent troffers
- Ideal choice for commercial interiors



Rapid Response



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
22SR-LD2-29-C-UNV-L835-CD1-U	2'x2', Recessed Troffer	2-T5, 2-T8	3500K	120/277V	3,095	23	28	080083752584	PL2K2CYL(120V) , PURGNZ9E(277V)
22SR-LD2-29-C-UNV-L840-CD1-U	2'x2', Recessed Troffer	2-T5, 2-T8	4000K	120/277V	3,157	23	28	080083752577	PSRAE17C
24SR-LD2-48-C-UNV-L835-CD1-U	2'x4', Recessed Troffer	2-T8, 2-T5	3500K	120/277V	4,805	38	16	080083752492	P6V4CWNY
24SR-LD2-48-C-UNV-L840-CD1-U	2'x4', Recessed Troffer	2-T8, 2-T5	4000K	120/277V	4,901	38	16	080083752485	PDLK7ZMQ

Note: DLC Premium items are noted in bold.

RBG LED Series

Metalux

- Architectural elegant 6-inch grid, 4-inch aperture fixture
- Recessed, surface or suspension mounting
- Field-selectable CCT: 3000K, 3500K, 4000K via a switch
- 3 field-selectable lumens and watts via a switch; Flexibility to changing needs of a space
- Use for open and traditional offices, classrooms, coves, corridors, retail or anywhere stylish lines of light are desired



Catalog Number	Product Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts (HI)	Pallet Quantity	UPC	DLC Product ID
4RBG6-SL1-L8SCT3	4' Length	2-F32T8, 1-F54T5HO, 2-F28T5	3000K/3500K/4000K	120-227V	500/750/1,000*	36	75	080083866465	PUREBLSF, PSMWARPL, PW27GGE8

*Lumens per ft.

CGT LED Panel Series

Metalux

- Affordable panel that fits in shallow plenums with room to spare; Thin 2 1/8 inch height
- Robust die-formed steel housing is post-painted for maximum durability
- Acrylic micro optics provide uniform illumination from corner to corner
- Extruded aluminum bezel with mitered corners tightly sealed to housing for durability
- Ideal for office spaces, schools, healthcare and retail merchandising areas



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
22CGT3535C	2'x2' Recessed Panel	3-T8	3500K	120/277V	3,449	32	72	080083880003	P6WE1HNZ
22CGT3540C	2'x2' Recessed Panel	3-T8	4000K	120/277V	3,582	32	72	080083880027	P0YGNM7S
24CGT4535C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120/277V	4,268	38	36	080083880089	P28JP113
24CGT4540C	2'x4' Recessed Panel	2-T8, 3-T8	4000K	120/277V	4,432	38	18	080083880102	PLTEVMIJ
24CGT5535C	2'x4' Recessed Panel	3-T8, 4-T8	3500K	120/277V	5,139	47	36	080083880164	PGQBATOL
24CGT5540C	2'x4' Recessed Panel	3-T8, 4-T8	4000K	120/277V	5,337	47	36	080083880188	P5F04P82

FPS LED Panel Series

Metalux

- Ultra-thin, high-performance flat panel; Less than 2-inches height for shallow plenums
- Up to 120 lm/W; Field-selectable CCT: 3000K, 3500K, 4000K via a switch
- 3 field-selectable lumens and watts via a switch; Flexibility to changing needs of a space
- Integrated grid retention clips provide installation speed and flexibility
- Solution for office spaces, schools, healthcare facilities and retail merchandising areas



Catalog Number	Product Description	Replaces Up To	Selectable CCT	Voltage	Selectable Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
22FPSL2SCT3	2'x2' Recessed Panel	3-T8	3000K/3500K/4000K	120/277V	1,800-3,300	16	40	080083889402	PIBWK9P9, PB32RP9H, PJQG8V0T
24FPSL2SCT3	2'x4' Recessed Panel	2-T8, 3-T8	3000K/3500K/4000K	120/277V	3,400-6,400	30.2	20	080083889365	PK4M6K93, PZFJCMXS, PU0HKZ87

FPanel LED Panel Series

Metalux

- Ultra-thin flat panel; Less than 2-inches height for shallow plenums
- Easy to install, wire and wire nuts included
- Refined visual optics, superior acrylic light guide; uniform corner to corner illumination
- Integrated grid retention clips provide installation speed and flexibility
- Solution for office spaces, schools, healthcare facilities and retail merchandising areas



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
22FP3235C	2'x2' Recessed Panel	3-T8	3500K	120/277V	3307	29	44	080083833528	PQC9IUIC
22FP3240C	2'x2' Recessed Panel	3-T8	4000K	120/277V	3,560	30	44	080083833542	PUOIG6S2
22FP4235C	2'x2' Recessed Panel	2-U6T8	3500K	120/277V	4,641	39	44	080083833580	P8HIK308
22FP4240C	2'x2' Recessed Panel	3-U6T8	4000K	120/277V	4,567	39	44	080083833603	PELH4PNQ
24FP4735C	2'x4' Recessed Panel	2-T8, 3-T8	3500K	120/277V	4,990	40	22	080083833641	PRZ2RGDY
24FP4740C	2'x4' Recessed Panel	2-T8, 3-T9	4000K	120/277V	4,858	40	22	080083833665	PGY6ID6B
24FP6440C	2'x4' Recessed Panel	3-T8, 4-T9	4000K	120/277V	6,611	59	22	080083833726	PUQIRODO

Troffer

GRLED Series

Metalux

- Built and designed for general purpose lighting applications
- Shallow, low-profile housing, makes it compatible with highly restrictive plenums
- Traditional prismatic A12 lens and door assembly; Insulated ceiling (IC) rated
- Easy to install; Fits most T-grid systems; Below the ceiling maintenance
- Great choice for commercial offices, schools, hospitals, retail and more applications



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
24GR-LD5-48-F1-UNV-L840-CD1-U	2'x4' A Lens Troffer	2-T8	4000K	120/277V	4,800	43	28	080083817153	PF64UQWQ

Note: DLC Premium items are noted in bold.

SLSTP LED Striplight Series

Metalux

- Low-profile, high-quality luminaire with latest LED and electronic driver technology
- Frost white polycarbonate lens with linear prisms for even illumination
- Single lens eliminates the tandem appearance
- Quick installation features; Ideal for single or continuous row applications
- Perfect solution for restricted spaces and for stock and design build application



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
4SLSTP4040DD-UNV	4' Single Lens	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4,000	43	72	080083705825	PXZQGN9C, PPA1YS12
8SLSTP11040DD-UNV	8' Single Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	10,464	83	70	080083807680	PWA7BZM9, PUOOP0M3
8SLSTP8040DD-UNV	8' Single Lens	4T8 32W, 2-T12 75W	4000K	120/277V	8,176	71	70	080083814787	POK8WFD1, PARMCVA1

Troffer/Strip

ST LED Striplights

Metalux

- Full-width LED strip light; Ideal for replacing single or 2-lamp fluorescent strip lights
- Superior performance with lumens up to 9400 and 123 lm/W
- Tool-less channel cover; Unique single or dual lens tube design
- Surface or suspended mounting; Wireless access from below
- Continuous row mount aligner included to add-on length as needed regardless of application or layout



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
2ST1L1040R	2' Single Lens	1-T8 17W	4000K	120/277V	1,165	10	288	080083838165	PLYWPPTN5MXA
2ST2L2040R	2' Dual Lens	2-T8 17W	4000K	120/277V	2,298	19	180	080083838172	PLT3RHMTZ063
4ST1L2040R	4' Single Lens	1-T8 32W	4000K	120/277V	2,298	20	252	080083838189	PLALG17SBDJR
4ST2L4040R	4' Dual Lens	2-T8 32W, 1-T5HO 54W	4000K	120/277V	4,433	39	150	080083838196	PLT1KD8JM2VZ
8ST2L8040R	8' Dual Lens	4-T8 32W, 2-T12 75W	4000K	120/277V	8,867	78	150	080083838202	PL5RGM59H32E

WNLED Wraparound Series

Metalux

- Utility commercial LED wraparound; Single or continuous row applications
- Frosted lens offers best-in-class uniform illumination
- Use in a broad range of commercial, schools, institutional, retail and residential applications
- Provides long service life, eliminating re-lamping issues and minimizing maintenance common with traditional fluorescent



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
4WNLED-LD4-40SL-F-UNV-L840-CD1-U	4' Linear Wrap	2-T12, 2-T8 32W	4000K	120/277V	4,062	36	85	080083756889	PK3W95DW

CWPLD LED Wraparound Series

Metalux

- Versatile, commercial model, low-profile LED wraparound
- Premium optical linear prisms provide even and wide distribution, minimizing fixtures required
- Surface, wall, suspended and row mounting; Quick row mounting channel
- Trade sized knock outs included for "hard pipe" wiring through ends
- Mounts over the most common junction boxes



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
4CWPLD4040C	4' Commercial	2-T12, 2-T8	4000K	120/277V	4,700	43	60	080083749072	P5SLI38B, PER729JP

WPLD LED Wraparound Series

Metalux

- Streamlined, low-profile design
- Smooth lens provides soft, uniform, glare-free light output
- Providing up to 60% energy savings over fluorescent light sources
- Suitable for ceiling, wall or suspension mounting
- Mounting slots allow for installation directly into the junction box with 100° of rotational freedom



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
4WPLD4035C	4' Low Profile	2-T8 32W	3500K	120/277V	4,000	45	84	080083750603	PZ4NNCFK
4WPLD4040C	4' Low Profile	2-T8 32W	4000K	120/277V	4,603	42	84	080083749676	PYGI6R4N

WP LED Wraparound Series

Metalux

- Compact LED wrap light delivers value and energy savings
- Perfect retrofit solution for replacing single or 2-lamp fluorescent wraparounds
- Low-profile, highly versatile design; Post-painted die-formed channel
- Prismatic lens ensures even, glare-free light distribution
- Ideal for commercial applications from schools and dorms to warehouses and retail areas



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	DLC Product ID
4WP3040C	4' Linear Utility	2-T8 32W	4000K	120/277V	3,400	31	72	080083858361	PC1Y20YN

FM LED Dimming Flushmounts

Metalux

- Versatile ceiling- or wall-mount series for a broad range of residential and commercial applications
- Full frost, opal white lens provides optimal light output with no pixilation
- Even, uniform light distribution; Easy lens installation
- Ideal for offices, corridors, stairways, bedroom, closet and foyers applications where customers are replacing incandescent, circline or compact fluorescent lamps



Catalog Number	Product Description	Replaces Up To	CCT	Voltage	Lumens	Watts	Pallet Quantity	UPC	ENERGY STAR Unique ID
FM11WRCCR	11" Flushmount, Round	22 W T9 Circline	3000K/4000K/5000K	120V	1,100	14	72	080083840151	2324855
FM15WRCCR	15" Flushmount, Round	100W INC or 32W T9 Circline	3000K/4000K/5000K	120V	1,800	22	32	080083845378	2324853

Wrap/Flushmount