

SURE-LITES | ALL-PRO | ATLITE

EXIT & EMERGENCY



Sure-Lites
p. 49-51



All-Pro
p. 51-52



AtLite
p. 52



SEL LED Emergency Lighting

Sure-Lites

- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™
- Injection-molded, high-impact thermoplastic
- Long life LED's, No maintenance nickel cadmium battery
- EZ hang feature reduces installation time and cost



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
SEL17	2 Head, NiCad	White	2-5.4W Inc. Heads	17 ft.	120-277V	0.78W	270	080083722143
SEL25	2 Head, NiCad	White	2-9W Inc. Heads	25 ft.	120-277V	0.6W/0.64W	270	080083736669
SEL25SD	2 Head, NiCad, Self Diagnostic	White	2-9W Inc. Heads	25 ft.	120-277V	0.67	324	080083723027
SEL50	2 Head, NiCad	White	2-12W Inc. Heads	50 ft.	120-277V	1W/1.02W	324	080083733347
SEL50SD	2 Head, NiCad, Self Diagnostic	White	2-12W Inc. Heads	50 ft.	120-277V	1.19	270	080083733361

AP2SQ Emergency Lighting

Sure-Lites

- LED emergency light with a minimum of 90 minutes of run time
- Compact form factor optimizes aesthetics
- Adjustable square heads maximize design flexibility; Each head outputs 80 lumens
- No maintenance nickel cadmium battery
- Universal j-box mounting pattern and snap-fit polycarbonate housing construction reduces installation time



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
AP2SQLLED	2 Head, NiCad	White	2-5W Inc.Heads	12 ft.	120/277V	2 at 277V	288	080083824922

SELW LED Outdoor Emergency Lighting

Sure-Lites

- Code compliant, wet location for outdoor use; Standard 0°C to 40°C temperature rating
- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™; 25 feet of emergency egress coverage
- Injection-molded, high-impact thermoplastic
- Long life LED's, No maintenance nickel cadmium battery



SELW25BZ



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
SELW25BZ	2 Rotatable Heads, NiCad	Bronze	2-9 W INC Heads	25 ft.	120-277V	1.4	224	080083764037




Exit & Emergency

XR LED Emergency Lighting

Sure-Lites

- Emergency light with minimum of 90 minutes runtime; Chicago and New York City compliant
- 20-gauge sheet metal housing; Heads are fully adjustable and 300 lumens each
- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™, No maintenance nickel cadmium battery
- External battery disconnect and EZ Hang feature reduces installation time and cost



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
XR6C-LED	Steel, NiCad	White	2-12W INC Heads	60 ft.	120-277V	1.7	144	080083753215

SELMTG LED Emergency Lighting

Sure-Lites

- Architectural emergency light; Up to 60-feet of coverage; Rugged sheet metal housing
- Designed to reduce egress system cost and maintenance and improve reliability
- Proprietary adjustable AccuLED Optics™; Recessed heads to eliminate ceiling disruption
- Self-diagnostic automatically performs NFPA required testing; City of Chicago and New York City compliant
- External battery disconnect and EZ Hang features reduce installation time and cost



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
SELMTG60R5SD	2 Rotatable Heads, NiCad, Self Diag.	White	2-12 W INC Heads	60 ft.	120-277V	5	168	080083823406

CHX Exit Signage

Sure-Lites

- Chicago code compliant exits are ideal for general purpose applications
- Extensive range of field-installed accessories and choice of faces
- Ceiling and end mounting; Lens installs from side of fixture for convenient maintenance
- Durable steel construction and attractive styling
- High-efficiency illumination; Compatible in commercial, institutional and multi-housing applications



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
CHX71	Self Powered, Steel	White	2-12 W INC Heads	N/A	120/277V	3	120	080083567614
CHXC71	Self Powered Combo Unit, Steel	White	2-12 W INC Heads	60 ft.	120/277V	3.6	90	080083771271

EBP LED Emergency Battery Packs

Sure-Lites

- Battery Pack automatically switches to emergency mode when AC power fails
- Maintains illumination of an LED fixture for a minimum of 90 minutes
- UL 924 classified for field retrofit installation
- Guaranteed compatibility with Cooper Lighting Solutions' LED fixtures with accessible LED drivers



Catalog Number	Product Description	Voltage	Watts	Pallet Quantity	UPC
EBPLED7W	Emergency Battery Pack	120/277V	7	240	080083732265
EBPLED14W	Emergency Battery Pack	120/277V	14	288	080083732272
EBPLED-7.5WSD	Emergency Battery Pack	120/277V	7.5	210	080083158621
EBPLEDLP-10WSD	Emergency Battery Pack	120/277V	10	400	080083158645

EBP Fluorescent Emergency Battery Packs

Sure-Lites

- Battery Pack automatically switches to emergency mode when AC power fails
- Powers a fluorescent lamp for 90 minutes during a power outage
- UL 924 classified for field retrofit installation
- Compatible with most linear fluorescent lamps



Catalog Number	Product Description	Voltage	Watts	Pallet Quantity	UPC
EBP500	Emergency Battery Pack	120/277V	2.7	576	080083906741
EBP1400	Emergency Battery Pack	120/277V	3.8	432	080083912162

APEL LED Emergency Lighting

All-Pro

- Emergency light with a minimum of 90 minutes of run time
- No maintenance nickel cadmium battery
- Fully adjustable LED heads maximizes design flexibility
- Compact form factor optimizes aesthetics; Components are injection-molded, high impact thermoplastic
- Universal j-box mounting pattern and snap-fit housing construction reduce installation time



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
APEL	2 Head, NiCad	White	2-5.4W Inc. Heads	17 ft.	120/277V	0.47W at 277V	384	080083566501
APELH2	2 Head, Nicad, Remote Capacity	White	4-5.4 W INC Heads	34 ft.	120/277V	0.8 W at 277 V	512	080083804986

Exit & Emergency

APX LED Exit Signage

All-Pro

- Economical LED exit sign for general purpose applications
- Durable, injection-molded, thermoplastic material resists discoloration due to UV radiation
- Energy-efficient, low-maintenance LED's provide bright illumination
- Universal configurations (single- and double-face); Universal mounting (ceiling, wall and end)



Catalog Number	Product Description	Finish	Voltage	Watts	Pallet Quantity	UPC
APX7G	Self Powered, Unv. Green	White	120/277V	1.05W at 277V	270	080083566549
APX7R	Self Powered, Unv. Red	White	120/277V	1.14W at 277V	270	080083566532

APC LED EM Combo Light

All-Pro

- Economical LED combo unit; Exit and LED emergency lighting heads
- Durable, injection-molded, thermoplastic material resists discoloration due to UV radiation
- Energy-efficient, low-maintenance LED's provide bright illumination
- Universal configurations (single- and double-face); Universal mounting (ceiling, wall and end)
- Low-voltage disconnect, Line-Latched; Brownout circuit



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
APC7G	2 Heads, Unv. Green	White	2-5.4W Inc. Heads	17 ft.	120/277V	1.68W at 277V	192	080083567164
APC7R	2 Heads, Unv. Red	White	2-5.4W Inc. Heads	17 ft.	120/277V	1.68W at 277V	192	080083566556
APCH7G	2 Heads, Unv. Green, Remote Cap.	White	4-5.4W Inc. Heads	34 ft.	120/277V	1.68W at 277V	192	080083567188
APCH7R	2 Heads, Unv. Red, Remote Cap.	White	4-5.4W Inc. Heads	34 ft.	120/277V	1.68W at 277V	192	080083567171

APWR LED Remote Heads

All-Pro

- Emergency lighting remote heads unit; Allows for 17 feet of emergency egress coverage
- Adjustable heads adjust 80° from vertical with 358° rotation
- Wet location listed and can be used indoors or outdoors
- Injection-molded thermoplastic material
- Universal mounting plate; Flame-resistant and impact-resistant



Catalog Number	Product Description	Finish	Replaces Up To	Coverage	Voltage	Watts	Pallet Quantity	UPC
APWR2	Remote Emergency Lamps, 2 Heads	White	2-5.4W Inc. Heads	17 ft.	3.6V	1W	810	080083608584

AUX LED Edge-Lit Exit Signage

AtLite

- Edge-lit Exit allows seamless presence in architecturally significant surroundings
- Eagle Eye self-diagnostics; New York City compliant
- Universal mounting; Universal Lens (clear, mirror, white and single- and double-sided)
- Ordering and installation simplified as all housing and lens options are included



Catalog Number	Product Description	Finish	Voltage	Watts	Pallet Quantity	UPC
AUXSSD	Unv. Self powered, Self Diag.	Silver	120/277V	1.1 at 277 V	50	080083703296

Exit & Emergency



Exit &
Emergency