

**Discrete LED solution.
Energy conscious illumination.**

The Archeon™ Medium LED roadway luminaire delivers all the performance benefits of the latest Eaton LED platforms and technologies with a modern, yet familiar cobrahead form factor. This discrete LED solution with the patented, high-efficiency AccuLED Optics™ system, provides uniform and energy conscious illumination for municipal streets and highways. Our customer focused features include single latch tool-less entry to serviceable components, industry leading surge protection options, with superior lumen maintenance and performance, all in an economical, architectural design.

Key features:

- Up to 147 lumens per watt
- Four optical distributions (Type II, III, IV and V), that are precisely designed to shape the distribution, maximizing efficiency and fixture spacing
- Multiple lumen packages ranging from 5,000 - 21,000 delivered lumens
- 4000K CCT standard with minimum 70 CRI, optional 2700K (80 CRI), 3000K (70 CRI) and 5000K CCT (70 CRI)
- Optional 3 or 7-PIN NEMA twistlock photocontrol receptacle (ANSI-C131.41)
- Tool-less access for ease of installation and maintenance
- Standard with three-position tunnel compression type terminal block




Quick facts:

- Replaces up to 100-400W equivalent HID
- 0-10V dimming driver standard (Optional DALI)
- 3G vibration rated
- IP66 rated optics
- Universal voltage (120-277V 50/60 Hz)
- Operates at -40°C to +40°C (-40°F to 104°F), limited 50°C high ambient option available
- Five-year warranty
- Dimensions: 30-1/2" (L), 12-1/2" (W), 5-1/4" (H)
- EPA (Sq. Ft.): 0.71
- Weight: 18 lbs. (8.16 kgs.)

Learn more about our outdoor lighting solutions at www.eaton.com/lighting

Design features



Maintenance

Standard metal latch, tool-less entry, quick disconnects and safety door lanyard. Available with 10MSP or 10kV surge option.



Optics

Discrete LEDs available with optional house side shield.



Surge Protection

Standard UL 1449 Listed 10kV/10kA surge protective device protects against common (line-to-ground) and differential (line-to-line) mode surges.

up to
71%
SAVINGS
on lighting energy costs

Efficacy

Up to 71 percent savings over comparable HID fixtures.



Powering Business Worldwide

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. SA521002EN
November 15, 2018 10:38 AM

Eaton is a registered trademark.
All other trademarks are property of their respective owners.
Product availability, specifications, and compliances are subject to change without notice.