

LED Area and Wall Lighting

Dusk to Dawn Security Lighting

HALO®

The HALO LED Area and Wall Light incorporates patented optics and advanced LED technology into a heavy duty die-cast aluminum housing built for long lasting performance.

Available with integrated or NEMA twist lock photocontrols, these dusk-to-dawn fixtures were designed to replace and outperform traditional lamp sources, from 65W CFL all the way up to 175W mercury vapor, generating significant energy savings while reducing maintenance costs.

Features

- Maintenance-free LEDs with rated life of 50,000 hours
- Patented precision over-optics and reflector for maximum output
- Photo control provides nighttime ON/ daytime OFF
- Heavy-duty corrosion resistant die-cast metal construction
- Sturdy mounting arm installs to walls or poles
- Perfect security lighting for barns and outdoor dark, secluded areas
- 5 year limited warranty
- Compatible with EA24 extension arm (sold separately)

AL5550LPCIGY



AL5550LPCIBZ




AL3150LPCGY
AL5550LPCGY




AL3150LPCBZ
AL5550LPCBZ



Model	Lumens	Power	Efficacy	Wattage Equivalent	CCT	CRI	Photocontrol	Finish
AL5550LPCIGY	5500	53.3	103.2	150W MH or 175W MV	5000K	73	Integrated	Gray
AL5550LPCIBZ	5500	53.3	103.2	150W MH or 175W MV	5000K	73	Integrated	Bronze
AL5550LPCGY	5500	53.3	103.2	150W MH or 175W MV	5000K	73	Twist Lock	Gray
AL5550LPCBZ	5500	53.3	103.2	150W MH or 175W MV	5000K	73	Twist Lock	Bronze
AL3150LPCGY	3500	33.4	104.8	100W MH or 70W HPS	5000K	73	Twist Lock	Gray
AL3150LPCBZ	3500	33.4	104.8	100W MH or 70W HPS	5000K	73	Twist Lock	Bronze



AL5550 Series



AL3150 Series

EATON

Powering Business Worldwide

LED Area and Wall Lighting

Dusk to Dawn Security Lighting

HALO®

AL3250LPCGY


AL3250LPCBZ

AL1550LPCGY


AL1550LPCBZ



Model	Lumens	Power	Efficacy	Wattage Equivalent	CCT	CRI	Photocontrol	Finish
AL3250LPCGY	3750	32.4	115.7	100W MH or 70W HPS	5000K	73	Integrated	Gray
AL3250LPCBZ	3750	32.4	115.7	100W MH or 70W HPS	5000K	73	Integrated	Bronze
AL1550LPCGY	1997	19.4	102.9	65W CFL or 180W Inc	3500K	83	Integrated	Gray
AL1550LPCBZ	1997	19.4	102.9	65W CFL or 180W Inc	3500K	83	Integrated	Bronze



AL3250 Series



AL1550 Series



AL3150 Series

AL5550 Series

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. SA502086EN
May 2018

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.