

DESCRIPTION

The ALTO series of lampholders offers the beauty and functional design that sophisticated spaces require. The ALTO family includes lampholders in a range of sizes that accept a number of lamp types and sizes. For Halo and Lazer-by-Halo track systems. The light weight and small size of this lampholder family makes them ideal for use in museums, galleries, malls, exhibits and similar areas where high interior light is needed.

SPECIFICATION FEATURES

A...Electrical Quick Lock Adapter

Polycarbonate casing. Attaches electrically and mechanically anywhere along Power-Trac. Visual polarity line assures proper grounding.

Two position conductor allows use in single circuit and either circuit of two circuit track.

B...Yoke

Yoke allows lampholder to rotate 338° horizontally and provides 0° to 90° vertical pivot for maximum aiming adjustability.

C...Adjustment Knob

Adjustment knob locks lampholder into position.

D...Housing

Spun aluminum with baked enamel finish.

E...Face Plate


Deep Face plate provides high visual cutoff to lamp. Face plate twists off for easy relamping.

F...Accessory Clips

Accessory clips accommodate lenses and louvers.

Labels

UL listed and CSA certified for use with Halo and Lazer-by-Halo track and track systems.



(L3750 Shown in Illustration)

Catalog #	Type
Project	
Comments	
Prepared by	Date



L3750



L3754




L3756

ORDERING INFORMATION

SAMPLE NUMBER: L3750P

Lampholders	Finishes	Accessories
L3750 L3754 L3756	P=Satin White MB=Matte Black	(See Below)




L3750

For use with: 250W PAR38
L =6 5/8" [168mm]
W=6 1/4" [159mm]
E =11 1/2" [267mm]

Accessories

L1968 Barn Doors
L200 Series Filters
L214 UV Filter
L275 Cube Cell Louver




L3754

For use with: 300W PAR56
Q500W PAR56
L =6 5/8" [168mm]
W=8 1/4" [210mm]
E =12 1/4" [279mm]

Accessories

L1970 Barn Doors
L300 Series Filters
L314 UV Filter
L277 Louver



L3756

For use with: 500W PAR64
L =8" [203mm]
W=9 1/2" [241mm]
E =14 3/4" [395mm]

Accessories

L1975 Barn Doors
L279 Louver

ALTO
HIGH INTENSITY
DISPLAY
LAMPHOLDERS

Power-Trac®

ADV023217
Supersedes ADV990389

ACCESSORIES

L1968 Barn Door Shutters

Black finish Barn Door Shutters attach to outside of L3750. Built in accessory clips allows use of L200 series color filters or L275 Louver.

Color Code: MB



L1968 Barn Doors

L1970 Barn Door Shutters

Black finish Barn Door Shutters attach to outside of L3754. Built in accessory clips allows use of L300 series color filters or L277 Louver.

Color Code: MB

L1975 Barn Door Shutters

Black finish Barn Door Shutters attach to outside of L3756. Built in accessory clips allows use of L279 Louver.

Color Code: MB





L1970, L1975 Barn Doors

L200 Series Color and UV Filters
4 11/16" (119mm)

For use with PAR38 Lampholders. Provides either a soft or intense hue to accent a lighting installation.

- L211=Medium Pink
- L212=Warm Red
- L214=Ultraviolet Filter
- L220=Daylight Blue
- L221=Medium Blue
- L231=Medium Amber
- L241=Medium Green



L200 Series Filters

L200 Series Optical Lenses



L1961 Barn Door Shutters required to hold lenses.

L210=Linear Spread Lens - L210 lens fans out light beam 55° - 27 1/2° each side of center

L215=Radial Spread Lens
L215 lens spreads light beam 30° in all directions - 15° on all sides of center

L250=Linear Spread Lens spreads beam in one direction

L265=Prismatic Spread Lens spreads beam in all directions





L200 Series Lenses

L300 Series Color and UV Filters
6 5/16" (160mm)

Can be used with L1543 lampholder when L1964 Barn door shutters are used. Provides either a soft or intense hue accent a lighting installation.

- L312=Warm Red Color Filter
- L314=Ultraviolet Filter
- L320=Daylight Blue Color Filter
- L330=Straw Color filter
- L331=Medium Amber Color Filter
- L341=Medium Green Color Filter



L300 Series Filters

L275 Cube Cell Louver


4 3/4" OD (121mm). Black finish 1/2" cells for directing light and eliminating glare.

L277 Cube Cell Louver

6 1/4" OD (159mm). Black finish 1/2" cells for directing light and eliminating glare.

L279 Cube Cell Louver

4 3/4" OD (121mm) . Black finish 1/2" cells for directing light and eliminating glare.



L275, L277, L279 Cube Louver

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at www.cooperlighting.com