

Installation Instructions – Decorative High Bay Select

Instructions d'installation – Decorative High Bay Select

Instrucciones de instalación – Decorative High Bay Select

IMPORTANT: Read carefully before installing fixture. Failure to comply with these instructions may result in death, serious bodily injury and property damage. Retain for future reference.

These instructions do not claim to cover all details or variations in the equipment, procedure, or process described, nor to provide directions for meeting every possible contingency during installation, operation or maintenance. When additional information is desired to satisfy a problem not covered sufficiently for user's purpose, please contact your nearest representative.

This lighting fixture has been shipped complete with one of several mounting options. Please follow the installation instructions specific to the catalog part that you ordered.

WARNING



Risk of Fire, Electrical Shock, Cuts or other Casualty Hazards- Installation and maintenance of this product must be performed by a qualified electrician. This product must be installed in accordance with the applicable installation code by a person familiar with the construction and operation of the product and hazards involved.



Risk of Fire and Electric Shock- Make certain power is OFF before starting installation or attempting any maintenance. Disconnect power at fuse or circuit breaker.



Risk of Fire- Minimum 90°C supply conductors.



Risk of Personal Injury or property damage- Fixture may become damaged and/or unstable if not installed properly.


- Due to sharp edges, handle with care.
- Do not install this product in locations such as gymnasiums, arenas, sports complexes, multi-purpose rooms, and other locations where the fixture potentially will be subject to impacts from external sources. Doing so may result in cracking and/or breaking of the fixture which may cause pieces to fall from application.
- Clean with a dry cloth only. Do not apply abrasive chemicals or cleaning agents. Doing so may result in cracking and/or breaking of the fixture which may cause pieces to fall from application.
- Do not install this product in food prep areas and hazardous environments which may expose the product to pollutants such as oil, grease, or VOC's. Doing so will void the products warranty and may cause fixture to become damaged and/or unstable.
- Do not mount luminaire within 6" of a combustible surface.
- Ensure adequate structure to support luminaire weight.

DISCLAIMER OF LIABILITY: Cooper Lighting Solutions assumes no liability for damages or losses of any kind that may arise from the improper, careless, or negligent installation, handling or use of this product.

NOTE: Specifications and dimensions subject to change without notice.

ATTENTION Receiving Department: Note actual fixture description of any shortage or noticeable damage on delivery receipt. File claim for common carrier (LTL) directly with carrier. Claims for concealed damage must be filed within 15 days of delivery. All damaged material, complete with original packing must be retained.


CCT Select Instructions



Warning: Be sure fixture is not powered or energized before sliding switches to change CCT or lumen.

1. To select the CCT, slide the first switch to the desired LED color temperature (3000K, 3500K, 4000K, 5000K, 6500K CCT).
2. To select the lumen, slide the second switch, to the desired power level or wattage (L, M, H).


Wiring Diagram for LED light Engine



Emergency Battery installation instructions can be found at www.cooperlighting.com

Emergency Battery sold separately and is not included with luminaire.

For more information scan this QR Code.



Luminaire Installation

1. Install hook. (Figure 1.)




Figure 1.




Figure 2.




Figure 3.




Figure 4.

Warning: Be sure fixture is not powered or energized before sliding switches to change CCT or lumen.

DO NOT USE POWER CORD OR WIRING TO HANG FIXTURES. MAY CAUSE DAMAGE OR INJURY.

1. Turn off power at main fuse/breaker box. Carefully open carton, remove fixture from carton.
2. Flip up hook 90-degrees. (Figure 1)
3. Slip 3D printed shade over LED Housing. (Figure 2.) Alternatively, the shade can be installed from below after fixture is hung and wired. (Figure 5).
4. Once set over the fixture, ensure the shade snaps into place to secure. (Figure 3)
5. Hang fixture to structure (by others). (Figure 4)
6. Attach included safety cable to existing or new structure. Do not use cord or wiring to hang fixtures.
7. Connect LED high bay wiring to incoming power supply. See wiring diagram.




Figure 5.

Sensor Accessory





Sensor and remote control not included with luminaire.
Items sold separately.

Refer to sensor instruction sheet found at www.cooperlighting.com.
For additional high-bay accessories, scan QR code.


Sensor



Remote Control



Highbay sensor
Model # UHBS-SENSOR PK



Remote control
Model # UHBS SENSOR REMOTE




Surface Mount Bracket Accessory

Surface Mount Bracket Accessory not included with luminaire.
Item sold separately.

Refer to instruction sheet found at www.cooperlighting.com.
For more information, scan QR code.



Lens Optic Adjustment Instructions



1. Disconnect power before adjusting lens optics. Lens may be hot to touch. Allow to cool before handling.
2. Push latch to unlock (Fig. 4).
3. Rotate lens by grabbing lens handles with both hands (Fig. 5).
4. Rotate lens to desired distribution (WB, MB or NB).
5. Lock lens in place. Push latch back into original position (Fig. 6).
6. Energize product.

FCC Statement

Note: This equipment has been tested and found to comply with the limits for a Class A digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference when the equipment is operated in a commercial environment. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instruction manual, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his own expense.

Énoncé de la FCC

Remarque : Cet équipement a été mis à l'essai et déclaré conforme aux limites établies pour un dispositif numérique de classe A en vertu de l'article 15 des règlements de la FCC. Ces limites sont conçues pour assurer une protection raisonnable contre tout brouillage nuisible lorsque l'équipement fonctionne dans un environnement commercial. Cet équipement produit, utilise et peut émettre de l'énergie radioélectrique et, s'il n'est pas installé et utilisé conformément aux instructions, il peut créer des parasites nuisibles aux communications radio. L'utilisation de cet équipement dans une installation résidentielle est susceptible de provoquer des interférences nuisibles, auquel cas l'utilisateur devra corriger ces interférences à ses propres frais.

Declaración de la FCC

Nota: Este equipo ha sido probado y cumple con los límites para un dispositivo digital de Clase A, de conformidad con la parte 15 de las Normas de la FCC. Estos límites están diseñados para proporcionar una protección razonable contra interferencias perjudiciales cuando el equipo se opera en un entorno comercial. Este equipo genera, utiliza y puede emitir energía de radiofrecuencia y, si no se instala y utiliza de acuerdo con el manual de instrucciones, puede causar interferencias perjudiciales en las comunicaciones de radio. El funcionamiento de este equipo en un área residencial puede causar interferencias perjudiciales, en cuyo caso el usuario deberá corregir las interferencias por su cuenta.

Warranties and Limitation of Liability

Please refer to <https://www.cooperlighting.com/global/resources/legal> for our terms and conditions.

Garanties et limitation de responsabilité

Veuillez consulter le site <https://www.cooperlighting.com/global/resources/legal> pour obtenir les conditions générales.

Garantías y Limitación de Responsabilidad

Visite <https://www.cooperlighting.com/global/resources/legal> para conocer nuestros términos y condiciones.