


<b>Project</b>		<b>Catalog #</b>		<b>Type</b>	
<b>Prepared by</b>		<b>Notes</b>		<b>Date</b>	



# Metalux

## RMK2

### Regress Mount Accessory Kit

#### Typical Applications

Office • Education • Healthcare • Retail

#### Product Certification



#### Interactive Menu

- Product Specifications page 2
- Dimensional Details page 2
- Compatible Fixtures page 3
- Product Warranty

### Top Product Features

- Raises lit surface 2" into the ceiling plane
- Metal bevel design conceals fixture frame for a clean aesthetic
- Visually appealing design provides depth and additional glare control
- Fits most Metalux recessed panel product configurations
- Available in 2x2, 2x4, 1x4, and 6" wide linear sizes

### Order Information

Catalog No #	Description	UPC	Kit Weight (lbs.)	Master Pack Qty	Pallet Qty
RMK2-22-W	2' x 2' Regress Kit, White Finish, Field assembly required	080083287185	3.0	9	144
RMK2-24-W	2' x 4' Regress Kit, White Finish, Field assembly required	080083288007	4.6	9	144
RMK2-14-W	1' x 4' Regress Kit, White Finish, Field assembly required	080083288021	4.0	9	144
RMK2-62-W	6" x 2' Regress Kit, White Finish, Field assembly required	080083288045	2.0	9	288
RMK2-64-W	6" x 4' Regress Kit, White Finish, Field assembly required	080083288069	3.6	9	144
RMK2-68-W	6" x 8' Regress Kit, White Finish, Field assembly required	080083288083	6.8	9	144

## Product Specifications

### Construction

- Extruded aluminum frame with miter corners at 2" nominal height
- Die formed metal L-brackets and fasteners secure kit together
- Multiple sizes available to fit recessed or linear panels
- Designed to fit most lay-in ceiling grids including Metalux drywall frame kits (ordered separately)
- Accessory kit ships in one compact unit and requires field assembly

### Size

- Available frame sizes in 2' x 2', 2' x 4', and 1' x 4' kits for recessed panels
- Available 6" x 2ft, 4ft or 8ft kits for linear panels
- Consult factory for availability and fit with other troffer families

### Mounting

- Includes all needed hardware to secure fixture to kit and to the T-Grid. Refer to the installation instructions for more details
- Designed for use in retrofit, remodel or new construction applications
- Available as a pre-installed option on several panel fixtures. See fixture ordering logic found on CGT, CGTS, FP, FPS and RBG spec sheets

### Finish

- Standard white polyester powder coat finish painted after fabrication


### Compliance and Certifications

- Field install regress mount kits are UL compliant accessories
- Can be used in damp locations. See fixture for primary compliance rating.
- Regress kit does not alter design or construction of luminaire


### Product Warranty

- Accessory kit has a 1-year limited warranty

## Regress Kit Assembly View



## Dimensional Details



### Troffer and Panel Kits

Catalog #	Length	Width	Inside Length	Inside Width	Height
RMK2-22-W	23-23/32"	23-23/32"	21-1/2"	21-1/2"	2"
RMK2-24-W	47-3/4"	23-23/32"	45-1/2"	21-1/2"	2"
RMK2-14-W	47-3/4"	11-23/32"	45-1/2"	9-1/2"	2"

### 6" Wide Linear Kits

Catalog #	(A) Length	Width	(B) Inside Length	Inside Width	Height
RMK2-62-W	23-23/32"	5-3/4"	21-15/32"	3-1/2"	2"
RMK2-64-W	47-3/4"	5-3/4"	45-1/2"	3-1/2"	2"
RMK2-68-W	95-3/4"	5-3/4"	93-1/2"	3-1/2"	2"

## Regress Kit Compatibility Matrix

	RMK2-24-W	RMK2-22-W	RMK2-14-W	RMK2-62-W	RMK2-64-W	RMK2-68-W
	2' x 4'	2' x 2'	1' x 4'	6" x 2'	6" x 4'	6" x 8'
<b>Metalux<sup>(1)</sup></b>						
CGT/CGTS	✓	✓	✓			
FP/FPS	✓	✓	✓			
RBG <sup>(2)</sup>				✓	✓	✓

**Notes:** (1) Consult fixture spec sheet for mod-shop (late-point assembly) options and lead-times. (2) RBG stock SKUs only qualify for mod-shop option.

## Fixture Kit Installation

### Ordering Information:

(Regress Mount Kit can be assembled and installed on all stock products. This includes all other available commercial options. See product spec sheet for more details.

Family	Size	Regress Kit	Example Order Info	Notes
CGT / CGTS	1' x 4'	RMK2-14-W	22CGTS-L3C3-RMK2	Stock product only
	2' x 2'	RMK2-22-W		
	2' x 4'	RMK2-24-W		
FP / FPS	1' x 4'	RMK2-14-W	14FP4240C-RMK2	Stock product only
	2' x 2'	RMK2-22-W		
	2' x 4'	RMK2-24-W		
RBG	2FT	RMK2-62-W	4RBG6-SL1-L8SCT3-RMK2	Stock product only
	4FT	RMK2-64-W		
	8FT	RMK2-68-W		