
Lumière 1250 Calle Suerte Carnarilla, CA 93012-8053 PH (805) 484-7713 FAX (805) 445-7693



www.cooperlighting.com

INSTALLATION INSTRUCTIONS: 613 WELL LIGHT



WARNING:

WARNING:
WIRNIG AND INSTALLATION MUST BE PERFORMED BY A QUALIFIED
ELECTRICIAN ONLY. TURN POWER OFF BEFORE INITIAL INSTALLATION.
SERVICING, NAINTENANCE, AND RELAMPING.
FIXTURES 5-KOULD ALWAYS BE INSTALLED IN ACCORDANCE WITH LOCAL
AND/OR NATIONAL ELECTRIC CODES.

THIS IS A 12 VOLT FIXTURE.

A REMOTE TRANSFORMER IS REQLIRED (NOT INCLUDED)
USE U.L. LISTED WATERPROOF WIRE NUT CONNECTORS CATALOG #:
KING-T6, MANUFACTURED BY KING TECHNOLOGY, Inc. OR EQUIVALENT.
DO NOT INSTALL THIS FIXTURE IN ANY COMBUSTIBLE MATERIALS.

NOTE

THIS FIXTURE CAN BE USED FOR IN-GROUND, CONCRETE POUR, BRICK, AND MASONRY INSTALLATIONS. IT IS NOT DESIGNED FOR INSTALLATION IN ANY COMBUSTIBLE MATERIALS.

INSTALLATION INSTRUCTIONS:

- REMOVE LENS BEZEL BY LOGSENING FOUR SOCKET CAP SCREWS USING ALLEN HEX KEY (INCLUDED). REMOVE PIVOT RING/LAMP HOLDER ASSEMBLY BY LIFTING IT UP AND OUT OF THE HOUSING.
- 2. RUN THE LOW VOLTAGE WIRES FROM REMOTE TRANSFORMER, THROUGH THE 1/2" NPSM CONDUIT HUB INTO THE HOUSING. ATTACH CONDUIT AND FITTING TO THE HUBS ON THE BOTTOM OF THE FIXTURE HOUSING. USE THEADS SEALER OR TEFLOND TAPE ON THREADS TO ENSURE A WATER TIGHT CONNECTION.
- 3. PUSH MR16 LAMP (NOT INCLUDED) INTO SOCKET, THEN INSTALL LAMP INTO LAMP HOLDER, FOLLOWED BY SNAP RING.
- CONNECT 12 VOLT SUPPLY WIRES TO SOCKET WIRES USING WATERPROOF WIRE NUT CONNECTORS (NOT INCLUDED). POLARITY NOT CRITICAL.


- 5, MOVE PIVOT RING RETAINING CLIP TO DESIRED POSITION AND REINSTALL PIVOT RING/LAMP HOLDER ASSEMBLY.
- 6. O-RING MUST BE SEATED PROPERLY IN PLACE AND LENS BEZEL ASSEMBLY MUST BE CLEAN FOR A PROPER SEAL.
- 7. REINSTALL LENS BEZEL USING FOUR SOCKET CAP SCREWS.
- 8. APPLY POWER TO THE FIXTURE TO TEST FOR PROPER OPERATION.

LAMP:

USE ONLY 12V, 50 WATTS MAXIMUM, BI-PIN, MR1B, HALOGEN LAMP. CHECK PACKAGE AND FIXTURE LABELING CAREFULLY FOR PROPER LAMP TYPE AND WATTAGE.

TO RELAMP:

TO RELAMP:
REMOVE LENS BEZEL BY REMOVING FOUR SOCKET CAP SCREWS FROM
THE LENS BEZEL. LIFT PIVOT RING/LAMP HOLDER ASSEMBLY OUT.
PULL (DO NOT TWIST) THE SOCKET OFF BOTTOM OF LAMP. REMOVE
SNAP RING AND LAMP. PUSH NEW LAMP BI-PINS INTO SOCKET. PLACE
LAMP INTO LAMP BEZEL AND SECURE WITH SNAP RING. LOWER PIVOT
RING INTO FXTURE. RE-AIM IF DESIRED. REPLACE LENS BEZEL AND
0-RING. SECURE WITH FOUR SOCKET CAP SCREWS.



Cooper Lighting Solutions Lumiere reserves the right to make design changes without notice for product improvement.