



Lights. Camera. Safety.


Lighting is everywhere. Why shouldn't it do more?
LumenSafe offers significant benefits:

Flexible integration

LumenSafe is compatible with virtually any video management system or security platform as provided by the security integrator.

Specifications

Cooper Lighting Solutions ("CLS") provides world-class lighting solutions with incredible efficacy and patented optics for uniform light distribution. CLS collaborates with integrators to develop and specify differentiated solutions for our mutual customers.



30% Lower Install Cost

Efficient, "plug & play" installation means shorter system install time; contractors can install the luminaire and camera at the same time, with no additional labor required.

All-in-one solution

Our all-in-one LumenSafe solution makes installation easier. Integrated camera and networking equipment mean: no additional wiring is needed beyond providing line power to the luminaire.



Galleon

Area/Site Luminaire

- > Choice of 16 high-efficiency optical distributions
- > 40 lumen packages, providing up to 68,000 delivered lumens
- > 0-10V dimming standard
- > Available with wireless lighting control systems, photocell receptacle and occupancy sensor options
- > Pole, mast-arm or wall-mounted configurations



Navion

Area/Site and Roadway Luminaire

- > Choice of 16 high-efficiency optical distributions
- > 24 lumen packages, providing up to 42,000 delivered lumens
- > 0-10V dimming standard
- > Available with wireless lighting control systems, photocell receptacle and occupancy sensor options



Archeon Large

Roadway Luminaire

- > Choice of 4 high-efficiency optical distributions
- > 20 lumen packages, providing up to 31,000 delivered lumens
- > Available with integrated photocell receptacle
- > Single-latch tool-less entry



AXIS P3225-VE Mk II

Network Camera

- > Outstanding video quality in both strong and poor light conditions
- > Outdoor ready and IK10 vandal resistant
- > Remote zoom and focus
- > WDR Forensic Capture
- > Lightfinder technology for exceptional light sensitivity



AXIS P3227-LVE

Network Camera

- > High quality, detailed video surveillance under any light conditions
- > Crystal clear overhead and close-up views
- > Outdoor ready and IK10 vandal resistant
- > Remote zoom and focus
- > WDR - Forensic Capture



AXIS M5525-E PTZ

Network Camera

- > Easily follow and capture moving objects
- > Affordable and versatile camera for indoor and outdoor use
- > Zoomed in detailed and broad view image capture
- > 10X Optical zoom and continuous 360° pan

Exceptional performance

- > Remarkable optical performance
- > Patented high-efficiency AccuLED Optics™ system
- > Energy-conscious LEDs
- > Superior efficiency and control
- > Uniform illumination to desired areas

Quality imaging

- > All cameras used in our joint solution provide outstanding video quality in any lighting conditions
- > Axis Zipstream technology for reduced bandwidth and storage needs
- > WDR Forensic Capture ensures image detail in bright and dark areas
- > Multiple video compressions and streaming file format options
- > Day and night functionality

For a complete list of compatible products, visit:
<https://www.cooperlighting.com/brands/cls/lumensafe.html>

Cooper Lighting Solutions is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.