


WaveLinx

Wireless lighting controls with or without batteries




Use what you already know and complete projects and open schools faster while reducing cost with the Eaton WaveLinx system, for LED lighting and controls.


Wire integrated luminaire or retrofit kit




Wire for power not load switching




Easy programming with mobile application
(Wireless Area Controller required)



Go from this...



To this!



How to Videos



Now simple standard wiring provides so much more. Here's what you get:

Lighting

- Continuous dimming
- Individual control

Occupancy

- Auto On to 50% or Vacancy
- Auto Off of lighting and plug loads


Daylighting

- Continuous dimming to OFF
- Open or closed loop

Scheduling

Security

- UL2900-1 Listed
- UL924
- DLC NLC V2 qualified



Stay secure with unparalleled 7-tier network security features



WaveLinx is UL2900-1 listed to the Standard for Software Cybersecurity for Network-Connectable Products
Eaton has the first lab approved to participate in UL's Data Acceptance Program for Cybersecurity



Powering Business Worldwide

WaveLinx

Wireless lighting controls with or without batteries

Satisfy your customer and your bottom line. Get off the job faster and at a lower installation cost with Wavelinx components.

WaveLinx products

CATALOG NUMBER	DESCRIPTION	VOLTAGE	UPC
WAC-POE	Wireless Area Controller 1 required per 15 rooms	WPOE-120	080083763818
WPOE-120	PoE power supply for WAC	120V	080083763825
WSP-CA-010	Wireless Dimming Switchpack 0-10V output supports up to 30 typical LED drivers	120-347VAC 16A LED	080083840816
W4S-RL-S4-*	4 small button field programmable wallstation with Raise/Lower (W, V, G, B)	120/277VAC Not load switching, for radio power only	080083866809
WB5-S3-W	White 3 small 1 large button with Raise/Lower field programmable wallstation (Scene 1, Scene 2, Scene 3, Off, v, ^)		080083865505
WB6-S3D-W	White 6 small button field programmable wallstation (Scene 1, Scene 2, Scene 3, Raise, Lower, Off)	Qty 4 AAA batteries	080083865604
WB6-S5-W	White 6 small button field programmable wallstation (Scene 1, Scene 2, Scene 3, Scene 4, Scene 5, Off)		080083865628
WOLC-7P-010	Outdoor Lighting Control Module	120/347VAC 10A LED	080083837540
WR-20	Wireless 20A Receptacle	120V 20A	080083763788
WR-15	Wireless 15A Receptacle	120V 15A	080083763771
CWPD-1500	Wireless PIR 1500 sq ft Ceiling Sensor	Qty 2 AA batteries	080083763795

Reduce installation time by 60% with MWS products

CATALOG NUMBER	DESCRIPTION	UPC
12EC12/2G11	120V 12AWG Extender Cable 11' long	622697307677
12EC12/2G15	120V 12AWG Extender Cable 15' long	622697308094
12FC12/2G11	120V 12AWG Fixture Cable 11' long	622697362317
12ST12/2G	120V 12AWG Circuit Starter Cable	622697277376
27EC12/2G11	277V 12AWG Extender Cable 11' long	622697310127
27EC12/2G15	277V 12AWG Extender Cable 15' long	622697310172
27FC12/2G11	277V 12AWG Fixture Cable 11' long	622697362690
27ST12/2G	277V 12AWG Circuit Starter Cable	622697277604
27ST12/2G	277V 12AWG Circuit Starter Cable	080083837540

Save time and money with stock fixtures with integrated sensors

CATALOG NUMBER	DESCRIPTION	LUMEN PACKAGE & CCT	UPC
22CZRK-LD4-34-UNV-L840-CD1-SWPD1-U	2x2 Cruze retrofit kit w/integrated sensor	3400 Lumen, 4000K CCT	080083809103
24CZ-LD5-40-UNV-L840-CD1-SWPD1-U	2x4 Cruze luminaire w/integrated sensor	4000 Lumen, 4000K CCT	080083809080
22CZ2-34HE-UNV-L840-CD1-SWPD1-U	2x2 Cruze ST High Efficiency luminaire w/integrated sensor	3400 Lumen, 4000K CCT	080083881246
24CZ2-40HE-UNV-L840-CD1-SWPD1-U	2x4 Cruze ST High Efficiency luminaire w/integrated sensor	4000 Lumen, 4000K CCT	080083881468



Powering Business Worldwide

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada Sales
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

Eaton
18001 East Colfax Avenue
Aurora, CO 80011
P: 303-393-1522
www.eaton.com/lighting

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. SB503090EN
April 26, 2019 3:32 PM

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.

Product availability, specifications,
and compliances are subject to
change without notice.