



Installer Friendly Reliable Security Money Savings

FSL503 Floodlights

This floodlight series utilizes selectable CCT functionality, advanced optics and multiple mounting options. 5,800 lumen output and dusk-to-dawn operation allows for a versatile application range from residential to light commercial.



white



bronze



Powering Business Worldwide

FSL503 LED Floodlights Outdoor Security Lighting

	Feature	Benefit	Result
Performance	Field Selectable CCT (3000K, 4000K, 5000K)	1 SKU covers all applications	
	Up to 112 Lm/W, 70K life hours at L70	Save over 80% over traditional incandescent floodlights	
	Universal Voltage (120-277VAC)	Universal Install	
	5 year warranty	Guaranteed performance	
Construction	Die-Cast aluminum housing with UV stable clear lens	Durable, impact resistant housing that prevents discoloration over time	
	Adaptor plate included in box	Universal mounting (Recessed J-Box, Surface mount J-Box, Pole mount below 4' Flood only)	



Ordering Information

Series	Voltage	Power (W)	Delivered Lumens (Lm)	Efficacy (Lm/W)	CCT	UPC	Pallet Quantity	Controls
FSL503TB	120-277V	51.6	5800	112.4	3000K,4000K,5000K	080083867110	96	None
FSL503TW	120-277V	51.6	5800	112.4	3000K,4000K,5000K	080083867158	96	None
FSL503TIB	120-277V	51.6	5800	112.4	3000K,4000K,5000K	080083836062	96	Integrated Photocell
FSL503TIW	120-277V	51.6	5800	112.4	3000K,4000K,5000K	080083867134	96	Integrated Photocell

Competitor Comparison

= Market Leading

Feature	FSL503	Competitor A (Flood)	Competitor A (Area Light)	Competitor B (Area Light)
Lumens	5,800	1,900	4,700	5,563
Lm/W	Up to 112	Up to 74	Up to 114	Up to 132
CCT	Selectable (3K,4K,5K)	4000K	5000K	3000K,4000K,5000K
Mounting	Universal (Wall + Eave/ Recessed + Surface)	Wall + Eave	Wall	Wall
Installation	Hanger hook easy mount, Adapter plate	-	Wall or Pole mount	Wall or Pole mount
Voltage	120-277V	120V	120V	120V
Lens	70,000 hours	50,000 hours	50,000 hours	100,000 hours
Listings	cULus	cULus, EStar	cULus, EStar	cULus
Warranty	5	5	5	5
Family	Flood, D2D	Flood, D2D	D2D only	D2D only



Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. SA506012EN
February 27, 2019 4:57 PM

Eaton is a registered trademark.
All other trademarks are property of their respective owners.
Product availability, specifications, and compliances are subject to change without notice.