

## DESCRIPTION

692 Series LED Trims - 6-inch Aperture Reflectors - are integral elements in the Halo ML56 LED Downlighting System. ML56 LED System is a series of modular LED Light Modules for use with dedicated 5" or 6" ML56 LED trims. The ML56 LED trims in 5" and 6" aperture sizes are designed to fit Halo, All-Pro and others 5" or 6" recessed housings. The ML56 system is suitable for new construction, remodel or retrofit installation.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

692 Series LED trims are 6-inch aperture reflectors offered in Specular Clear, Haze (Semi-Specular Clear), and White (Matte White). 692 Series Reflectors also feature matte white finish flange. The precision spun aluminum reflector provides excellent optical performance. The 692 reflectors may be used in most standard height 6-inch aperture recessed housings; Halo, All-Pro, and more (refer to ML56 LED Light Module specifications for details).

- For use with ML56 Series LED light modules
- For use in standard housings
- Reflectors with self-flange
- Wet location shower listed with ML56 LED Light Modules
- Torsion springs pull trim and light module tight to ceiling
- ML56 downlight trims and modules make any housing AIR-TITE™ (ASTM E283)

## Compatible with ML56 LED System of LED Downlight Light Modules

### 600 Series - 80CRI, 600lm

#### 5" / 6" LED Retrofit Downlight Engine

ML5606827 - 2700K  
ML5606830 - 3000K  
ML5606835 - 3500K  
ML5606840 - 4000K

### 600 Series - 90CRI, 600lm

#### 5" / 6" LED Retrofit Downlight Engine

ML5606927 - 2700K  
ML5606930 - 3000K  
ML5606935 - 3500K  
ML5606940 - 4000K

### 900 Series - 80CRI, 900lm

#### 5" / 6" LED Retrofit Downlight Engine

ML5609827 - 2700K  
ML5609830 - 3000K  
ML5609835 - 3500K  
ML5609840 - 4000K

### 900 Series - 90CRI, 900lm

#### 5" / 6" LED Retrofit Downlight Engine

ML5609927 - 2700K  
ML5609930 - 3000K  
ML5609935 - 3500K  
ML5609940 - 4000K

### 1200 Series - 80CRI, 1200lm


#### 5" / 6" LED Retrofit Downlight Engine

ML5612827 - 2700K  
ML5612830 - 3000K  
ML5612835 - 3500K  
ML5612840 - 4000K

### 1200 Series - 90CRI, 1200lm

#### 5" / 6" LED Retrofit Downlight Engine

ML5612927 - 2700K  
ML5612930 - 3000K  
ML5612935 - 3500K  
ML5612940 - 4000K



692SC



692H



692W

## 692 Series LED Trim

### 6-Inch Reflector

For use with  
Halo ML56  
LED System  
Light Modules



## ORDERING INFORMATION

SAMPLE NUMBER: 692SC

Trim	Finish	Accessory
692= 6" Reflector	<b>SC</b> =Specular Clear, White Flange <b>H</b> =Haze (Semi-Specular), White Flange <b>W</b> =White (Matte White), White Flange	<b>TRM690WH</b> = 6" LED Oversize Trim Ring for use with 69* series trims, White 6.9" I.D., 9.5" O.D. Ring slips over LED trim. Inset design allows 6" trim to fit into oversize ring for an even trim surface <b>ML56CLIP</b> = Friction Clip Mounting Kit - For retrofitting non-torsion spring housings, 6" clips