

## E44 4" Trim Series

The E44 trims are offered in open, lens and lens wall wash in both round and square apertures. They are adjustable and feature 360° rotation, 35° tilt and when combined with various distribution lamps provide a broad range of optical distributions providing accent, task, wall washing / grazing and general area illumination.

Catalog #		Type
Project		
Comments		Date
Prepared by		

### WAFER THIN TRIMS



The E44 wafer thin trims are used with the new construction housings. The 1.0 mm thin profile provides minimal ceiling presence.

#### Directional Open

- 1430** Conical Reflector
- 1431** Conical Baffle
- 1434** Round Pinhole
- 1435** Round Pinhole w/Oculus
- 1464** Square Pinhole
- 1465** Square Pinhole w/Oculus

#### Lens Wall Wash

- 1432** Angle Cut Conical Reflector
- 1436** Round Pinhole
- 1466** Square Pinhole

#### Directional Lens

- 1433** Conical Reflector
- 1437** Round Pinhole
- 1467** Square Pinhole

### DIRECTIONAL OPEN



**1430**  
Conical Reflector,  
Open, 35° tilt

#### ORDERING INFORMATION

**SAMPLE NUMBER:** 1430MWWF

Trim	Finish
<b>1430</b> = 4" conical reflector, open, 35° tilt	<b>BN</b> =Brushed Nickel <b>GB</b> =German Bronze <b>H</b> =Haze <b>HWF</b> =Haze, White Flange <b>MWWF</b> =Matte White, White Flange



**1431**  
Conical Baffle,  
Open, 35° tilt

#### ORDERING INFORMATION

**SAMPLE NUMBER:** 1431MBWF

Trim	Finish
<b>1431</b> = 4" conical baffle, open, 35° tilt	<b>BBWF</b> =Black Baffle, White Flange <b>BN</b> =Brushed Nickel <b>GB</b> =German Bronze <b>MBWF</b> =White Baffle, White Flange



**1434**  
Round Pinhole,  
Open, 35° tilt

#### ORDERING INFORMATION

**SAMPLE NUMBER:** 1434MW

Trim	Finish
<b>1434</b> = 4" round pinhole, open, 35° tilt	<b>BN</b> =Brushed Nickel <b>GB</b> =German Bronze <b>MW</b> =Matte White



**1435**  
Round Pinhole with Oculus,  
Open, 35° tilt

#### ORDERING INFORMATION

**SAMPLE NUMBER:** 1435MWWB

Trim	Finish
<b>1435</b> = 4" round pinhole w/oculus, open, 35° tilt	<b>BNBB</b> =Brushed Nickel, Black Baffle <b>GBBB</b> =German Bronze, Black Baffle <b>MWBB</b> =Matte White, Black Baffle <b>MWWB</b> =Matte White, White Baffle

## DIRECTIONAL OPEN



**1464**  
Square Pinhole,  
Open, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1464MW

Trim	Finish
<b>1464</b> = 4" square pinhole, open, 35° tilt	<b>BN</b> =Brushed Nickel <b>GB</b> =German Bronze <b>MW</b> =Matte White



**1465**  
Square Pinhole w/Oculus,  
Open, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1465MWWB

Trim	Finish
<b>1465</b> = 4" square pinhole w/oculus, open, 35° tilt	<b>BNBB</b> =Brushed Nickel, Black Baffle <b>GBBB</b> =German Bronze, Black Baffle <b>MWBB</b> =Matte White, Black Baffle <b>MWWB</b> =Matte White, White Baffle

## LENS WALL WASH



**1432**  
Angle Cut Conical Reflector,  
Lens Wall Wash

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1432MWWF

Trim	Finish
<b>1432</b> = 4" angle cut conical reflector, lens wall wash	<b>H</b> =Haze <b>HWF</b> =Haze, White Flange <b>MWWF</b> =Matte White, White Flange



**1436**  
Round Pinhole,  
Lens Wall Wash

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1436MWWB

Trim	Finish
<b>1436</b> = 4" round pinhole, lens wall wash	<b>MWBB</b> =Matte White, Black Baffle <b>MWWB</b> =Matte White, White Baffle



**1466**  
Square Pinhole,  
Lens Wall Wash

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1466MWWB

Trim	Finish
<b>1466</b> = 4" square pinhole, lens wall wash	<b>MWBB</b> =Matte White, Black Baffle <b>MWWB</b> =Matte White, White Baffle

## DIRECTIONAL LENS



**1433**  
Conical Reflector,  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1433MWWF

Trim	Finish
<b>1433</b> = 4" conical reflector, diffuse lens, 35° tilt	<b>H</b> =Haze <b>HWF</b> =Haze, White Flange <b>MWWF</b> =Matte White, White Flange



**1437**  
Round Pinhole,  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1437MWWB

Trim	Finish
<b>1437</b> = 4" round pinhole, diffuse lens, 35° tilt	<b>BNBB</b> =Brushed Nickel, Black Baffle <b>GBBB</b> =German Bronze, Black Baffle <b>MWBB</b> =Matte White, Black Baffle <b>MWWB</b> =Matte White, White Baffle



**1467**  
Square Pinhole,  
Diffuse Lens, 35° tilt

## ORDERING INFORMATION

**SAMPLE NUMBER:** 1467MWWB

Trim	Finish
<b>1467</b> = 4" square pinhole, diffuse lens, 35° tilt	<b>BNBB</b> =Brushed Nickel, Black Baffle <b>GBBB</b> =German Bronze, Black Baffle <b>MWBB</b> =Matte White, Black Baffle <b>MWWB</b> =Matte White, White Baffle