

## E26 6" Trim Series


### DESCRIPTION

Air-Tite™ baffle trim with reflector 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

### SPECIFICATION FEATURES

- Self-flange metal baffle with upper reflector
- Socket supporting baffle
- Torsion spring retention
- Accepts a wide range of lamps
- Makes installation Air-Tite regardless of housing used



#### Dimensions:

H: 5" [127mm]

OD: 7-1/4" [184mm]

Housings	Max Lamp Compatibility
H7ICT H7ICAT	40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40, 75W R30
H7RICT H7RICAT	30WAT, 30WATH, 30PAT: 40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40
E7ICAT E7RICAT	30SNAT, 30TBZAT: 40W A19, 60W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40
H7UICAT	70W A19, 75W PAR30S, 75W PAR30L, 100W PAR38, 85W BR30, 100W R30
H7ICTNB H7ICATNB	40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40, 75W R30
E7ICATNB	30WAT, 30WATH, 30PAT: 40W A19, 75W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40 30SNAT, 30TBZAT: 40W A19, 60W PAR30S, 75W PAR30L, 65W PAR38, 65W BR30, 90W BR40
H7T	100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 85W BR30, 100W R30
H7TCP	75W A19, 75W PAR30S, 75W PAR30L, 150W PAR38, 85W BR30, 100W R30
H7RT	100W A19, 150W A21, 50W PAR30S, 50W PAR30L, 150W PAR38, 85W BR30, 100W R30
E7TAT	100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 65W BR30
E7RTAT	100W A19, 150W A21, 50W PAR30S, 75W PAR30L, 150W PAR38, 65W BR30
H7TNB	100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 85W BR30, 100W R30
E7TATNB	100W A19, 150W A21, 75W PAR30S, 75W PAR30L, 150W PAR38, 65W BR30

Compatible with Halogen, Incandescent, LED\* or CFL\* lamps.

### ORDERING INFORMATION

SAMPLE NUMBER: 30WAT

Trim	Finish
30WAT= 6" White Baffle & Reflector, White Trim	WH=White
30WATH= 6" White Baffle & Clear Reflector, White Trim	WH=White
30PAT= 6" Black Baffle & Reflector, White Trim	WH=White
30SNAT= 6" Satin Nickel Baffle & Reflector, Satin Nickel Trim	SN=Satin Nickel
30TBZAT= 6" Tuscan Bronze Baffle & Reflector, Tuscan Bronze Trim	TBZ=Tuscan Bronze

### HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
30WAT 30WATH 30PAT 30SNAT 30TBZAT	Reflector & Baffle	•	•	•	•	•	•	•	•
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
		•	•						
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
•	•	•	•	•	•	•	•		
		H27RT	E27TAT	E27RTAT					

For use in select other's housings, refer to U.L. classification list at [www.cooperlighting.com](http://www.cooperlighting.com).

\*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Cooper Lighting Solutions does not warranty the lamp.




**30WAT**  
White Trim, White Baffle and Reflector




**30WATH**  
White Trim, White Baffle and Clear Reflector



**30PAT**  
White Trim, Black Baffle and Clear Reflector



**30SNAT**  
Satin Nickel Trim, Satin Nickel Baffle and Reflector



**30TBZAT**  
Tuscan Bronze Trim, Tuscan Bronze Baffle and Reflector

**30**

6-Inch Super Trim™  
Air-Tite™ Baffle



For use in Halo listed housings.



Select trims are classified for use in others housings.  
See [www.cooperlighting.com](http://www.cooperlighting.com).

TD518201EN  
10/19/2016