

0-10V Sensor Dimmers

Greengate



**Meet energy codes.
Reduce cost.
Save time.**



OSW-D-010 / VSW-D-010
0-10V Dual Tech Sensor Dimmer
Occupancy / Vacancy





OSW-P-010 / VSW-P-010
0-10V PIR Sensor Dimmer
Occupancy/Vacancy

EATON

Powering Business Worldwide

3 Devices in one

Eaton's 0-10V DualTech Sensor Dimmer is a 3-in-1 solution that combines functionality of a switchpack, a sensor and a 0-10V dimmer into one wallbox device to help customers save labor costs, reduce installation time as well as meet the latest energy codes and standards.




One device replaces three!

Eaton's 0-10V DualTech Sensor Dimmer solution offers a convenient and cost effective way for users to satisfy commercial energy codes like ASHRAE 90.1 and California Title 20 that require designs that enable energy savings for Commercial facilities.

Design features

- 0-10V Dimming
- Occupancy sensing
- Integrated photocontrol for daylight harvesting*
- Title 20 compliant
- Easily configurable for application specific operation
- Surge and zero cross protection
- Universal input (120-277V)
- cULus, NOM and ANCE certified

*Available only on DualTech Models






Catalog No.	Description	Compatible Lamp Types	Rating		Colors
			Watt	V/AC	
OSW-D-010-	0-10V Dual Tech Sensor Dimmer - Occupancy with LED Single pole/3-Way preset	0-10VDC LED/FLR	960	120	White (W)
			2200	277	Black (BK)
					Gray (G)
VSW-D-010-	0-10V Dual Tech Sensor Dimmer - Vacancy with LED Single pole/3-Way preset	0-10VDC LED/FLR	960	120	Light Almond (LA)
			2200	277	Ivory (V)
					Red (R)

For ordering devices, include Catalog no. followed by the Color suffix:
W (White), B (Black), G (Gray), LA (Light Almond), V (Ivory), R (Red)

Note: Not all colors are available in stock and some color options may have extended lead times.



Catalog No.	Description	Compatible Lamp Types	Rating		Colors
			Watt	V/AC	
OSW-P-010-	0-10V Occupancy Dimmer Sensor	0-10VDC LED/FLR	1200	120	White (W)
			2200	277	Black (BK)
VSW-P-010-	0-10V Vacancy Dimmer Sensor	0-10VDC LED/FLR	1200	120	Gray (G)
			2200	277	Light Almond (LA)
					Ivory (V)

For ordering devices, include Catalog no. followed by the Color suffix:
W (White), B (Black), G (Gray), LA (Light Almond), V (Ivory)

Note: Not all colors are available in stock and some color options may have extended lead times.



Lighting Product Lines

Ametrix
AtLite
Corelite
Ephesus
Fail-Safe
Halo
Halo Commercial
Invue
io
Iris
Lumark
Lumière
McGraw-Edison
Metalux
MWS
Neo-Ray
Portfolio
RSA
Shaper
Streetworks
Sure-Lites

Controls Product Lines

Fifth Light Technology
Greengate
iLight (International Only)
iLumin
Zero 88

Connected Lighting Systems

Distributed Low-Voltage Power
HALO Home
iLumin Plus
LumaWatt Pro
WaveLinx

Eaton

1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting
For service or technical assistance:
1-800-553-3879

Canada Sales

5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. BR503058EN
February 2019

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.