

# Screwless wallplates

Catalog#	Prepared by
Project	Date
Comments	Type

## Overview

The screwless wallplate is a system accessory for Greengate wall box devices. The wallplate fits a standard decorator opening or toggle opening and provides a contemporary, sleek design.

## Features

- Screwless Wallplates clip easily into place with gentle pressure
- Virtually unbreakable polycarbonate construction
- Mid-sized to cover wall imperfections and large wallboard openings
- Available in multi-gang configurations
- Available in a variety of colors
- Meets flammability requirements per UL 94, V2 rated

Clearly marked top edges makes mounting plate easy to orient and attach



Screwless wallplates clip easily into place with gentle pressure and no visible screws



Powering Business Worldwide

## Specifications

<b>Construction</b>	Polycarbonate
<b>Environmental</b>	Flammability: Meets UL 94 requirements; wallplates V2 rated
<b>Operating Environment</b>	Temperature: -40°F to 149°F (-40°C to 65°C)
<b>Size</b>	Decorator Opening Dimensions: 2.64" H x 1.31" W (67.1mm x 33.3mm) Toggle Opening Dimensions: 1" H x 0.5" W (25.4mm x 12.7mm)
<b>Wallplate Dimensions</b>	1-Gang: 4.88" H x 3.13" W (123.8mm x 79.4mm) 2-Gang: 4.88" H x 4.95" W (123.8mm x 125.4mm) 3-Gang: 4.88" H x 6.76" W (123.8mm x 171.4mm) 4-Gang: 4.88" H x 8.57" W (123.8mm x 217.5mm) 5-Gang: 4.88" H x 10.38" W (123.8mm x 263.5mm) 6-Gang: 4.88" H x 12.19" W (123.8mm x 309.5mm)


## Description

Screwless wallplates appear to float freely on the surface of the wall and are designed for easy and fast installation. Mounting plate attaches to the device and the wallplate is simply pressed into place.

## Installation


This system accessory will require wall mounting at the site.

## Dimensions



### Decorator Wallplates can be used with:

Occupancy and Vacancy sensors, GDS, GMDS, Automatic Turn-Off switches and 0-10V slide dimmers



### Toggle Wallplates can be used with:

Momentary toggle switches, Automatic Turn-Off switches

## Ordering

### Decorator Wallplates

Catalog #	Description
<b>1-Gang</b>	
PJS26W	White, Single Gang, Screwless Wallplate
PJS26V	Ivory, Single Gang, Screwless Wallplate
PJS26GY	Gray, Single Gang, Screwless Wallplate
PJS26BK	Black, Single Gang, Screwless Wallplate
<b>2-Gang</b>	
PJS262W	White, Two Gang, Screwless Wallplate
PJS262V	Ivory, Two Gang, Screwless Wallplate
PJS262BK	Black, Two Gang, Screwless Wallplate
<b>3-Gang</b>	
PJS263W	White, Three Gang, Screwless Wallplate
PJS263V	Ivory, Three Gang, Screwless Wallplate
PJS263BK	Black, Three Gang, Screwless Wallplate
<b>4-Gang</b>	
PJS264W	White, Four Gang, Screwless Wallplate
PJS264V	Ivory, Four Gang, Screwless Wallplate
PJS264BK	Black, Four Gang, Screwless Wallplate
<b>5-Gang</b>	
PJS265W	White, Five Gang, Screwless Wallplate
PJS265V	Ivory, Five Gang, Screwless Wallplate
PJS265BK	Black, Five Gang, Screwless Wallplate
<b>6-Gang</b>	
PJS266W	White, Six Gang, Screwless Wallplate
PJS266V	Ivory, Six Gang, Screwless Wallplate
PJS266BK	Black, Six Gang, Screwless Wallplate

### Toggle Wallplates

Catalog #	Description
<b>1-Gang</b>	
PJS1W	White, Single Gang, Screwless Wallplate
PJS1V	Ivory, Single Gang, Screwless Wallplate
<b>2-Gang</b>	
PJS2W	White, Two Gang, Screwless Wallplate
PJS2V	Ivory, Two Gang, Screwless Wallplate
<b>3-Gang</b>	
PJS3W	White, Three Gang, Screwless Wallplate
PJS3V	Ivory, Three Gang, Screwless Wallplate
<b>4-Gang</b>	
PJS4W	White, Four Gang, Screwless Wallplate
PJS4V	Ivory, Four Gang, Screwless Wallplate

**Eaton**  
 1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
 Eaton.com

Eaton  
 Lighting systems – Controls products  
 203 Cooper Circle  
 Peachtree City, GA 30269  
[www.eaton.com/lightingsystems](http://www.eaton.com/lightingsystems)

© 2015 Eaton  
 All Rights Reserved  
 Printed in USA  
 Publication No. TD503016EN  
 June 15, 2015

Eaton is a registered trademark.

All other trademarks are property  
 of their respective owners.