

# Shoplights

## SHP Series - LED Shoplights



The Metalux SHP LED Shoplight comes in two new lumen packages, expanded mounting options and a compact, low profile design. This fully integrated LED luminaire can be used in applications such as workshops and utility rooms where task lighting and portability are important. The all new SHP shoplight can be surface mounted or suspended using the included hanging chain, S-hooks or brackets. A 5 ft. grounded cord and plug, and pull chain allows for easy on/off operation and installation. The SHP has a five-year warranty and uses LEDs at a rated life of 50,000 hours.

### Construction and Performance

- Fully assembled 43" long metal housing with finished end caps
- Two unique lumen packages – standard (3200) and high output (4500)
- Frosted white polycarbonate lens for an even distribution
- 4000K CCT at CRI > 80 provides excellent color rendering for task applications
- Includes 36" chain-set, S-hooks and snap brackets for suspended or surface mount installation
- Standard 120V 5 ft. grounded power cord and plug, and pull chain for easy on/off operation
- Up to 109 lm/W provides >40% energy savings over 2-lamp T8 shoplights

### Reliability and Compliance

- cULus listed for dry locations, Energy Star, and FCC Class B compliant
- Five-year comprehensive warranty
- Excellent lumen maintenance L70 > 50K based on TM21

Model#	Product Description	LED		Compared to T12 Fluorescent		Compared to T8 Fluorescent	
		Lumens	Wattage	Fixture Wattage	Energy Savings	Fixture Wattage	Energy Savings
4SHP3240R	Utility LED Shoplight, 120V	3460	32W	62W	48%	56W	43%
4SHP4540R	Utility LED Shoplight, 120V	4486	43W	62W	31%	56W	23%

Model#	Product Description	UPC	Unit Carton (L x W x H)	Energy Qualification
4SHP3240R	Utility LED Shoplight, 3200 lumens, 4000K, 120V	080083785599	44 in. x 4.3 in. x 3.5 in.	Energy Star®
4SHP4540R	Utility LED Shoplight, 4500 lumens, 4000K, 120V	080083785605	44 in. x 4.3 in. x 3.5 in.	Energy Star®

**Eaton**  
 1121 Highway 74 South  
 Peachtree City, GA 30269  
 P: 770-486-4800  
[www.eaton.com/lighting](http://www.eaton.com/lighting)

Canada Sales  
 5925 McLaughlin Road  
 Mississauga, Ontario L5R 1B8  
 P: 905-501-3000  
 F: 905-501-3172

© 2017 Eaton  
 All Rights Reserved  
 Printed in USA  
 Publication No. SA519024EN  
 September 26, 2017

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.

