

347V Flat Panels have arrived!

Cover more applications with Eaton's Industry Leading Flat Panel Offering



Eaton is excited to announce the launch our new high performance & cost effective 347V dedicated Flat Panels as the latest additions to our industry leading Flat Panel offering. Now available in 347V with up to 6400 Lumens with 3500K, 4000K, and 5000K options in stock! The Eaton Flat Panel series provides premium performance and pleasing aesthetics. The luminaire is optimized for shallow plenum grid ceilings but may also be surface or suspension mounted

Developed using Eaton's latest generation of solid-state components and electronic driver technologies, these panels are targeted at distributor day-to-day stock requirements and design build projects, making them an ideal choice for both new construction and renovation.

Construction and Performance

- Dedicated 347V Driver, 0-10V Dimming
- 3500K, 4000K, 5000K options in stock
- Excellent performance with up to 6400 Lumens
- Acrylic light guide – longer life and consistent colour
- Tightly sealed bezel and light guides – no bug or debris intrusion
- Ultra thin less than 2" height fits shallow plenums with room to spare
- Surface and Suspension mounting options available

Reliability and Compliance

- Indoor luminaires are cULus listed for 25C ambient environments
- IC rated for direct insulation contact
- RoHS compliant
- Damp location listed
- 5 Year Comprehensive Warranty

Catalog Number	Product Description	Lumens	CCT
14FP4235C-347V	1x4 Flat Panel 4200L, 35K, 0-10V, 347V	4200	3500K
14FP4240C-347V	1x4 Flat Panel 4200L, 40K, 0-10V, 347V	4200	4000K
14FP4250C-347V	1x4 Flat Panel 4200L, 50K, 0-10V, 347V	4200	5000K
22FP4235C-347V	2x2 Flat Panel 4200L, 35K, 0-10V, 347V	4200	3500K
22FP4240C-347V	2x2 Flat Panel 4200L, 40K, 0-10V, 347V	4200	4000K
22FP4250C-347V	2x2 Flat Panel 4200L, 50K, 0-10V, 347V	4200	5000K
24FP4735C-347V	2x4 Flat Panel 4700L, 35K, 0-10V, 347V	4700	3500K
24FP4740C-347V	2x4 Flat Panel 4700L, 40K, 0-10V, 347V	4700	4000K
24FP6435C-347V	2x4 Flat Panel 6400L, 35K, 0-10V, 347V	6400	3500K
24FP6440C-347V	2x4 Flat Panel 6400L, 40K, 0-10V, 347V	6400	4000K
24FP6450C-347V	2x4 Flat Panel 6400L, 50K, 0-10V, 347V	6400	5000K

All SKUs listed above are in stock and pricing will be loaded during the next FLASH update.



Powering Business Worldwide

Eaton
1121 Highway 74 South
Peachtree City, GA 30269
P: 770-486-4800
www.eaton.com/lighting

Canada
5925 McLaughlin Road
Mississauga, Ontario L5R 1B8
P: 905-501-3000
F: 905-501-3172

© 2018 Eaton
All Rights Reserved
Printed in USA
June, 2019

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.